



SERIES 970

POWERTRIP™ CONNECTORS



THE POWER CONNECTOR FOR EXTREME ENVIRONMENTS

FIRST EDITION • MARCH 2013

SERIES 970
HIGH CURRENT,
HARSH ENVIRONMENT

POWERTRIP™

*The power connector
for extreme environments*



Protect circuits with Series 970 PowerTrip™ connectors

The George HW Bush, pictured above, is the first US Navy surface ship to use the Series 970 PowerTrip™ connector. Series 970 connectors fill the need for a military-grade harsh environment power connector with improved mechanical, environmental and electrical performance. PowerTrip™ also delivers reduced size and weight compared to lower-density 5015 type power connectors. Featuring triple-start mating threads, crimp rear-release contacts, upgraded finish choices and improved EMI protection, the PowerTrip™ connector is ideal for power distribution units, hybrid electric drives, motors, and other high current, high-reliability applications.



**POWER
TRIP™**


Glenair®

Glenair, Inc.
1211 Air Way
Glendale, CA
91201-2497
818-247-6000
sales@glenair.com
www.glenair.com

Series 970 Connectors and Accessories Introduction Table of Contents




Introduction to the Series 970 PowerTrip™



Cutaway Views, Features and Benefits2
Connector Selection Guide.....3
Contact System, Current Rating.....4

A

General Information and Reference



Contact Arrangements5
Wire Diameter Table9
Connector Materials and Finishes10
Product Specification.....11
Material and Finish Options.....14
PowerTrip™ Connectors for Space Flight.....15

B

Cable Connectors



970-001 Cable Plug with Accessory Thread.....16
970-011 Cable Plug with Integral Banding Porch.....18
970-005 Cable Receptacles20
Overmolded Turboflex Cordsets.....19

C

Panel Mount Connectors



970-003 Square Flange Receptacles20
970-009 Low Profile Square Flange Receptacles22
970-013 Low Profile Square Flange w/ O-ring24
970-008 Low Profile square Flange w/ PC Tails.....26
970-012 Hermetic Receptacles30
970-004 Jam Nut Receptacles32
970-010 Low Profile Jam Nut Receptacles34

D


Feed-Thru Bulkhead Connectors



970-006 Feed-Thru Bulkhead.....36
970-007 Hermetic Feed-Thru Bulkhead38

E

Filtered Connectors



240-970W Square Flange Filter Receptacle40
240-970J Jam Nut Filter Receptacle42
PowerTrip™ Powerline Filters44

F

Contacts and Tools



Contacts **850-026, 850-027, 850-037, 850-038**45
Crimp Tools.....48
Insertion/Extraction Tools, Shield termination Tools49
Connector Holding Tools50

G

Accessories



Accessories Selection Guide.....51
Backshells and Boots52
Panel Gaskets74
Protective Covers76

H



Series 970 Connectors and Accessories Introduction



Cutaway View, Features and Benefits

Series 970 PowerTrip™ Connectors

The Series 970 connector is a high current, harsh environment connector capable of meeting the demanding requirements of modern defense and aerospace systems. The connector is significantly smaller and lighter than lower-density 5015 type connectors.


Features

- **Fast, easy connector mating with triple-start ACME thread. 360° turn for full mating**
- **5 polarizing keys, 6 keying positions**
- **LouverBand sockets for improved conductivity and longer life**
- **High conductivity copper alloy contacts**
- **Crimp, rear release contact system**
- **Splined backshell interface for improved EMI protection**
- **Ratcheting coupling for secure mating**
- **-65° C to +200° C**
- **Size 8, 4 and 1/0 contact sizes**
- **Last-mate, first-break size 12 and 16 contacts**



Plug Key Positions				
Pos	A°	B°	C°	D°
1	80	142	196	293
2	135	170	200	310
3	49	169	200	244
4	66	140	200	257
5	62	145	180	280
6	79	153	197	272

Receptacle keyways are mirrored



Cable Mount Plugs and Receptacles

Cable Plug with
Accessory Threads
970-001



Page 16

Cable Plug with
Integral Banding
Porch
970-011



Page 18

Cable Receptacle
with Accessory
Threads
970-005



Page 20

Overmolded TurboFlex Cordsets



Page 22

Panel Mount Receptacles

Square Flange
Receptacle with
Accessory Threads
970-003



Page 23

Square Flange
Receptacle, Low
Profile
970-009



Page 25

Square Flange
Receptacle, Low
Profile, O-ring
970-013



Page 27

Square Flange
Receptacle, Low
Profile, PC Tails
970-008



Page 29

Square Flange
Receptacle,
Hermetic
970-012



Page 33

Jam Nut Receptacle
with Accessory
Threads
970-004




Page 35

Jam Nut
Receptacle, Low
Profile
970-010



Page 37

Filtered Jam Nut
Receptacle
240-970J



Page 45

Filtered Square
Flange Receptacle
240-970W



Page 43

Feed-Thru Bulkhead Receptacles

Jam Nut Feed-Thru
Receptacle
970-006



Page 39

Hermetic Jam
Nut Feed-Thru
Receptacle
970-007



Page 41



Series 970 Connectors and Accessories Introduction

LouverBand Contact System, Current Rating

About the PowerTrip Contact System

Series 970 contacts are precision-machined using high conductivity copper alloy. A stamped and formed spring ("louverband") is installed into the socket contact. The spring is made from 6 mil beryllium copper (BeCu). Testing has demonstrated that this contact system outperforms conventional aerospace-grade contact systems. The louverband spring provides many points of electrical contact with the mating pin, as opposed to a few "high spots" on a conventional four-finger contact as shown in *Fig. 2*. The size #8 Powertrip socket contact has a total of 18 louvers. The #4 has 27 louvers, and the #1/0 has 42 louvers. The louverband design offers lower voltage drop for reduced temperature rise and higher current carrying capacity. In addition to its electrical advantages, the louverband also is mechanically superior to four-finger contacts. The louverband spring has consistent, stable normal force, even when subjected to thousands of mating cycles and temperature extremes.

About "Last-Mate, First-Break" Capability

PowerTrip connectors should be mated and demated only after the circuit has been de-energized. The Powertrip contact arrangements include layouts with size #12 and #16 contacts. These contacts are designed to mate only after the larger power contacts are mated. When uncoupled, the size #12 and #16 contacts separate before the power contacts are disengaged. These smaller contacts are typically used for safety interlock circuits.

About Current Rating

PowerTrip connector current carrying capacity and maximum contact resistance are in accordance with AS39029 specifications for conventional contacts. Testing of Powertrip contacts has shown the contact resistance (voltage drop) to be up to 60% lower than the allowable voltage drops of AS39029. Temperature -Rise tests have also demonstrated the Powertrip contact to generate less heat under load than conventional contacts. However, the maximum safe current load is dependent on a number of application-specific variables. The maximum safe current load is the combination of the electrical load and ambient conditions that do not exceed a maximum connector internal hot-spot temperature of +200° C, which is the maximum recommended operating temperature.

Contact Resistance after 1000 Mating Cycles




Figure 1
LouverBand Socket Contact



Figure 2
Conventional Contact on the Left, LouverBand Contact on the Right

CURRENT RATING	
Contact Size	Amps
16	13
12	23
8	60
4	100
1/0	175
2/0	205

Series 970 Connectors and Accessories Technical Reference Contact Arrangements







SERIES 970 CONTACT ARRANGEMENTS

Contact Size	Contact Arrangement	Contact Size and Quantity					
		#16	#12	#8	#4	#1/0	#2/0
Size #16	28-15	15					
Size #12	32-20	1	19				
	32-A22		22				
Size #8	18-2			2			
	18-4		2	2			
	20-3			3			
	20-5		2	3			
	20-7	4		3			
	20-4			4			
	24-5			5			
	28-8		1	7			
	28-12	6		6			
	32-12	2		10			
	36-16	3		13			
40-21			21				
Size #4	24-2				2		
	24-6		4		2		
	24-3				3		
	24-A6		3		3		
	28-4				4		
	28-9	5			4		
	32-5				5		
	32-7				7		
	36-A8				8		
	36-9	14	14	2	1		
	40-10	16		9	4		
Size #1/0	24-1					1	
	32-2					2	
	32-4				2	2	
	32-3					3	
	32-6		3			3	
	36-4					4	
	36-B8	4				4	
	40-5					5	
Size #2/0	24-A1						1
	36-2						2

CONTACT ARRANGEMENTS

CONTACT SYMBOLS



Shell Size-Contact Quantity	18-2	18-4		20-3
Contact Size	2 #8	2 #8	2 #12	3 #8
Amps	120	120	46	180
Total Amps	120	166		180







Series 970 Connectors and Accessories
 Technical Reference
 Contact Arrangements

Contact Arrangements shown are mating face views of pin connectors.
 Socket arrangements are reversed.





B

CONTACT SYMBOLS







Shell Size-Contact Quantity	20-4	20-5		20-7	
Contact Size	4 #8	3 #8	2 #12	3 #8	4 #16
Amps	240	180	46	180	52
Total Amps	240	226		232	

CONTACT SYMBOLS



Shell Size-Contact Quantity	24-1	24-A1	24-2
Contact Size	1 #1/0	1 #2/0	2 #4
Amps	175	205	200
Total Amps	175	205	200

CONTACT SYMBOLS





Shell Size-Contact Quantity	24-3	24-5	24-6	
Contact Size	3 #4	5 #8	2 #4,	4 #12
Amps	300	300	200	92
Total Amps	300	300	292	

Series 970 Connectors and Accessories
 Technical Reference
 Contact Arrangements





Contact Arrangements shown are mating face views of pin connectors.
 Socket arrangements are reversed.

CONTACT SYMBOLS





Shell Size-Contact Quantity	24-A6		28-4	
Contact Size	3 #4	3 #12	4 #4	
Amps	300	69	400	
Total Amps	369		400	

CONTACT SYMBOLS



Shell Size-Contact Quantity	28-8		28-9	
Contact Size	1 #12	7 #8	4 #4	5 #16
Amps	23	420	400	65
Total Amps	443		465	

CONTACT SYMBOLS



Shell Size-Contact Quantity	28-12		28-15	
Contact Size	6 #8	6 #16	15 #16	
Amps	360	78	195	
Total Amps	438		195	





Series 970 Connectors and Accessories
 Technical Reference
 Contact Arrangements

Contact Arrangements shown are mating face views of pin connectors.
 Socket arrangements are reversed.




B

CONTACT SYMBOLS






Shell Size-Contact Quantity	32-2	32-3
Contact Size	2 #1/0	3 1/0
Amps	350	525
Total Amps	350	525

CONTACT SYMBOLS



Shell Size-Contact Quantity	32-4		32-5
Contact Size	2 #1/0	2 #4	5 #4
Amps	350	200	500
Total Amps	550		500

CONTACT SYMBOLS





Shell Size-Contact Quantity	32-6		32-7
Contact Size	3 #1/0	3 #12	7 #4
Amps	525	69	700
Total Amps	594		700

Series 970 Connectors and Accessories
 Technical Reference
 Contact Arrangements and Wire Diameter






Contact Arrangements shown are mating face views of pin connectors.
 Socket arrangements are reversed.

CONTACT SYMBOLS






Shell Size-Contact Quantity	32-12		32-20	
Contact Size	10 #8	2 #16	1 #16	19 #12
Amps	600	26	13	437
Total Amps	626		450	

CONTACT SYMBOLS



Shell Size-Contact Quantity	32-A22	36-2
Contact Size	2 #12	2 #2/0
Amps	46	410
Total Amps	46	410

CONTACT SYMBOLS



Shell Size-Contact Quantity	36-4	36-A8
Contact Size	4 #1/0	8 #4
Amps	700	800
Total Amps	700	800





Series 970 Connectors and Accessories Technical Reference

Contact Arrangements and Wire Diameter

**Contact Arrangements shown are mating face views of pin connectors.
Socket arrangements are reversed.**




B

CONTACT SYMBOLS



Shell Size-Contact Quantity	36-B8		36-9			
Contact Size	4 #1/0	4 #16	1 #4	2 #8	14 #12	14 #16
Amps	700	52	100	120	322	182
Total Amps	752		724			

CONTACT SYMBOLS




Shell Size-Contact Quantity	36-16		40-5
Contact Size	3 #16	13 #8	5 #1/0
Amps	39	780	875
Total Amps	819		875

Series 970 Connectors and Accessories
 Technical Reference
 Contact Arrangements and Wire Diameter



Contact Arrangements shown are mating face views of pin connectors.
 Socket arrangements are reversed.



B

Shell Size-Contact Quantity	40-10			40-21
Contact Size	4 #4	9 #8	16 #16	21 #8
Amps	400	540	78	1260
Total Amps	1018			1260

Wire Insulation Diameters

This table shows the minimum and maximum wire diameters compatible with Series 970 connectors. Wires smaller than specified will not seal properly. Wires larger than specified will be difficult to install and extract.

Contact Size	Wire Size (AWG)	Finished Wire Outside Dimensions			
		Minimum Diameter		Maximum Diameter	
		Inches	mm	Inches	mm
16	16	.053	1.35	.103	2.62
12	12	.085	2.16	.158	4.01
8	8	.187	4.75	.203	5.16
4	4	.280	7.11	.320	8.13
1/0	0	.465	11.81	.500	12.7
2/0	2/0	.590	14.99	.630	16.00



Series 970 Connectors and Accessories
Technical Reference
Contact Rating, Materials and Finishes

B

MATERIALS AND FINISHES

COMPONENT	MATERIAL	FINISH
Contacts, Size #1/0, #4 and #8	Pin contact and socket contact body: high-conductivity copper alloy per ASTM B301 Hermetic contact: ferrous alloy per ASTM B 829 Socket contact spring: beryllium copper	Code 1: Silver per ASTM-B700, 0.0002 – 0.0003 thick over nickel plate per QQ-N-290 class 2 .000050-.000100 thick Code 2: Gold per ASTM B488, Type II, Code C, Class 1.25, .000050-.000100 thick over nickel plate per QQ-N-290, Class 2, .000050-.000100 thick
Contacts, Size #12 and #16	Pin contact: copper alloy Socket contact: copper alloy, stainless steel hood	Gold per ASTM B488, Type II, Code C, 0.000015-0.000025 thick over palladium per ASTM B679, 0.000060-0.000100 thick, over nickel per SAE AMS-QQ-N-290 Class 2, 0.000050-0.000100 thick
Contacts, Hermetic, Size #12 and #16	Pin contact: ferrous alloy per ASTM B 829 Socket Contact: ferrous alloy pin, copper alloy socket, stainless steel hood	Code 1: Silver per ASTM-B700, 0.0002 – 0.0003 thick over nickel plate per QQ-N-290 class 2 .000050-.000100 thick Code 2: Gold per ASTM B488, Type II, Code C, Class 1.25, .000050-.000100 thick over nickel plate per QQ-N-290, Class 2, .000050-.000100 thick
Aluminum Shells, Coupling Nuts	Aluminum alloy 6061 or 7075	See Ordering Information
Stainless Steel Shells, Coupling Nuts, Hermetic Receptacle Shells	Stainless steel, AISI 316	See Ordering Information
Insulators	Fiberglass-reinforced thermosetting epoxy resin per ASTM-D-5948, Type GEI-5, black	None
Insulator, Hermetic	Vitreous glass	None
Interfacial Seals, Grommets	Fluorosilicone/silicone blend, blue	None
EMI Spring	Beryllium copper	Nickel-plated
Contact Retention Clip	Beryllium copper	None
Clinch Nut	Stainless Steel	Passivated
Anti-Decoupling Ratchet Spring	Stainless Steel	None
Filter Element	Multilayer ceramic planar array	

Series 970 Connectors and Accessories
 Technical Reference
 Product Specification



DESCRIPTION	REQUIREMENT	PROCEDURE																					
Altitude Immersion	No evidence of moisture on connector interface or contacts. At the end of the third cycle, while still submersed, connectors shall meet 2000 Vac dielectric withstanding voltage and 1,000 megohms insulation resistance.	EIA-364-03 Simulated 75,000 feet altitude																					
Altitude- Low Temperature	Insulation resistance greater than 5,000 megohms while mated and exposed to simulated 110,000 feet altitude and -65°C.	EIA-364-105 Mated pair																					
Blowing Sand and Dust	Connectors shall meet electrical and mechanical requirements following exposure to sand and dust.	MIL-STD-810G Method 510.5 Mated connectors																					
Contact Insertion and Removal Force (Maintenance Aging)	<table border="1"> <thead> <tr> <th>Contact Size</th> <th>Max. Pounds</th> </tr> </thead> <tbody> <tr><td>16</td><td>20</td></tr> <tr><td>12</td><td>30</td></tr> <tr><td>8</td><td>35</td></tr> <tr><td>4</td><td>40</td></tr> <tr><td>1/0</td><td>40</td></tr> </tbody> </table>	Contact Size	Max. Pounds	16	20	12	30	8	35	4	40	1/0	40	EIA-364-24									
Contact Size	Max. Pounds																						
16	20																						
12	30																						
8	35																						
4	40																						
1/0	40																						
Contact resistance (copper alloy)	<table border="1"> <thead> <tr> <th>Wire Size</th> <th>Test Current</th> <th>Voltage Drop</th> </tr> </thead> <tbody> <tr><td>16</td><td>13</td><td>49</td></tr> <tr><td>14</td><td>17</td><td>40</td></tr> <tr><td>12</td><td>23</td><td>42</td></tr> <tr><td>8</td><td>46</td><td>26</td></tr> <tr><td>4</td><td>80</td><td>23</td></tr> <tr><td>1/0</td><td>150</td><td>21</td></tr> </tbody> </table>	Wire Size	Test Current	Voltage Drop	16	13	49	14	17	40	12	23	42	8	46	26	4	80	23	1/0	150	21	EIA-364-06 Test current in amperes. Maximum voltage drop in millivolts. Silver-coated copper wire, +25°C.
Wire Size	Test Current	Voltage Drop																					
16	13	49																					
14	17	40																					
12	23	42																					
8	46	26																					
4	80	23																					
1/0	150	21																					
Contact resistance (ferrous alloy hermetic)	<table border="1"> <thead> <tr> <th>Wire Size</th> <th>Test Current</th> <th>Voltage Drop</th> </tr> </thead> <tbody> <tr><td>16</td><td>10</td><td>539</td></tr> <tr><td>14</td><td>13</td><td>440</td></tr> <tr><td>12</td><td>17</td><td>462</td></tr> <tr><td>8</td><td>33</td><td>286</td></tr> <tr><td>4</td><td>60</td><td>253</td></tr> <tr><td>1/0</td><td>100</td><td>231</td></tr> </tbody> </table>	Wire Size	Test Current	Voltage Drop	16	10	539	14	13	440	12	17	462	8	33	286	4	60	253	1/0	100	231	EIA-364-06 Test current in amperes. Maximum voltage drop in millivolts. Silver-coated copper wire, +25°C.
Wire Size	Test Current	Voltage Drop																					
16	10	539																					
14	13	440																					
12	17	462																					
8	33	286																					
4	60	253																					
1/0	100	231																					
Contact Retention	<table border="1"> <thead> <tr> <th>Contact Size</th> <th>Min. Pounds</th> </tr> </thead> <tbody> <tr><td>16</td><td>25</td></tr> <tr><td>12</td><td>30</td></tr> <tr><td>8</td><td>50</td></tr> <tr><td>4</td><td>60</td></tr> <tr><td>1/0</td><td>75</td></tr> </tbody> </table>	Contact Size	Min. Pounds	16	25	12	30	8	50	4	60	1/0	75	EIA-364-29 Method B									
Contact Size	Min. Pounds																						
16	25																						
12	30																						
8	50																						
4	60																						
1/0	75																						
Salt Spray material/finish code ME	No exposure of base metal. Connectors shall meet DWV, contact resistance, shell-to-shell resistance and coupling torque	EIA-364-26 96 hours																					
Dynamic Salt Spray material/finish codes NF, ZR, MT, Z1	No exposure of base metal. Connectors shall meet DWV, contact resistance, shell-to-shell resistance and coupling torque	MIL-DTL-38999 Para. 4.5.13.2 50 cycles of mating and unmating prior to test 452 hours mated 48 hours unmated 450 cycles of mating and unmating following salt spray exposure																					
Coupling Torque	<table border="1"> <thead> <tr> <th>Shell Size</th> <th>Maximum (in-lb.)</th> </tr> </thead> <tbody> <tr><td>18</td><td>28</td></tr> <tr><td>20</td><td>32</td></tr> <tr><td>24</td><td>36</td></tr> <tr><td>28</td><td>47</td></tr> <tr><td>32</td><td>53</td></tr> <tr><td>36</td><td>65</td></tr> <tr><td>40</td><td>75</td></tr> </tbody> </table>	Shell Size	Maximum (in-lb.)	18	28	20	32	24	36	28	47	32	53	36	65	40	75						
Shell Size	Maximum (in-lb.)																						
18	28																						
20	32																						
24	36																						
28	47																						
32	53																						
36	65																						
40	75																						
Current Rating	<table border="1"> <thead> <tr> <th>Contact Size</th> <th>Copper Alloy</th> <th>Ferrous Alloy</th> </tr> </thead> <tbody> <tr><td>16</td><td>13</td><td>10</td></tr> <tr><td>12</td><td>23</td><td>17</td></tr> <tr><td>8</td><td>60</td><td>33</td></tr> <tr><td>4</td><td>100</td><td>60</td></tr> <tr><td>1/0</td><td>175</td><td>125</td></tr> </tbody> </table>	Contact Size	Copper Alloy	Ferrous Alloy	16	13	10	12	23	17	8	60	33	4	100	60	1/0	175	125	EIA-364-70			
Contact Size	Copper Alloy	Ferrous Alloy																					
16	13	10																					
12	23	17																					
8	60	33																					
4	100	60																					
1/0	175	125																					
Dielectric Withstanding Voltage at Sea Level (not applicable to filter connectors)	No breakdown or flashover at 2000 volts	EIA-364-20 AC rms 50-60 Hz 2mA max. leakage current																					



Series 970 Connectors and Accessories
 Technical Reference
 Product Specification

B

DESCRIPTION	REQUIREMENT	PROCEDURE																										
Dielectric Withstanding Voltage at Sea Level, filter connectors	No breakdown or flashover at 1250 volts	EIA-364-20 Volts DC 2mA max. leakage current																										
EMI Shielding Effectiveness	<table border="1"> <thead> <tr> <th>Frequency MHz</th> <th>Min. Atten. dB</th> </tr> </thead> <tbody> <tr><td>100</td><td>90</td></tr> <tr><td>200</td><td>88</td></tr> <tr><td>300</td><td>88</td></tr> <tr><td>400</td><td>87</td></tr> <tr><td>800</td><td>85</td></tr> <tr><td>1000</td><td>85</td></tr> <tr><td>1500</td><td>76</td></tr> <tr><td>2000</td><td>70</td></tr> <tr><td>3000</td><td>69</td></tr> <tr><td>4000</td><td>68</td></tr> <tr><td>6000</td><td>66</td></tr> <tr><td>10000</td><td>65</td></tr> </tbody> </table>	Frequency MHz	Min. Atten. dB	100	90	200	88	300	88	400	87	800	85	1000	85	1500	76	2000	70	3000	69	4000	68	6000	66	10000	65	EIA-364-66 1,000 MHz to 10,000 MHz. MIL-DTL-38999L Para. 4.5.28.1 100 MHz to 1,000 MHz Prior to EMI test, connectors shall be mated a minimum of 500 cycles.
Frequency MHz	Min. Atten. dB																											
100	90																											
200	88																											
300	88																											
400	87																											
800	85																											
1000	85																											
1500	76																											
2000	70																											
3000	69																											
4000	68																											
6000	66																											
10000	65																											
External Bend Moment	No evidence of damage. <table border="1"> <thead> <tr> <th>SHELL SIZE</th> <th>Bend Moment (in-lb.)</th> </tr> </thead> <tbody> <tr><td>18</td><td>420</td></tr> <tr><td>20</td><td>450</td></tr> <tr><td>24</td><td>570</td></tr> <tr><td>28</td><td>630</td></tr> <tr><td>32</td><td>750</td></tr> <tr><td>36</td><td>810</td></tr> <tr><td>40</td><td>870</td></tr> </tbody> </table>	SHELL SIZE	Bend Moment (in-lb.)	18	420	20	450	24	570	28	630	32	750	36	810	40	870	SAE AS50151 Para. 4.6.20										
SHELL SIZE	Bend Moment (in-lb.)																											
18	420																											
20	450																											
24	570																											
28	630																											
32	750																											
36	810																											
40	870																											
Fluid Immersion	No visual evidence of degradation from immersion in various fuels and oils. Following immersion connectors shall meet coupling torque and dielectric withstanding voltage at sea level.	EIA-364-10																										
Fungus Resistance	Connector materials shall be fungus inert	MIL-STD-810G Method 508.6																										
High-Impact Shock	No discontinuity, no cracking, breaking or loosening of parts. Connectors shall meet electrical requirements after shock test.	MIL-DTL-38999L Para. 4.5.23.2 MIL-S-901, grade A																										
Humidity, 21 Day (Damp heat, Long Term)	No deterioration which will adversely affect the connector. Following the drying period, connectors shall meet 100 megohms minimum, contact resistance, shell-to-shell resistance, DWV, mating and unmating requirements.	EIA-364-31 Condition C Method II 90-95% RH 40° C Apply 100 volts DC during test. 4 hours drying time at ambient temperature prior to final measurements.																										
Humidity, Cyclic (Damp Heat, Cyclic) (Moisture Resistance)	No deterioration which will adversely affect the connector. 100 megohms minimum insulation resistance during the final cycle. Following the recovery period, connectors shall meet contact resistance, shell-to-shell resistance and DWV requirements.	EIA-364-31 Condition B Method III 80-98% RH 10 cycles (10 days) +25° C to +65° C Step 7b vibration deleted. 24 hour recovery period.																										
Impact, Cable Connectors	No impairment of function. Connector shall meet contact resistance, insulation resistance and waterproof sealing.	EIA-364-42 1 meter 8 drops																										
Ingress Protection	IP67 rating	IEC-60529																										
Insert Retention	<table border="1"> <thead> <tr> <th>SHELL SIZE</th> <th>FORCE (lbs.)</th> </tr> </thead> <tbody> <tr><td>18</td><td>50</td></tr> <tr><td>20</td><td>75</td></tr> <tr><td>24</td><td>85</td></tr> <tr><td>28</td><td>105</td></tr> <tr><td>32</td><td>115</td></tr> <tr><td>36</td><td>135</td></tr> <tr><td>40</td><td>165</td></tr> </tbody> </table>	SHELL SIZE	FORCE (lbs.)	18	50	20	75	24	85	28	105	32	115	36	135	40	165	EIA-364-35 Unmated connectors 100 ± 5 pounds per square inch										
SHELL SIZE	FORCE (lbs.)																											
18	50																											
20	75																											
24	85																											
28	105																											
32	115																											
36	135																											
40	165																											
Insulation Resistance at Ambient Temperature	5,000 megohms minimum	EIA-364-21 500 volts DC ± 50 volts.																										
Insulation Resistance at Elevated Temperature	1,000 megohms minimum following 30 minutes at +200°C	EIA-364-21 500 volts DC ± 50 volts.																										

**Series 970 Connectors and Accessories
Technical Reference
Product Specification**



DESCRIPTION	REQUIREMENT	PROCEDURE						
Low Level Contact Resistance	<table border="0"> <tr> <td><u>Wire Size</u></td> <td><u>Max. Milliohms</u></td> </tr> <tr> <td>16</td> <td>5</td> </tr> <tr> <td>20</td> <td>9</td> </tr> </table>	<u>Wire Size</u>	<u>Max. Milliohms</u>	16	5	20	9	EIA-364-23 100 milliamperes maximum and 20 millivolts maximum open circuit voltage
<u>Wire Size</u>	<u>Max. Milliohms</u>							
16	5							
20	9							
Magnetic Permeability	2 μ maximum.	EIA-364-54						
Mechanical Durability, at Ambient Temperature	No deterioration which will adversely affect the connector after 500 cycles of mating and unmating. Connectors shall meet contact resistance, insulation resistance, shell-to-shell resistance, DWV, and coupling torque.	EIA-364-09						
Mechanical Shock	No discontinuity of greater than 1 microsecond, no cracking, breaking or loosening of parts, plug shall not become disengaged from receptacle. Connectors shall meet electrical requirements after shock test.	EIA-364-27 Condition D 3 shocks X 3 axes X 2 directions = 18 shocks 2941 m/s ² (300 g's), 3 ms, half-sine						
Operating Temperature	-65°C to +200°C Filter Connectors -55°C to +125°C							
Outgassing	Connectors, when specially processed for outgassing control, shall not exceed 1.0% Total Mass Loss (TML) and 0.1% Collected Volatile Condensable Material (CVCM)	ASTM E 595						
Ozone Exposure	No evidence of degradation due to ozone exposure that will adversely affect performance	EIA-364-14 Wired, mated connectors						
Resistance to Indirect Lightning Strike	No damage or degradation to material or finish that would affect subsequent use, no damage or hardening of elastomeric materials that adversely affects sealing effectiveness. Connector must meet coupling torque, DWV and IR and shell-to-shell conductivity. Applicable to connectors with conductive plating finishes.	EIA/ECA-364-75 Table XII, group 14 10,000 Amps peak current Test details per MIL-DTL-38999 Para. 4.5.47						
Shell-To-Shell Conductivity	Finish Code ME 1 millivolt drop maximum Finish Code NF, MT 2.5 millivolt drop maximum Finish Code ZR 10 millivolt drop maximum Finish Code Z1 50 millivolt drop maximum	EIA-364-83 Unwired connectors						
Socket Contact Engagement and Separation Force	Contact engagement and separation forces shall meet the requirements of SAE AS39029 Table 9	SAE AS39029						
Thermal Shock	No mechanical damage or loosening of parts. Following thermal shock, connector shall meet contact resistance, DWV, insulation resistance and shell-to-shell resistance requirements.	EIA-364-32 Test Condition VI 5 cycles consisting of -65° C 30 minutes, +25° C 5 minutes max., +200° C 30 minutes, +25° C 5 minutes max.						
Vibration, Random, at Ambient Temperature	No discontinuity of greater than 1 microseconds, no cracking, breaking or loosening of parts, plug shall not become disengaged from receptacle. Connectors shall meet electrical requirements after vibration test.	MIL-DTL-38999 Para. 4.5.23.2.4						
Vibration, Random, at Elevated Temperature	No discontinuity of greater than 1 microseconds, no cracking, breaking or loosening of parts, plug shall not become disengaged from receptacle. Connectors shall meet electrical requirements after vibration test.	EIA-364-28 Test Condition VI Letter "J" 50- 2,000 Hz 43.92 g rms 200° C						
Vibration, Sine	No discontinuity of greater than 1 microseconds, no cracking, breaking or loosening of parts, plug shall not become disengaged from receptacle. Connectors shall meet electrical requirements after vibration test.	MIL-DTL-38999L Para. 4.5.23.2.1						
Water Immersion	No evidence of water penetration into mated connectors.	MIL-STD-810F Method 512.4, 1 meter immersion for 1 hour						
Water Pressure	No evidence of water penetration into mated connectors or backshell interface. ≥ 100 MΩ insulation resistance.	MIL-DTL- 28840 Paragraph 4.1.15. 6 feet immersion in tap water, 48 hours						
Outgassing	Special Bakeout Required 1.0% Total Mass Loss (TML) 0.1% Collected Volatile Condensable Material (CVCM)	ASTM E595						



Series 970 Connectors and Accessories Technical Reference Material and Finish Options

B

MATERIAL AND FINISH OPTIONS FOR POWERTRIP CONNECTORS AND ACCESSORIES

Powertrip connector shells are made of aluminum alloy or stainless steel. These shells are plated to improve corrosion resistance and conductivity. Electroless nickel plating is used for instrumentation, avionics and space applications where corrosion protection is not critical. Cadmium plating provides superior corrosion protection, but the United States Department of Defence (DOD) mandated the elimination of cadmium from DOD weapons systems because of toxicity concerns. The European Union has also restricted the use of cadmium on electronics equipment (RoHS). The top choices for cadmium replacement are Nickel-PTFE (MT) and Zinc-Nickel (ZR). In this catalog you will find four standard platings for aluminum shells: *Electroless Nickel*, *Nickel-PTFE*, *Black Zinc-Nickel*, and *Olive-Drab Cadmium*. A fifth option is *Passivated Stainless Steel* for extremely hostile environments. Glenair also offers dozens of optional material and finish options, typically with no minimum orders or lengthy lead times. A selection of these optional finishes is shown in the table below.

STANDARD MATERIAL & FINISH SELECTION GUIDE

Property	Alum/ Nickel	Alum/ Nickel-PTFE	Alum/ Olive Drab Cadmium	Alum/ Black Zinc-Nickel	SST/ Passivate
Glenair Code	ME	MT	NF	ZR	Z1
Corrosion Resistance	Fair	Excellent	Excellent	Excellent	Excellent
Temperature Range	-65°C to +200°C	-65°C to +175°C	-65°C to +175°C	-65°C to +175°C	-65°C to +200°C
Salt Spray Hours	96	1000 ⁽¹⁾	1000 ⁽¹⁾	1000 ⁽¹⁾	2000
Conductivity	Excellent	Excellent	Good	Good	Fair
Relative Cost	\$\$	\$\$\$	\$\$	\$\$\$	\$\$\$\$
RoHS Compliant ⁽²⁾	Yes	Yes	No	Yes	Yes

(1) Dynamic salt spray testing reduces 1000 hours to 500 hours. Dynamic testing includes 500 connector mating cycles.

(2) Does not contain cadmium or hexavalent chromium. Meets EU requirements.

The following table contains optional plating codes not shown in the ordering information. If one of these optional finishes is preferred over the above standard finishes, substitute the appropriate code in the part number.

OPTIONAL MATERIAL AND FINISH CODES

Code	Material	Finish	Finish Specification	Hrs. Salt Spray	Electrical Conductivity	Operating Temp. Range	RoHS Compliance ⁽²⁾
AB	Marine Bronze	Unplated		1000	Conductive	-65 to +200°C	✓
AL	Aluminum	AlumiPlate	MIL-DTL-83488	1000 ⁽¹⁾	Conductive	-65 to +175°C	✓
C	Aluminum	Anodize, Black	AMS-A-8625	48	Non-Conductive	-65 to +175°C	✓
E	Aluminum	Chem Film	MIL-DTL-5541	168	Conductive	-65 to +175°C	
G2	Aluminum	Anodize, Hardcoat	AMS-A-8625	336	Non-Conductive	-65 to +200°C	✓
JF	Aluminum	Cadmium, Gold	SAE-AMS-QQ-P-416	1000 ⁽¹⁾	Conductive	-65 to +175°C	
M	Aluminum	Electroless Nickel	AMS-C-26074	48	Conductive	-65 to +200°C	✓
NC	Aluminum	Zinc-Cobalt, Olive Drab	ASTM B 840	350	Conductive	-65 to +175°C	
P	Stainless Steel	Electrodeposited Nickel	SAE-AMS-QQ-N-290	500	Conductive	-65 to +200°C	✓
Z1	Stainless Steel	Passivate	SAE-AMS-QQ-P-35	1000	Conductive	-65 to +200°C	✓
Z2	Aluminum	Gold	MIL-DTL-45204	48	Conductive	-65 to +200°C	✓
ZL	Stainless Steel	Electrodeposited Nickel	SAE-AMS-QQ-N-290	1000 ⁽¹⁾	Conductive	-65 to +200°C	✓
ZM	Stainless Steel	Electroless Nickel	AMS-C-26074	1000	Conductive	-65 to +200°C	✓
ZMT	Stainless Steel	Nickel-PTFE	SAE AMS 2454	1000 ⁽¹⁾	Conductive	-65 to +200°C	✓
ZN	Aluminum	Zinc-Nickel, Olive Drab	ASTM B841	500	Conductive	-65 to +175°C	
ZNU	Aluminum	Zinc-Nickel, Black	ASTM B841	500	Conductive	-65 to +175°C	
ZU	Stainless Steel	Cadmium, Black	SAE-AMS-QQ-P-416	1000	Conductive	-65 to +175°C	
ZW	Stainless Steel	Cadmium, Olive Drab	SAE-AMS-QQ-P-416	2000	Conductive	-65 to +175°C	

(1) Dynamic salt spray testing reduces 1000 hours to 500 hours. Dynamic testing includes 500 connector mating cycles.

(2) Does not contain cadmium or hexavalent chromium. Meets EU requirements.



POWERTRIP™ CONNECTORS FOR SPACE FLIGHT

OUTGASSING

- **Standard connectors must be baked out to meet outgassing requirements.**
- **Modification codes are a convenient way to specify special outgassing bakeout.**

Space flight equipment requires low-outgassing components in order to prevent degradation to optics and other sensitive instruments. The space industry has adopted a standardized test procedure, ASTM E595, to evaluate outgassing properties. In the ASTM test, material samples are heated to 125° C at a vacuum of 5 X 10⁻⁵ torr for 24 hours. The test sample is then weighed to calculate the Total Mass Loss (TML), which may not exceed 1.0% of the total initial mass. A collector plate is used to determine the Collected Volatile Condensable Material (CVCM), which may not exceed 0.1% of the total original specimen mass. Powertrip™ connectors contain nonmetallic materials such as rubber, plastic, adhesives and potting compounds which can give off gasses when subjected to a vacuum or high heat. Unless the connector is specially processed, the TML and CVCM can exceed allowable limits. Glenair is able to offer two bakeout processes which assure all materials comply with ASTM E595: an 8 hour oven bakeout at 400° F or a 24 hour thermal vacuum outgassing at 125° C. The table below shows suffix codes which specify outgassing processing.

CONNECTOR MATERIAL AND FINISH OPTIONS

- **Cadmium and silver plating are prohibited in space.**
- **Specify electroless nickel plating on connector shells and gold plating on contacts.**

Some types of metals are prohibited for space flight. "Cadmium, zinc, chemically coated cadmium or zinc, or silver shall not be used as a connector or contact finish" (NASA EEE-INST-002 Instructions for EEE Parts Selection, Screening, Qualification, and Derating). NASA recommends electroless nickel or gold plating on connector shells and gold plating for contacts.

NASA SCREENING

- **"Mission critical" connectors for space flight should undergo rigorous 100% final inspection.**
- **Modification codes are available to invoke special screening.**

NASA recommends that connectors for space flight be specially screened. NASA EEE-INST-002 Instructions for EEE Parts Selection, Screening, Qualification, and Derating contains three levels of screening: level 1 for highest reliability, level 2 for high reliability and level 3 for standard reliability. Glenair suffix codes are available to invoke NASA screening. The table below shows these "Mod" codes which can also include outgassing processing.

NASA SCREENING LEVELS AND MODIFICATION CODES			
NASA Screening Level	Special Screening Only	Special Screening Plus Outgassing Processing	
		48 Hour Oven Bake 175° C.	Thermal Vacuum Outgassing 24 hrs. 125° C.
Level 1 Highest Reliability	Mod 429B	Mod 429J	Mod 429C
Level 2 High Reliability	Mod 429	Mod 429K	Mod 429A
Level 3 Standard Reliability	(Use standard part number)	Mod 186	Mod 186M



Series 970 PowerTrip™ Connectors and Accessories Cable Connectors 970-001 Plug with Accessory Thread

PLUG CONNECTORS



Series 970 PowerTrip™ plug connectors feature high current LouverBand contacts and rugged water resistant construction for the most demanding environments. Coupling threads are triple-start ACME type. EMI protected with ground spring and splined backshell interface. Anti-decoupling ratchet prevents de-mating under vibration. Standard contacts are silver plated high conductivity copper alloy, or choose gold-plated contacts for improved corrosion protection. Fluorosilicone rubber gaskets and grommets provide watertight sealing. Contacts are packaged with connector.

- EMI Protected
- High Current Contacts
- Splined Backshell Interface
- Ratchet Self-Locking

PRODUCT FACTS

2000 VAC Sea Level DWV Rating
-65°C to +200°C Operating Temperature
6 Feet Water Immersion, 48 Hours
65 dB min. Attenuation, up to 10GHz
500 Cycles Mating Durability
MIL-S 901 Grade A High-Impact Shock
43 g Random Vibration

HOW TO ORDER

SERIES	SHELL MATERIAL AND FINISH	SHELL SIZE - INSERT ARRANGEMENT						CONTACT TYPE AND PLATING	KEY POSITION
970-001 Plug Connector	ME Aluminum, Electroless Nickel Finish	Contact Arr.	Contact Size and Qty					P1 Pin Contacts, Silver Plating*	-1 Position 1
		#16	#12	#8	#4	#1/0			
	MT Aluminum, Nickel-PTFE Finish	18-2			2			P2 Pin Contacts, Gold Plating	-2 Position 2
		18-4		2	2				
		20-3			3				
		20-4			4				
	NF Aluminum, Olive Drab Cadmium	20-5		2	3			S1 Socket Contacts, Silver Plating*	-3 Position 3
		20-7	4		3				
		24-2				2			
		24-3				3			
	ZR Aluminum, Black Zinc-Nickel Finish	24-5			5			S2 Socket Contacts, Gold Plating	-4 Position 4
		24-6		4		2			
		24-A6		3		3			
		28-4				4			
	Z1 Passivated Stainless Steel	28-8		1	7			A Pin Connector, without Contacts	-5 Position 5
		28-9	5			4			
		28-15	15						
		32-2					2		
		32-3					3		
		32-4				2	2		
32-5					5				
32-6			3			3			
32-20	1	19							
36-4					4	B Socket Connector, without Contacts	-6 Position 6		
36-16	3		13						
40-5					5				
40-21			21						
Sample Part Number									
970-001	MT	18-2						P2	-1


* Size 12 and 16 contacts are gold-plated. Size 8, 4 and 1/0 are silver plated.

Series 970 PowerTrip™ Connectors and Accessories Cable Connectors


970-001 Plug with Accessory Thread



970-001 PLUG CONNECTOR



DIMENSIONS				
Shell Size	Ø A		B Mating Thread	C Accessory Thread
	In.	mm.		
18	1.485	37.72	1.125-0.1P-.3L-TS-2B	1.125-18 UNEF-2A
20	1.583	40.21	1.250-0.1P-.3L-TS-2B	1.250-18 UNEF-2A
24	1.875	47.63	1.500-0.1P-.3L-TS-2B	1.4375-18 UNEF-2A
28	2.186	55.52	1.750-0.1P-.3L-TS-2B	1.8125-16 UN-2A
32	2.420	61.47	2.000-0.1P-.3L-TS-2B	2.0625-16 UNS-2A
36	2.709	68.81	2.250-0.1P-.3L-TS-2B	2.250-16 UN-2A
40	2.980	75.69	2.500-0.1P-.3L-TS-2B	2.500-16 UN-2A



KEY POSITIONS				
Position	A°	B°	C°	D°
1	80	142	196	293
2	135	170	200	310
3	49	169	200	244
4	66	140	200	257
5	62	145	180	280
6	79	153	197	272



Series 970 PowerTrip™ Connectors and Accessories Cable Connectors

970-011 Cable Plug with Integral Banding Porch

970-011 CABLE PLUG



These connectors, often called “in-line”, “line” or “free-hanging” plugs, are installed on cables for cord-to-cord applications. These connectors feature high current LouverBand contacts. Coupling threads are triple-start ACME type. EMI protected with ground spring and integral shield banding porch. Standard contacts are silver plated high conductivity copper alloy, or choose gold-plated contacts for improved corrosion protection. Fluorosilicone rubber gaskets and grommets provide watertight sealing. Unassembled contacts are packaged with connector.

- EMI Protected
- High Current Contacts
- Integral Banding Porch
- Ratchet Self-Locking

PRODUCT FACTS

2000 VAC Sea Level DWV Rating
-65°C to +200°C Operating Temperature
6 Feet Water Immersion, 48 Hours
65 dB min. Attenuation, up to 10GHz
500 Cycles Mating Durability
MIL-S 901 Grade A High-Impact Shock
43 g Random Vibration

HOW TO ORDER


SERIES	SHELL MATL AND FINISH	SHELL SIZE - INSERT ARRANGEMENT					CONTACT TYPE AND PLATING	KEY POSITION
970-011 Cable Plug	ME Aluminum, Electroless Nickel Finish	Contact Arr.					P1 Pin Contacts, Silver Plating*	-1 Position 1
		#16	#12	#8	#4	#1/0		
	MT Aluminum, Nickel-PTFE Finish	18-2		2			P2 Pin Contacts, Gold Plating	-2 Position 2
		18-4	2	2				
	NF Aluminum, Olive Drab Cadmium	20-3		3			S1 Socket Contacts, Silver Plating*	-3 Position 3
		20-4		4				
	ZR Aluminum, Black Zinc-Nickel Finish	20-5	2	3			S2 Socket Contacts, Gold Plating	-4 Position 4
		20-7	4	3				
	Z1 Passivated Stainless Steel	24-2			2		A Pin Connector, without Contacts	-5 Position 5
		24-3			3			
	Z1 Passivated Stainless Steel	24-5		5			B Socket Connector, without Contacts	-6 Position 6
		24-6	4	2				
	Z1 Passivated Stainless Steel	24-A6	3	3			* Size 12 and 16 contacts are gold-plated. Size 8, 4 and 1/0 are silver plated.	
		28-4		4				
	Z1 Passivated Stainless Steel	28-8	1	7				
		28-9	5	4				
	Z1 Passivated Stainless Steel	32-2	15			2		
		32-3				3		
	Z1 Passivated Stainless Steel	32-4			2	2		
		32-5			5			
	Z1 Passivated Stainless Steel	32-6		3		3		
		32-20	1	19				
	Z1 Passivated Stainless Steel	36-4				4		
		36-16	3		13			
	Z1 Passivated Stainless Steel	40-5				5		
		40-21			21			
Sample Part Number								
970-011	MT	24-5					P1	-1

Series 970 PowerTrip™ Connectors and Accessories Cable Connectors


970-011 Cable Plug with Integral Banding Porch



970-011 CABLE PLUG



DIMENSIONS							
Shell Size	$\varnothing A$		B Mating Thread	$\varnothing C$		D	
	In.	mm		In.	mm.		
18	1.485	37.72	1.125-0.1P-0.3L-TS-2B	1.037	26.34	2.063	52.4
20	1.583	40.21	1.250-0.1P-0.3L-TS-2B	1.163	29.54	2.063	52.4
24	1.857	47.17	1.500-0.1P-0.3L-TS-2B	1.350	34.29	2.063	52.4
28	2.186	55.52	1.750-0.1P-0.3L-TS-2B	1.670	42.42	2.063	52.4
32	2.420	61.47	2.000-0.1P-0.3L-TS-2B	1.945	49.40	2.063	52.4
36	2.709	68.81	2.250-0.1P-0.3L-TS-2B	2.176	55.27	2.063	52.4



KEY POSITIONS				
Position	A°	B°	C°	D°
1	80	142	196	293
2	135	170	200	310
3	49	169	200	244
4	66	140	200	257
5	62	145	180	280
6	79	153	197	272



Series 970 PowerTrip™ Connectors and Accessories

Cable Connectors

970-005 Cable Receptacle

970-005 CABLE RECEPTACLES



These connectors, often called “in-line,” “line” or “free-hanging” receptacles, are installed on cables for cord-to-cord applications. These connectors feature high current LouverBand contacts. Coupling threads are triple-start ACME type. EMI protected with ground spring and splined backshell interface. Standard contacts are silver plated high conductivity copper alloy, or choose gold-plated contacts for improved corrosion protection. Fluorosilicone rubber gaskets and grommets provide watertight sealing. Unassembled contacts are packaged with connector.

- EMI Protected
- High Current Contacts
- Splined Backshell Interface

PRODUCT FACTS

2000 VAC Sea Level DWV Rating
-65°C to +200°C Operating Temperature
6 Feet Water Immersion, 48 Hours
65 dB min. Attenuation, up to 10GHz
500 Cycles Mating Durability
MIL-S 901 Grade A High-Impact Shock
43 g Random Vibration

HOW TO ORDER



SERIES	SHELL MATL AND FINISH	SHELL SIZE - INSERT ARRANGEMENT					CONTACT TYPE AND PLATING	KEY POSITION	
		Contact Arr.	Contact Size and Qty						
		#16	#12	#8	#4	#1/0			
970-005 Cable Receptacle	ME Aluminum, Electroless Nickel Finish			2			P1 Pin Contacts, Silver Plating*	-1 Position 1	
		18-2		2					
		18-4	2	2					
	MT Aluminum, Nickel-PTFE Finish				3		P2 Pin Contacts, Gold Plating	-2 Position 2	
		20-3			3				
		20-4			4				
	NF Aluminum, Olive Drab Cadmium			2	3		S1 Socket Contacts, Silver Plating*	-3 Position 3	
		20-5		2	3				
		20-7	4		3				
	ZR Aluminum, Black Zinc-Nickel Finish					2	S2 Socket Contacts, Gold Plating	-4 Position 4	
		24-2				2			
		24-3				3			
	Z1 Passivated Stainless Steel				5		A Pin Connector, without Contacts	-5 Position 5	
		24-5			5				
		24-6	4		2				
	970-005 Cable Receptacle	MT Aluminum, Nickel-PTFE Finish	24-A6	3		3		B Socket Connector, without Contacts	-6 Position 6
			28-4				4		
			28-8		1	7			
			28-9	5			4		
			32-2	15					
			32-3						
32-4						2	2		
32-5						5			
32-6				3			3		
32-20			1	19					
36-4					4				
36-16	3		13						
40-5					5				
40-21			21						
Sample Part Number									
970-005	MT		24-5				P1	-1	

* Size 12 and 16 contacts are gold-plated. Size 8, 4 and 1/0 are silver plated.

Series 970 PowerTrip™ Connectors and Accessories
Cable Connectors
970-005 Cable Receptacle



970-005 CABLE RECEPTACLE CONNECTOR



KEY POSITIONS				
Position	A°	B°	C°	D°
1	80	142	196	293
2	135	170	200	310
3	49	169	200	244
4	66	140	200	257
5	62	145	180	280
6	79	153	197	272




DIMENSIONS						
Shell Size	A Mating Thread	B Accessory Thd	C		D	
			In. ±.010	mm. ±0.25	In. ±.005	mm. ±0.13
18	1.125-.1P-.3L-TS-2A	1.125-18 UNEF-2A	1.328	33.73	1.138	28.91
20	1.250-.1P-.3L-TS-2A	1.250-18 UNEF-2A	1.515	38.48	1.325	33.66
24	1.500-.1P-.3L-TS-2A	1.4375-18 UNEF-2A	1.703	43.26	1.513	38.43
28	1.750-.1P-.3L-TS-2A	1.8125-16 UN-2A	2.078	52.02	1.888	47.96
32	2.000-.1P-.3L-TS-2A	2.0625-16 UNS-2A	2.265	57.53	2.075	52.71
36	2.250-.1P-.3L-TS-2A	2.250-16 UN-2A	2.515	63.89	2.325	55.06
40	2.500-.1P-.3L-TS-2A	2.500-16 UN-2A	2.765	70.23	2.575	65.41



Series 970 PowerTrip™ Connectors and Accessories Cable Connectors TurboFlex Cordsets

TURBOFLEX CORDSETS



PRODUCT FACTS

Conductors:

- Annealed stranded copper, nickel or silver coated
- High strandcount construction for excellent flexibility
- 16 through 1/0 AWG

Insulation:

- Duraelectric™ rubber
- 2000 volt rating

Cable jacket:

- Duraelectric™ rubber
- 2000 volt rating
- -65° to +260°C

Overmold Compound:

- Duraelectric™ rubber
- 2000 volt rating

Features:

- Excellent cold temperature flexibility
- 2000 volt rating
- Good abrasion resistance
- Excellent resistance to fuels and solvents
- Halogen free
- Flame retardant
- Water resistant
- Fugus resistant
- Excellent resistance to sunlight (UV) and ozone
- Fully shielded for EMI/RFI protection

Save cost and reduce leadtimes with Glenair-made Powertrip cordsets. Ultra-flexible overmolded power cords feature Glenair's high performance **Duraelectric™** rubber. Originally developed for US Navy conduit applications, flame retardant **Duraelectric™** elastomer has excellent cold temperature flexibility and outstanding resistance to solar radiation, solvents and fuels. Low smoke, zero halogen (LSZH) material. Glenair TurboFlex wires feature high strandcount copper and extruded **Duraelectric™** insulation. Outer jacket and overmold are **Duraelectric™** material.

Duraelectric™ Test Data and Specifications

Temperature Rating: -60°C to 260°C (with excursions to 290°C) Per MIL-PRF-24758A.

Halogen free per IEC 60614-1. Less than 5mg of HCl per 1 gram of product used.

Accelerated weathering (solar) per IEC 60068-2-5; 56 days exposure (equivalent to 50 years in the sun.)

Flame resistant per IEC 60614-1; material does not sustain combustion when the source of flame is removed.

Low smoke index per NES 711 (11.75); minimum standard is 25. Tested level is 11.75.

Smoke density class F1 per NF F 16-101 in accordance with DIN EN 60695-2-11:2001.

Toxicity index per NES 713 (1.9); minimum standard is 5. Tested level is 1.9.

Oxygen limiting index: 45.1 per EN ISO 4589-2:1999; minimum is 28.

12 second vertical burn: (pass) per 14CFR part 25.853 (a) AMDT25-116 APP F part 1 (a) (1) (ii)

Fluids per MIL-STD-810F, method 504

Fuel	MIL-T-83133: JPG
Hydraulic fluid	MIL-H-5606: Royco 756
Lubricating oil	MOL-L-23699: Royco -500
Cleaner	MIL-C-85570: calla -855
Solvent	Isopropyl Alcohol: TT-I-735
De-icer	AMS-1432: E36 runway de-icer
Coolant	MIL-C-87252: Coolanol 25R
Fire extinguishing foam	Amerex AFFF

ASTME E 595 vacuum outgassing—post bake results: TML .06%, CVCM .006%, WVR .02%

Fungus resistance testing (rating of 0) per MIL-STD-810F, method 508.5

ASTM D624 DIE B tear test: 150 KN/M

HOW TO ORDER

Please consult the Glenair factory or your local Glenair sales office

Series 970 PowerTrip™ Connectors and Accessories
Receptacle Connectors
970-003 Square Flange Receptacle



970-003 REAR PANEL MOUNT, SQUARE FLANGE RECEPTACLE



Series 970 PowerTrip™ extreme environment receptacle connectors are intended for high current applications where size 8 AWG to size 1/0 AWG wires are used. These connectors feature high current LouverBand contacts. Coupling threads are triple-start ACME type. EMI protected with ground spring on mating plug and splined backshell interface. Standard contacts are silver plated high conductivity copper alloy, or choose gold-plated contacts for improved corrosion protection. Fluorosilicone rubber gaskets and grommet provide watertight sealing. Contacts are packaged with connector.

- EMI Protected
- High Current Contacts
- Submersible
- Harsh Environment

PRODUCT FACTS
2000 VAC Sea Level DWV Rating
-65°C to +200°C Operating Temperature
6 Feet Water Immersion, 48 Hours
65 dB min. Attenuation, up to 10GHz
500 Cycles Mating Durability
MIL-S 901 Grade A High-Impact Shock
43 g Random Vibration

HOW TO ORDER

SERIES	SHELL MATL AND FINISH	SHELL SIZE - INSERT ARRANGEMENT	CONTACT TYPE AND PLATING	MOUNTING HOLE OPTION	KEY POSITION				
970-003 Square Flange Panel Mount Receptacle with Crimp Contacts	ME Aluminum, Electroless Nickel Finish	Contact Arr.		Contact Size and Qty		P1 Pin Contacts, Silver Plating*	N Thru-Hole	-1 Position 1	
		#16	#12	#8	#4				#1/0
		18-2		2					
		18-4	2	2					
		20-3		3					
		20-4		4					
	MT Aluminum, Nickel-PTFE Finish	20-5	2	3			P2 Pin Contacts, Gold Plating	T Clinch Nuts Installed in Mounting Holes for Back Panel Mounting.	-2 Position 2
		20-7	4	3					
		24-2			2				
		24-3			3				
		24-5		5					
		24-6		4	2				
	NF Aluminum, Olive Drab Cadmium	24-A6	3	3			S1 Socket Contacts, Silver Plating*	-3 Position 3	
		28-4		4					
		28-8		1	7				
		28-9	5		4				
		28-15	15						
		32-2				2			
	ZR Aluminum, Black Zinc-Nickel Finish	32-3				3	S2 Socket Contacts, Gold Plating	-4 Position 4	
		32-4			2	2			
		32-5				5			
32-6			3		3				
32-20		1	19						
36-4					4				
36-16		3		13					
40-5					5				
40-21				21					
Z1 Passivated Stainless Steel						A Pin Connector, without Contacts	-5 Position 5		
						B Socket Connector, without Contacts	-6 Position 6		
Sample Part Number									
970-003	MT	24-5		P1	N	-1			






Series 970 PowerTrip™ Connectors and Accessories

Receptacle Connectors

970-003 Square Flange Receptacle


970-003 REAR PANEL MOUNT, SQUARE FLANGE RECEPTACLE



D

DIMENSIONS

Shell Size	A		B	C	D		Ø E		E	Ø F	
	In.	mm.	Mating Thread	Accessory Thd	In.	mm.	In.	mm.	Clinch Nut Thd	In.	mm.
18	1.383	35.13	1.125-.1P-.3L-TS-2A	1.125-18 UNEF-2A	1.015	25.78	.146	3.71	6-32 UNC-2B	1.187	30.15
20	1.508	38.30	1.250-.1P-.3L-TS-2A	1.250-18 UNEF-2A	1.140	28.96	.146	3.71	6-32 UNC-2B	1.374	34.90
24	1.718	43.64	1.500-.1P-.3L-TS-2A	1.4375-18 UNEF-2A	1.281	32.54	.146	3.71	6-32 UNC-2B	1.562	39.67
28	2.138	54.31	1.750-.1P-.3L-TS-2A	1.8125-16 UN-2A	1.568	39.83	.170	4.32	8-32 UNC-2B	1.835	46.61
32	2.328	59.13	2.000-.1P-.3L-TS-2A	2.0625-16 UNS-2A	1.734	44.04	.170	4.32	8-32 UNC-2B	2.093	53.16
36	2.578	65.48	2.250-.1P-.3L-TS-2A	2.250-16 UN-2A	1.984	50.39	.170	4.32	8-32 UNC-2B	2.302	58.47
40	2.828	71.83	2.500-.1P-.3L-TS-2A	2.500-16 UN-2A	2.234	56.74	.170	4.32	8-32 UNC-2B	2.562	65.07




KEY POSITIONS

Position	A°	B°	C°	D°
1	80	142	196	293
2	135	170	200	310
3	49	169	200	244
4	66	140	200	257
5	62	145	180	280
6	79	153	197	272

Series 970 PowerTrip™ Connectors and Accessories
Receptacle Connectors
970-009 Low Profile Square Flange Receptacle



970-009 LOW PROFILE, REAR PANEL MOUNT, SQUARE FLANGE RECEPTACLE



970-009 receptacles have a shorter profile than standard square flange receptacles. This reduced protrusion behind the mounting panel results from removing the accessory threads, moving the mounting flange and replacing the grommet wire seal with a thinner wire separator. Series 970 PowerTrip™ extreme environment receptacle connectors are intended for high current applications where size 8 AWG to size 1/0 AWG wires are used. These connectors feature high current LouverBand contacts. Coupling threads are triple-start ACME type. EMI protected with ground spring and splined backshell interface. Standard contacts are silver plated high conductivity copper alloy, or choose gold-plated contacts for improved corrosion protection. Contacts are packaged with connector. Red stripe indicates full mating condition when the plug connector coupling ring fully covers the stripe.

970-009 connectors have a low profile wire separator instead of a thick watertight rear grommet. These connectors are splashproof but are not rated for water immersion or altitude immersion.

HOW TO ORDER


SERIES	SHELL MATL AND FINISH	SHELL SIZE - INSERT ARRANGEMENT						CONTACT TYPE AND PLATING	MOUNTING HOLE OPTION	KEY POSITION
970-009 Low Profile Square Flange Panel Mount Receptacle with Crimp Contacts	ME Aluminum, Electroless Nickel Finish	Contact Arr.						P1 Pin Contacts, Silver Plating*	N Thru-Hole	-1 Position 1
		Contact Size and Qty								
	MT Aluminum, Nickel-PTFE Finish	#16	#12	#8	#4	#1/0		P2 Pin Contacts, Gold Plating	T Clinch Nuts Installed in Mounting Holes for Back Panel Mounting.	-2 Position 2
		18-2		2						
		18-4	2	2						
		20-3		3						
		20-4		4						
		20-5		2	3					
		20-7	4	3						
		24-2				2				
		24-3				3				
		24-5			5					
	NF Aluminum, Olive Drab Cadmium	24-6		4		2		S1 Socket Contacts, Silver Plating*		-3 Position 3
		24-A6		3		3				
		28-4				4				
		28-8		1	7					
		28-9	5			4				
		28-15	15							
	ZR Aluminum, Black Zinc-Nickel Finish	32-2					2	S2 Socket Contacts, Gold Plating		-4 Position 4
		32-3					3			
32-4					2	2				
32-5						5				
32-6			3			3				
32-20		1	19							
36-4						4				
36-16		3		13						
Z1 Passivated Stainless Steel	40-5					5	A Pin Connector, without Contacts		-5 Position 5	
	40-21			21						
							B Socket Connector, without Contacts		-6 Position 6	
Sample Part Number										
970-009	MT	24-5						P1	N	-1






Series 970 PowerTrip™ Connectors and Accessories
Receptacle Connectors
970-009 Low Profile Square Flange Receptacle

970-009 LOW PROFILE, REAR PANEL MOUNT SQUARE FLANGE RECEPTACLE



D

DIMENSIONS												
Shell Size	A		B Mating Thread	C		D		Ø E		E Clinch Nut Thd	Ø F	
	In.	mm.		In.	mm.	In.	mm.	In.	mm.		In.	mm.
18	1.383	35.13	1.125-.1P-.3L-TS-2A	.972	24.69	1.015	25.78	.146	3.71	6-32 UNC-2B	1.187	30.15
20	1.508	38.30	1.250-.1P-.3L-TS-2A	1.116	28.35	1.140	28.96	.146	3.71	6-32 UNC-2B	1.374	34.90
24	1.718	43.64	1.500-.1P-.3L-TS-2A	1.300	33.02	1.281	32.54	.146	3.71	6-32 UNC-2B	1.562	39.67
28	2.138	54.31	1.750-.1P-.3L-TS-2A	1.604	40.74	1.568	39.83	.170	4.32	8-32 UNC-2B	1.835	46.61
32	2.328	59.13	2.000-.1P-.3L-TS-2A	1.875	47.63	1.734	44.04	.170	4.32	8-32 UNC-2B	2.093	53.16
36	2.578	65.48	2.250-.1P-.3L-TS-2A	2.093	53.16	1.984	50.39	.170	4.32	8-32 UNC-2B	2.302	58.47
40	2.828	71.83	2.500-.1P-.3L-TS-2A	2.310	58.67	2.234	56.74	.170	4.32	8-32 UNC-2B	2.562	65.07




KEY POSITIONS				
Position	A°	B°	C°	D°
1	80	142	196	293
2	135	170	200	310
3	49	169	200	244
4	66	140	200	257
5	62	145	180	280
6	79	153	197	272

Series 970 PowerTrip™ Connectors and Accessories
Receptacle Connectors
970-013 O-ring Sealed, Low Profile Square Flange Receptacle



Receptacle Connectors

970-013 REAR PANEL MOUNT SQUARE FLANGE RECEPTACLE



970-013 receptacles feature an O-ring for panel sealing. Low profile for reduced clearance inside equipment. Connector mounting flange is enlarged to include the O-ring. Series 970 PowerTrip™ extreme environment receptacle connectors are intended for high current applications where size 8 AWG to size 1/0 AWG wires are used. Contacts snap into connector and can be removed with a plastic tool. These connectors feature high current LouverBand contacts. Coupling threads are triple-start ACME type. EMI protected with ground spring and splined backshell interface. Standard contacts are silver plated high conductivity copper alloy, or choose gold-plated contacts for improved corrosion protection. Contacts are packaged with connector. Red stripe indicates full mating condition when the plug connector coupling ring fully covers the stripe.

970-013 connectors have a low profile wire separator instead of a thicker watertight rear grommet. These connectors are splashproof but are not rated for water immersion or altitude immersion.

HOW TO ORDER

SERIES	SHELL MATL AND FINISH	SHELL SIZE - INSERT ARRANGEMENT						CONTACT TYPE AND PLATING	MOUNTING HOLE OPTION	KEY POS.			
970-013 Low Profile Square Flange Panel Mount Receptacle with O-ring Panel Seal	ME Aluminum, Electroless Nickel Finish	Contact Arr.		Contact Size and Qty				P1 Pin Contacts, Silver Plating*	N Thru-Hole	-1 Position 1			
		#16	#12	#8	#4	#1/0							
		18-2		2									
		18-4	2	2									
		20-3			3								
		20-4			4								
		20-5		2	3								
		20-7	4		3								
		24-2				2							
		24-3				3							
	MT Aluminum, Nickel-PTFE Finish	NF Aluminum, Olive Drab Cadmium	ZR Aluminum, Black Zinc-Nickel Finish	Z1 Passivated Stainless Steel	Contact Arr.		Contact Size and Qty				P2 Pin Contacts, Gold Plating	T Clinch Nuts Installed in Mounting Holes for Back Panel Mounting.	-2 Position 2
					#16	#12	#8	#4	#1/0				
					24-5								
					24-6		4		2				
					24-A6		3		3				
					28-4			4					
					28-8		1	7					
					28-9	5			4				
					28-15	15							
					32-2				2				
32-3				3									
32-4				2									
32-5				5									
32-6		3		3									
32-20	1	19											
36-4				4									
36-16	3		13										
40-5				5									
40-21			21										
Sample Part Number													
970-013	MT	24-5						P1	N	-1			


D

* Size 12 and 16 contacts are gold-plated. Size 8, 4 and 1/0 are silver plated.




Series 970 PowerTrip™ Connectors and Accessories
Receptacle Connectors
970-013 Low Profile Square Flange Receptacle

970-013 REAR PANEL MOUNT SQUARE FLANGE RECEPTACLE



D

DIMENSIONS												
Shell Size	A		B Mating Thread	C		D		ø E		E Clinch Nut Thd	ø F	
	In.	mm.		In.	mm.	In.	mm.	In.	mm.		In.	mm.
18	1.591	40.41	1.125-.1P-.3L-TS-2A	.972	24.69	1.275	32.39	.146	3.71	6-32 UNC-2B	1.187	30.15
20	1.779	45.19	1.250-.1P-.3L-TS-2A	1.116	28.35	1.408	35.76	.146	3.71	6-32 UNC-2B	1.374	34.90
24	2.029	51.54	1.500-.1P-.3L-TS-2A	1.300	33.02	1.585	40.26	.146	3.71	6-32 UNC-2B	1.562	39.67
28	2.404	61.06	1.750-.1P-.3L-TS-2A	1.604	40.74	1.905	48.39	.170	4.32	8-32 UNC-2B	1.835	46.61
32	2.529	64.24	2.000-.1P-.3L-TS-2A	1.875	47.63	1.993	50.62	.170	4.32	8-32 UNC-2B	2.093	53.16
36	2.654	67.41	2.250-.1P-.3L-TS-2A	2.093	53.16	2.081	52.86	.170	4.32	8-32 UNC-2B	2.302	58.47
40	3.029	76.94	2.500-.1P-.3L-TS-2A	2.310	58.67	2.347	59.61	.170	4.32	8-32 UNC-2B	2.562	65.07




KEY POSITIONS				
Position	A°	B°	C°	C°
1	80	142	196	293
2	135	170	200	310
3	49	169	200	244
4	66	140	200	257
5	62	145	180	280
6	79	153	197	272

Series 970 PowerTrip™ Connectors and Accessories
Receptacle Connectors
970-008 Square Flange PC Tail Receptacle



970-008 REAR PANEL MOUNT SQUARE FLANGE RECEPTACLE WITH SIZE #8 PC TAILS

Series 970 PowerTrip™ receptacles with size #8 PC tail contacts for direct termination to circuit boards. Contacts are factory-installed and are non-removable. These connectors feature high current LouverBand contacts. Coupling threads are triple-start ACME type. EMI protected with ground spring and splined backshell interface. Standard contacts are silver plated high conductivity copper alloy, or choose gold-plated contacts for improved corrosion protection. Fluorosilicone rubber gaskets and epoxy potting provide watertight sealing. Connector shell has integral standoffs.



- EMI Protected
- High Current Contacts
- PC Board terminals
- Harsh Environment

PRODUCT FACTS
2000 VAC Sea Level DWV Rating
-65°C to +200°C Operating Temperature
6 Feet Water Immersion, 48 Hours
65 dB min. Attenuation, up to 10GHz
500 Cycles Mating Durability
MIL-S 901 Grade A High-Impact Shock
43 g Random Vibration


HOW TO ORDER

SERIES	SHELL MATL AND FINISH	SHELL SIZE - INSERT ARRANGEMENT	CONTACT TYPE AND PLATING	PC TAIL LENGTH	MOUNTING HOLE OPTION	KEY POS.
970-008 Low Profile Square Flange Panel Mount Receptacle with Printed Circuit Terminals	ME Aluminum, Electroless Nickel Finish	18-2 2 #8	P1 Pin Contacts, Silver Plating*	A .125 (3.18)	N Thru-Hole	-1 Position 1
	MT Aluminum, Nickel-PTFE Finish	18-4 2 #8, 2 #12	P2 Pin Contacts, Gold Plating	B .250 (6.35)	T Clinch Nuts Installed in Mounting Holes for Back Panel Mounting.	-2 Position 2
	NF Aluminum, Olive Drab Cadmium	20-3 3 #8	S1 Socket Contacts, Silver Plating*	C .375 (9.53)		-3 Position 3
	ZR Aluminum, Black Zinc-Nickel Finish	20-4 4 #8	S2 Socket Contacts, Gold Plating			-4 Position 4
	Z1 Passivated Stainless Steel	20-5 3 #8, 2 #12	* Size 12 and 16 contacts are gold-plated. Size 8, 4 and 1/0 are silver plated.			-5 Position 5
		20-7 3 #8, 4 #16				-6 Position 6
		24-5 5 #8				
Sample Part Number						
970-008	MT	24-5	P2	A	N	-1




Series 970 PowerTrip™ Connectors and Accessories
Receptacle Connectors
970-008 Square Flange PC Tail Receptacle

970-008 REAR PANEL MOUNT SQUARE FLANGE RECEPTACLE WITH SIZE #8 PC TAILS



DIMENSIONS

Shell Size	A		B Mating Thread	C		ø D	
	In.	mm.		In.	mm.	In.	mm.
18	1.383	35.13	1.125-.1P-.3L-TS-2A	1.015	25.78	1.187	30.15
20	1.508	38.30	1.250-.1P-.3L-TS-2A	1.140	28.96	1.374	34.90
24	1.718	43.64	1.500-.1P-.3L-TS-2A	1.281	32.54	1.562	39.67



KEY POSITIONS













Position	A°	B°	C°	D°
1	80	142	196	293
2	135	170	200	310
3	49	169	200	244
4	66	140	200	257
5	62	145	180	280
6	79	153	197	272

Series 970 PowerTrip™ Connectors and Accessories
Receptacle Connectors
970-008 Square Flange PC Tail Receptacle



Receptacle Connectors

970-008 PRINTED CIRCUIT BOARD PATTERNS










Contact Arrangement	Component Mounting Side of PCB	
 <p>18-2 2#8 Contacts</p>	 <p>18-2P Pin Connector</p>	 <p>18-2S Socket Connector</p>
 <p>18-4 2#8 Contacts, 2 #12 Contacts</p>	 <p>18-4P Pin Connector</p>	 <p>18-4S Socket Connector</p>
 <p>20-3 3#8 Contacts</p>	 <p>20-3P Pin Connector</p>	 <p>20-3S Socket Connector</p>
 <p>20-4 4#8 Contacts</p>	 <p>20-4P Pin Connector</p>	 <p>20-4S Socket Connector</p>

D



Series 970 PowerTrip™ Connectors and Accessories
Receptacle Connectors
970-008 Square Flange PC Tail Receptacle

970-008 PRINTED CIRCUIT BOARD PATTERNS

Contact Arrangement	Component Mounting Side of PCB	
 <p>20-5 3#8 Contacts, 2 #12 Contacts</p>	 <p style="text-align: center;">20-5P Pin Connector</p>	 <p style="text-align: center;">20-5S Socket Connector</p>
 <p>20-7 3#8 Contacts, 4 #16 Contacts</p>	 <p style="text-align: center;">20-7P Pin Connector</p>	 <p style="text-align: center;">20-7S Socket Connector</p>
 <p>24-5 5#8 Contacts</p>	 <p style="text-align: center;">24-5P Pin Connector</p>	 <p style="text-align: center;">24-5S Socket Connector</p>

D

Series 970 PowerTrip™ Connectors and Accessories
Receptacle Connectors
970-004 Jam-Nut Receptacle



970-004 REAR PANEL MOUNT JAM-NUT RECEPTACLE



Series 970 PowerTrip™ extreme environment receptacle connectors are intended for high current applications where size 8 AWG to size 1/0 AWG wires are used. These connectors feature high current LouverBand contacts. Coupling threads are triple-start ACME type. EMI protected with ground spring and splined backshell interface. Standard contacts are silver plated high conductivity copper alloy, or choose gold-plated contacts for improved corrosion protection. Fluorosilicone rubber gaskets and grommets provide watertight sealing. Contacts are packaged with connector.

- EMI Protected
- High Current Contacts
- Splined Backshell Interface
- Ratchet Self-Locking

PRODUCT FACTS	
2000 VAC Sea Level DWV Rating	
-65°C to +200°C Operating Temperature	
6 Feet Water Immersion, 48 Hours	
65 dB min. Attenuation, up to 10GHz	
500 Cycles Mating Durability	
MIL-S 901 Grade A High-Impact Shock	
43 g Random Vibration	

HOW TO ORDER

SERIES	SHELL MATL AND FINISH	SHELL SIZE - INSERT ARRANGEMENT					CONTACT TYPE AND PLATING		KEY POSITION
		Contact Arr.	Contact Size and Qty						
		#16	#12	#8	#4	#1/0			
970-004 Jam-nut Receptacle, for Rear Panel Mounting	ME Aluminum, Electroless Nickel Finish			2			P1 Pin Contacts, Silver Plating*	-1 Position 1	
	MT Aluminum, Nickel-PTFE Finish	18-2		2	2			P2 Pin Contacts, Gold Plating	-2 Position 2
		18-4		2	2			S1 Socket Contacts, Silver Plating*	-3 Position 3
		20-3			3				
		20-4			4				
		20-5		2	3				
		20-7	4		3				
	24-2				2				
	NF Aluminum, Olive Drab Cadmium	24-3				3		S2 Socket Contacts, Gold Plating	-4 Position 4
		24-5			5				
		24-6		4		2			
		24-A6		3		3			
		28-4				4			
		28-8		1	7				
	ZR Aluminum, Black Zinc-Nickel Finish	28-9	5			4		A Pin Connector, Supplied without Contacts	-5 Position 5
		28-15	15						
		32-2					2		
		32-3					3		
		32-4				2	2		
		32-5				5			
Z1 Passivated Stainless Steel	32-6		3			3	B Socket Connector, Supplied without Contacts	-6 Position 6	
	32-20	1	19						
	36-4					4			
	36-16	3		13					
	40-5					5			
	40-21			21					
Sample Part Number									
970-004	MT	24-5					P1	-1	






Series 970 PowerTrip™ Connectors and Accessories

Receptacle Connectors

970-004 Jam-Nut Receptacle

970-004 REAR PANEL MOUNT JAM-NUT RECEPTACLE



DIMENSIONS



Shell Size	A Mating Thd.	B Accessory Thd.	C Jam-nut Thd.	$\varnothing D$		E		F		G	
				In.	mm.	In.	mm.	In.	mm.	In.	mm.
18	1.125-.1P-.3L-TS-2A	1.125-18 UNEF-2A	1.250-18 UNEF-2A	1.733	44.02	1.639	41.63	1.438	36.53	1.212	30.78
20	1.250-.1P-.3L-TS-2A	1.250-18 UNEF-2A	1.4375-18 UNEF-2A	1.921	48.79	1.827	46.41	1.625	41.28	1.399	35.53
24	1.500-.1P-.3L-TS-2A	1.4375-18 UNEF-2A	1.625-18 UNEF-2A	2.108	53.54	2.014	51.16	1.822	46.28	1.587	40.31
28	1.750-.1P-.3L-TS-2A	1.8125-16 UN-2A	1.9375-16 UN-2A	2.425	61.60	2.327	59.11	2.188	55.58	1.899	48.23
32	2.000-.1P-.3L-TS-2A	2.0625-16 UNS-2A	2.125-16 UN-2A	2.607	66.24	2.513	63.83	2.375	60.33	2.084	52.93
36	2.250-.1P-.3L-TS-2A	2.250-16 UN-2A	2.375-16 UN-2A	2.857	72.57	2.763	70.18	2.625	66.68	2.323	59.00
40	2.500-.1P-.3L-TS-2A	2.500-16 UN-2A	2.625-16 UN-2A	3.107	78.92	3.013	76.53	2.875	73.03	2.548	64.72

KEY POSITIONS

Position	A°	B°	C°	D°
1	80	142	196	293
2	135	170	200	310
3	49	169	200	244
4	66	140	200	257
5	62	145	180	280
6	79	153	197	272

PANEL CUTOUT

Shell Size	Diameter		Flat	
	In.	mm.	In.	mm.
		-.000 +.010	-.00 +0.25	-.000 +.010
18	1.265	32.13	1.217	30.91
20	1.452	36.88	1.409	35.79
24	1.640	41.66	1.596	40.54
28	1.952	49.58	1.910	48.51
32	2.140	54.36	2.092	53.14
36	2.390	60.71	2.342	59.49
40	2.640	67.06	2.557	64.95



Series 970 PowerTrip™ Connectors and Accessories
Receptacle Connectors
970-010 Low Profile, Jam-Nut Receptacle



970-010 LOW PROFILE, REAR PANEL MOUNT JAM-NUT RECEPTACLE



970-010 receptacles have a shorter profile than standard jam-nut receptacles. This reduced protrusion behind the mounting panel results from removing the accessory threads, moving the mounting flange and replacing the grommet wire seal with a thinner wire separator. Series 970 PowerTrip™ extreme environment receptacle connectors are intended for high current applications where size 8 AWG to size 1/0 AWG wires are used. Contacts snap into connector through rear wire separator and can be removed with a plastic tool. These connectors feature high current LouverBand contacts. Coupling threads are triple-start ACME type. EMI protected with ground spring and splined backshell interface. Standard contacts are silver plated high conductivity copper alloy, or choose gold-plated contacts for improved corrosion protection. Contacts are packaged with connector. Red stripe indicates full mating condition

970-010 connectors have a low profile wire separator instead of a thick watertight rear grommet. These connectors are splashproof but are not rated for water immersion or altitude immersion.


HOW TO ORDER

SERIES	SHELL MATL AND FINISH	SHELL SIZE - INSERT ARRANGEMENT					CONTACT TYPE AND PLATING	KEY POSITION
		Contact Arr.	Contact Size and Qty					
970-010 Jam-nut Receptacle, for Rear Panel Mounting, Low Profile	ME Aluminum, Electroless Nickel Finish	#16	#12	#8	#4	#1/0	P1 Pin Contacts, Silver Plating*	-1 Position 1
		18-2		2				
		18-4	2	2				
		20-3		3				
		20-4		4				
	MT Aluminum, Nickel-PTFE Finish	20-5		2	3		P2 Pin Contacts, Gold Plating	-2 Position 2
		20-7	4		3			
		24-2				2		
		24-3				3		
		24-5			5			
	NF Aluminum, Olive Drab Cadmium	24-6		4		2	S1 Socket Contacts, Silver Plating*	-3 Position 3
		24-A6		3		3		
		28-4				4		
		28-8		1	7			
		28-9	5			4		
	ZR Aluminum, Black Zinc-Nickel Finish	28-15	15				S2 Socket Contacts, Gold Plating	-4 Position 4
		32-2				2		
		32-3				3		
		32-4				2		
		32-5				5		
32-6			3		3			
32-20		1	19					
36-4					4			
36-16		3		13				
40-5					5			
Z1 Passivated Stainless Steel	40-21			21		A Pin Connector, without Contacts	-5 Position 5	
						B Socket Connector, without Contacts	-6 Position 6	
Sample Part Number								
970-010	MT	24-5					P1	-1



Series 970 PowerTrip™ Connectors and Accessories
Receptacle Connectors
970-010 Low Profile Jam-Nut Receptacle

970-010 LOW PROFILE, REAR PANEL MOUNT JAM-NUT RECEPTACLE





D

DIMENSIONS										
Shell Size	A Mating Thd.	B Jam-nut Thd.	ø C		D		E		F	
			In.	mm.	In.	mm.	In.	mm.	In.	mm.
18	1.125-.1P-.3L-TS-2A	1.250-18 UNEF-2A	1.733	44.02	1.639	41.63	1.438	36.53	1.212	30.78
20	1.250-.1P-.3L-TS-2A	1.4375-18 UNEF-2A	1.921	48.79	1.827	46.41	1.625	41.28	1.399	35.53
24	1.500-.1P-.3L-TS-2A	1.625-18 UNEF-2A	2.108	53.54	2.014	51.16	1.822	46.28	1.587	40.31
28	1.750-.1P-.3L-TS-2A	1.9375-16 UN-2A	2.425	61.60	2.327	59.11	2.188	55.58	1.899	48.23
32	2.000-.1P-.3L-TS-2A	2.125-16 UN-2A	2.607	66.24	2.513	63.83	2.375	60.33	2.084	52.93
36	2.250-.1P-.3L-TS-2A	2.375-16 UN-2A	2.857	72.57	2.763	70.18	2.625	66.68	2.323	59.00
40	2.500-.1P-.3L-TS-2A	2.625-16 UN-2A	3.107	78.92	3.013	76.53	2.875	73.03	2.548	64.72

KEY POSITIONS				
Position	A°	B°	C°	D°
1	80	142	196	293
2	135	170	200	310
3	49	169	200	244
4	66	140	200	257
5	62	145	180	280
6	79	153	197	272

PANEL CUTOUT				
Shell Size	Diameter		Flat	
	In.	mm.	In.	mm.
		-.000	-.00	-.000
	+.010	+0.25	+.010	+0.25
18	1.265	32.13	1.217	30.91
20	1.452	36.88	1.409	35.79
24	1.640	41.66	1.596	40.54
28	1.952	49.58	1.910	48.51
32	2.140	54.36	2.092	53.14
36	2.390	60.71	2.342	59.49
40	2.640	67.06	2.557	64.95



Series 970 PowerTrip™ Connectors and Accessories

Bulkhead Feed-thru Connector

970-006



970-006 BULKHEAD FEED-THRU CONNECTOR



Series 970 PowerTrip™ jam-nut mount bulkhead feed-thru connectors have pin contacts on one side and socket contacts on the other side. Mount to bulkhead and attach mating plug connectors to both sides. Coupling threads are triple-start ACME type. Contacts are factory-installed and are non-removable. Standard contacts are silver plated high conductivity copper alloy for excellent conductivity, or choose gold-plated contacts for improved corrosion protection. Jam-nut mount available for panel thicknesses from 1/16 inch (1.58mm) up to 1.4 inches (35.56mm).

- High Current Contacts
- Harsh Environment

PRODUCT FACTS

2000 VAC Sea Level DWV Rating
-65°C to +200°C Operating Temperature
6 Feet Water Immersion, 48 Hours
65 dB min. Attenuation, up to 10GHz
500 Cycles Mating Durability
MIL-S 901 Grade A High-Impact Shock
43 g Random Vibration

HOW TO ORDER

SERIES	SHELL MATL AND FINISH	SHELL SIZE - INSERT ARRANGEMENT					CONTACT TYPE	CONTACT PLATING	PANEL THICKNESS	KEY POSITION		
		Cont. Arr.	Contact Size and Qty									
			#16	#12	#8	#4	#1/0					
970-006 Series 970 Bulkhead Feed-Thru Connector, with Jam-nut Mounting	ME Aluminum, Electroless Nickel Finish				2			P Pin Contacts on Jam-nut Side	1 Silver Plated Power Contacts (size 1/0, 4 and 8) and Gold Plated Signal Contacts	BLANK (Standard) .500 in max panel thickness	-1 Position 1	
		18-2			2							-2 Position 2
		18-4		2	2							
	MT Aluminum, Nickel-PTFE Finish				3			S Socket Contacts on Jam-nut Side	2 Gold Plated Contacts	B .950 max panel thickness	-3 Position 3	
		20-3			3							
		20-4			4							
		20-5		2	3							
	NF Aluminum, Olive Drab Cadmium		4		3			JAM NUT SIDE 	2 Gold Plated Contacts	C 1.400 max panel thickness (See Table III)	-4 Position 4	
		20-7	4		3							
		24-2				2						
		24-3				3						
		24-5			5							
	ZR Aluminum, Black Zinc-Nickel Finish			4		2		JAM NUT SIDE 	2 Gold Plated Contacts	C 1.400 max panel thickness (See Table III)	-5 Position 5	
		24-6		4		2						
		24-A6		3		3						
		28-4				4						
		28-8			1	7						
	Z1 Passivated Stainless Steel			5		4		JAM NUT SIDE 	2 Gold Plated Contacts	C 1.400 max panel thickness (See Table III)	-6 Position 6	
		28-9		5		4						
		28-15		15								
32-2						2						
32-3						3						
32-4					2	2						
32-5					5							
32-6			3			3						
32-20		1	19									
36-4						4						
36-16	3		13									
40-5					5							
40-21			21									
Sample Part Number												
970-006	MT		24-5				P	1		-1		




Series 970 PowerTrip™ Connectors and Accessories

Bulkhead Feed-thru Connector

970-006


970-006 HERMETIC BULKHEAD FEED-THRU CONNECTOR



DIMENSIONS										
Shell Size	A Mating Thd.	B Jam-nut Thd.	Ø C		D		E		F	
			In.	mm.	In.	mm.	In.	mm.	In.	mm.
18	1.125-.1P-.3L-TS-2A	1.250-18 UNEF-2A	1.733	44.02	1.639	41.63	1.438	36.53	1.212	30.78
20	1.250-.1P-.3L-TS-2A	1.4375-18 UNEF-2A	1.921	48.79	1.827	46.41	1.625	41.28	1.399	35.53
24	1.500-.1P-.3L-TS-2A	1.625-18 UNEF-2A	2.108	53.54	2.014	51.16	1.822	46.28	1.587	40.31
28	1.750-.1P-.3L-TS-2A	1.9375-16 UN-2A	2.425	61.60	2.327	59.11	2.188	55.58	1.899	48.23
32	2.000-.1P-.3L-TS-2A	2.125-16 UN-2A	2.607	66.24	2.513	63.86	2.375	60.33	2.084	53.01
36	2.250-.1P-.3L-TS-2A	2.375-16 UN-2A	2.857	72.57	2.763	70.18	2.625	66.68	2.323	59.00
40	2.500-.1P-.3L-TS-2A	2.625-16 UN-2A	3.107	78.92	3.013	76.53	2.875	73.03	2.548	64.72


D

KEY POSITIONS				
Position	A°	B°	C°	D°
1	80	142	196	293
2	135	170	200	310
3	49	169	200	244
4	66	140	200	257
5	62	145	180	280
6	79	153	197	272



PANEL CUTOUT				
Shell Size	Diameter		Flat	
	In.	mm.	In.	mm.
18	+0.010 -0.000	+0.25 -0.00	+0.010 -0.000	+0.25 -0.00
20	1.265	32.13	1.217	30.91
24	1.452	36.88	1.409	35.79
28	1.640	41.66	1.596	40.54
32	1.952	49.58	1.910	48.51
36	2.140	54.36	2.092	53.14
40	2.390	60.71	2.342	59.49
40	2.640	67.06	2.557	64.95

TABLE III: PANEL THICKNESS						
Panel Option	J Max		K		L Max	
	In.	mm.	In.	mm.	In.	mm.
Blank (std.)	.500	12.70	1.328/1.298	33.73/32.97	2.260	57.40
B	.950	24.13	1.801/1.771	45.75/44.98	2.733	69.42
C	1.400	35.56	2.274/2.244	57.76/57.00	3.206	81.43



RECEPTACLE CONNECTORS

Series 970 PowerTrip™

Connectors and Accessories 970-031 Jam Nut Receptacle

MATERIAL AND FINISH

- Shell - See Table 1
- Insulator - High grade rigid dielectric / N/A
- Seal - Fluorosilicone / N/A
- Contacts - Copper alloy / see part number development

NOTES

- Contacts furnished loose with the connector
- For customer termination and installation.
- Spare contacts, hole plugs, crimp tools, and installation
- And extraction tools ordered separately per drawing 979-003.
- See 979-001 for product specifications.
- DWV: 2000 VAC without breakdown or flashover
- IR: 5000 MEGOHM minimum
- Current rating: See Max Current Table


MAX CURRENT RATING

Contact Size	Max Current
16	13
12	23
8	60
4	100
1/0	175
2/0	205

HOW TO ORDER

Sample Part Number	970-031	MT	32	-6	P	1	-1
Basic Number	970-031 Jam Nut Receptacle with Banding Porch						
Material/Finish	See Material/Finish Table						
Shell Size	See Dimensions Table						
Insert Arrangement	See Insert Arrangements Table						
Insert Designation	P = Pin Contact S = Socket Contact A = Pin Insulator Less Pin Contacts B = Socket Insulator Less Socket Contacts						
Contact Plating	1 = Silver (Size 8 , 4 , 0 , and 2/0 only) 2 = Gold (Applies to "P" and "S" insert designators only. Omit for "A" and "B" designators)						
Alternate Key Position	1, 2, 3, 4, 5, or 6 See Key Positions Table						

INSERT ARRANGEMENTS




RECEPTACLE CONNECTORS

Series 970 PowerTrip™




Connectors and Accessories

970-031 Jam Nut Receptacle



DIMENSIONS																
Shell Size	A Mating Thread	B Jam Nut Thread	Ø C		D		E		F		Ø G		Ø H MTG. Hole		J Hole Flat	
			In.	mm.	In.	mm.	In.	mm.	In.	mm.	In.	mm.	In.	mm.	In.	mm.
18	1.125-0.1P-0.3L-TS-2A	1.250-18UNEF-2A	1.733	44.02	1.639	41.63	1.438	36.53	1.212	30.78	1.037	26.34	1.265	32.13	1.217	30.91
20	1.250-0.1P-0.3L-TS-2A	1.4375-18UNEF-2A	1.921	48.79	1.827	46.41	1.625	41.28	1.399	35.53	1.163	29.54	1.452	36.88	1.409	35.79
24	1.500-0.1P-0.3L-TS-2A	1.625-18UNEF-2A	2.108	53.54	2.014	51.16	1.822	46.28	1.587	40.31	1.350	34.29	1.640	41.66	1.596	40.54
28	1.750-0.1P-0.3L-TS-2A	1.9375-16UN-2A	2.425	61.60	2.327	59.11	2.188	55.58	1.899	48.23	1.670	42.42	1.952	49.58	1.910	48.51
32	2.000-0.1P-0.3L-TS-2A	2.125-16UN-2A	2.607	66.22	2.513	63.83	2.375	60.33	2.084	52.93	1.945	49.40	2.140	54.36	2.092	53.14
36	2.250-0.1P-0.3L-TS-2A	2.375-16UN-2A	2.857	72.57	2.763	70.18	2.625	66.68	2.323	59.00	2.176	55.27	2.390	60.71	2.342	59.49
40	2.500-0.1P-0.3L-TS-2A	2.625-16UN-2A	3.107	78.92	3.013	76.53	2.875	73.03	2.548	64.72	2.350	59.69	2.640	67.06	2.557	64.95



KEY POSITIONS				
Position	A°	B°	C°	D°
1	80	142	196	293
2	135	170	200	310
3	49	169	200	244
4	66	140	200	257
5	62	145	180	280
6	79	153	197	272

RECEPTACLE CONNECTORS

Series 970 PowerTrip™

Connectors and Accessories

970-032 Square Flange Receptacle Crimp Rear Release

MATERIAL AND FINISH

- Shell - See Table 1
- Insulator - High grade rigid dielectric / N/A
- Seal - Fluorosilicone / N/A
- Contacts - Copper alloy / see part number development


NOTES

- Contacts furnished loose with the connector
- For customer termination and installation.
- Spare contacts, hole plugs, crimp tools, and installation
- And extraction tools ordered separately per drawing 979-003.
- See 979-001 for product specifications.
- DWV: 2000 VAC without breakdown or flashover
- IR: 5000 MEGOHM minimum
- Current rating: See table 3


MAX CURRENT RATING	
Contact Size	Max Current
16	13
12	23
8	60
4	100
1/0	175
2/0	205

HOW TO ORDER							
Sample Part Number	970-032	MT	32	-4	P	1	N -1
Basic Number	970-032 Square Flange Receptacle Crimp Rear Release Banding Porch						
Material/Finish	See Material/Finish Table						
Shell Size	See Dimensions Table						
Insert Arrangement	See Insert Arrangements Table						
Insert Designation	P = Pin Contact S = Socket Contact A = Pin Insulator Less Pin Contacts B = Socket Insulator Less Socket Contacts						
Contact Plating	1 = Silver (Size 8, 4, 0, And 2/0 Only) 2 = Gold (Applies to " P " and " S " insert designators only. Omit for " A " and " B " designators)						
Mounting Hole Option	N = Thru Hole T = Threaded - Clinch Nut, Self Locking Per NASM45938/7						
Alternate Key Position	1, 2, 3, 4, 5, or 6 See Key Positions Table						

INSERT ARRANGEMENTS




Connectors and Accessories
970-032 Square Flange Receptacle Crimp Rear Release



DIMENSIONS

Shell Size	A		B		C Mating Thread	ø D Thru		D Threaded	ø E		ø F MTG. Hole	
	In.	mm.	In.	mm.		In.	mm.		In.	mm.	In.	mm.
18	1.383	35.13	1.015	25.78	1.125-0.1P-0.3L-TS-2A	0.146	3.7	#6-32UNC-2B	1.037	26.34	1.187	30.15
20	1.508	38.30	1.140	28.96	1.250-0.1P-0.3L-TS-2A				1.163	29.54	1.374	34.90
24	1.718	43.64	1.281	32.54	1.500-0.1P-0.3L-TS-2A				1.350	34.29	1.562	39.67
28	2.138	54.31	1.568	39.83	1.750-0.1P-0.3L-TS-2A	0.170	4.3	#8-32UNC-2B	1.670	42.42	1.835	46.61
32	2.328	59.13	1.734	44.04	2.000-0.1P-0.3L-TS-2A				1.945	49.40	2.093	53.16
36	2.578	65.48	1.984	50.39	2.250-0.1P-0.3L-TS-2A				2.176	55.27	2.302	58.47
40	2.828	71.83	2.234	56.74	2.500-0.1P-0.3L-TS-2A				2.350	59.69	2.562	65.07



KEY POSITIONS

Position	A°	B°	C°	D°
1	80	142	196	293
2	135	170	200	310
3	49	169	200	244
4	66	140	200	257
5	62	145	180	280
6	79	153	197	272

RECEPTACLE CONNECTORS

Series 970 PowerTrip™

Connectors and Accessories

970-033 In-Line Receptacle Crimp Rear Release Banding Porch

MATERIAL AND FINISH

- Shell - See Table 1
- Insulator - High grade rigid dielectric / N/A
- Seal - Fluorosilicone / N/A
- Contacts - Copper alloy / see part number development


NOTES

- Contacts furnished loose with the connector
- For customer termination and installation. Spare contacts, hole plugs, crimp tools, and installation and extraction tools ordered separately per drawing 979-003.
- See 979-001 for product specifications.
- DWV: 2000 VAC without breakdown or flashover
- IR: 5000 MEGOHM minimum
- Current rating: See Max Current Rating Table

MAX CURRENT RATING	
Contact Size	Max Current
16	13
12	23
8	60
4	100
1/0	175
2/0	205

HOW TO ORDER							
Sample Part Number	970-033	MT	32	-4	P	1	-1
Basic Number	970-033 In-Line Receptacle Crimp Rear Release Banding Porch						
Material/Finish	See Table I						
Shell Size	See Dimensions Table						
Insert Arrangement	See Insert Arrangements Table						
Insert Designation	P = Pin Contact S = Socket Contact A = Pin Insulator Less Pin Contacts B = Socket Insulator Less Socket Contacts						
Contact Plating	1 = Silver (Size 8 , 4 , 0 , And 2/0 Only) 2 = Gold (Applies to "P" and "S" insert designators only. Omit for "A" and "B" designators)						
Key Position	1, 2, 3, 4, 5, or 6 See Key Positions Table						

INSERT ARRANGEMENTS





RECEPTACLE CONNECTORS

Series 970 PowerTrip™



Connectors and Accessories

970-033 In-Line Receptacle Crimp Rear Release Banding Porch



KEY POSITIONS				
Position	A°	B°	C°	D°
1	80	142	196	293
2	135	170	200	310
3	49	169	200	244
4	66	140	200	257
5	62	145	180	280
6	79	153	197	272


SCALE 1.500

DIMENSIONS							
Shell Size	Ø A ±.010		B ±.005		C Mating Thread	Ø D	
	In.	mm.	In.	mm.		In.	mm.
18	1.328	33.73	1.138	28.91	1.125-0.1P-0.3L-TS-2A	1.037	26.34
20	1.515	38.48	1.325	33.66	1.250-0.1P-0.3L-TS-2A	1.163	29.54
24	1.703	43.26	1.513	38.43	1.500-0.1P-0.3L-TS-2A	1.350	34.29
28	2.078	52.02	1.888	47.96	1.750-0.1P-0.3L-TS-2A	1.670	42.42
32	2.265	57.53	2.075	52.71	2.000-0.1P-0.3L-TS-2A	1.945	49.40
36	2.515	63.89	2.325	58.94	2.250-0.1P-0.3L-TS-2A	2.176	55.27
40	2.765	70.23	2.575	65.41	2.500-0.1P-0.3L-TS-2A	2.390	60.71

Connectors and Accessories

809-532 Hex Jam Nut with Anti-Rotation Feature

HOW TO ORDER			
Sample Part Number	809-532	-M	25
Basic Number	809-532 Hex Jam Nut with Anti-Rotation Feature		
Material/Finish	ME = Electroless Nickel, Aluminum ZR = Zink Nickel, Black (Tri-Valent CR), Aluminum Z1 = Passivate, Stainless Steel ZL = Electrodeposited Nickel, Stainless Steel		
Shell Size	See Dimensions Table		




DIMENSIONS					
Shell Size	A Thread	ø B		ø C	
		In.	mm.	In.	mm.
18	1.250-18UNEF-2B	1.438	36.53	1.838	46.69
20	1.4375-18UNEF-2B	1.625	41.28	2.025	51.43
24	1.625-18UNEF-2B	1.822	46.28	2.225	56.52
28	1.9375-18UNEF-2B	2.188	55.58	2.585	65.66
32	2.125-18UNEF-2B	2.375	60.33	2.775	70.49
36	2.375-18UNEF-2B	2.625	66.68	3.150	80.01
40	2.625-18UNEF-2B	2.875	73.02	3.450	87.63

Series 970 PowerTrip™ Connectors and Accessories
 Receptacle Connectors
 970-012 Square Flange Mount, Solder Cup Hermetic



970-012 HERMETIC REAR PANEL MOUNT, SQUARE FLANGE RECEPTACLE



Series 970 PowerTrip™ hermetic receptacles feature 316L stainless steel shells and compression glass insulators. Solder cup contacts are nickel-iron alloy and are non-removable. Coupling threads are triple-start ACME type. Contacts are silver plated high conductivity copper alloy, or choose gold-plated contacts. Fluorosilicone rubber face seal on pin connector. Stainless steel shells are passivated, or choose nickel plating for improved shell-to-shell conductivity and EMI protection. Hermeticity is 1×10^{-7} cc/sec maximum helium leak rate with one atmosphere pressure differential.

- **Compression Glass Seal**
- **1×10^{-7} cc/sec He leak rate**
- **Both Pin and Socket Versions**
- **Stainless Steel Shell**

PRODUCT FACTS
2000 VAC Sea Level DWV Rating
-65°C to +200°C Operating Temperature
6 Feet Water Immersion, 48 Hours
65 dB min. Attenuation, up to 10GHz
500 Cycles Mating Durability
MIL-S 901 Grade A High-Impact Shock
43 g Random Vibration


HOW TO ORDER

SERIES	SHELL MATL AND FINISH	SHELL SIZE - INSERT ARRANGEMENT	CONTACT TYPE AND PLATING	MOUNTING HOLE OPTION	KEY POSITION					
970-012 Hermetic Square Flange Panel Mount Receptacle If Required, uses Flange Gasket 930-014-** (Not Included)	Z1 Passivated Stainless Steel	Contact Arr.	Contact Size and Qty					P1 Pin Contacts, Silver Plating	N Thru-Hole	-1 Position 1
		#16	#12	#8	#4	#1/0				
		18-2		2						
		18-4	2	2						
		20-3		3						
		20-4		4						
		20-5	2	3						
		20-7	4	3						
		24-2			2					
		24-3			3					
	24-5		5							
	24-6	4	2							
	24-A6	3	3							
	28-4		4							
	28-8	1	7							
	28-9	5		4						
	28-15	15								
	32-2				2					
	32-3				3					
	32-4			2	2					
32-5			5							
32-6	3			3						
32-20	1	19								
36-4				4						
36-16	3		13							
40-5				5						
40-21			21							
Sample Part Number										
970-012	Z1	20-4	P1	N	-1					




Series 970 PowerTrip™ Connectors and Accessories
Receptacle Connectors
970-012 Solder Cup Hermetic

970-012 HERMETIC REAR PANEL MOUNT, SQUARE FLANGE RECEPTACLE



DIMENSIONS											
Shell Size	A		B Mating Thread	C		D		Ø E Thru Hole		Ø F	
	In.	mm.		In.	mm.	In.	mm.	In.	mm.	In.	mm.
18	1.383	35.13	1.125-.1P-.3L-TS-2A	.972	24.69	1.015	25.78	.146	3.71	1.187	30.15
20	1.508	38.30	1.250-.1P-.3L-TS-2A	1.116	28.35	1.140	28.96	.146	3.71	1.374	34.90
24	1.718	43.64	1.500-.1P-.3L-TS-2A	1.300	33.02	1.281	32.54	.146	3.71	1.562	39.67
28	2.138	54.31	1.750-.1P-.3L-TS-2A	1.604	40.74	1.568	39.83	.170	4.32	1.874	47.60
32	2.328	59.13	2.000-.1P-.3L-TS-2A	1.875	47.63	1.734	44.04	.170	4.32	2.062	52.37
36	2.578	65.48	2.250-.1P-.3L-TS-2A	2.093	53.16	1.984	50.39	.170	4.32	2.302	58.47
40	2.828	71.83	2.500-.1P-.3L-TS-2A	2.310	58.67	2.234	56.74	.170	4.32	2.562	65.07




KEY POSITIONS				
Position	A°	B°	C°	D°
1	80	142	196	293
2	135	170	200	310
3	49	169	200	244
4	66	140	200	257
5	62	145	180	280
6	79	153	197	272

MAX CURRENT RATING	
Contact Size	Max Current
16	10
12	17
8	33
4	60
1/0	125

Series 970 PowerTrip™ Connectors and Accessories
 Receptacle Connectors
 970-030 Solder Cup Hermetic with O-ring Seal



970-030 HERMETIC REAR PANEL MOUNT, SQUARE FLANGE RECEPTACLE



Series 970 PowerTrip™ hermetic rear panel mount (RPM) receptacles feature stainless steel shells and compression glass insulators. Solder cup contacts are nickel-iron alloy and are non-removable. Coupling threads are triple-start ACME type. Contacts are silver plated high conductivity copper alloy, or choose gold-plated contacts. Fluorosilicone rubber face seal on pin connector. Choose passivated stainless steel shells, or nickel plating for improved shell-to-shell conductivity and EMI protection. Hermeticity is 1×10^{-7} cc/sec maximum helium leak rate with one atmosphere pressure differential.

- **Compression Glass Seal**
- **1×10^{-7} cc/sec He leak rate**
- **Pin and Socket Versions**
- **Stainless Steel Shell**

PRODUCT FACTS
2000 VAC Sea Level DWV Rating
-65°C to +200°C Operating Temperature
6 Feet Water Immersion, 48 Hours
65 dB min. Attenuation, up to 10GHz
500 Cycles Mating Durability
MIL-S 901 Grade A High-Impact Shock
43 g Random Vibration


HOW TO ORDER

SERIES	SHELL MATL AND FINISH	SHELL SIZE - INSERT ARRANGEMENT					CONTACT TYPE	CONTACT PLATING OPTION	MOUNTING HOLE OPTION	KEY POSITION	
970-030 Hermetic Square Flange Panel Mount Receptacle	Z1 Passivated Stainless Steel	Contact Arr.	Contact Size and Qty					P Pin, Solder Cup	1 (Size 0, 4, 8) Silver	N Thru-Hole	-1 Position 1
		#16	#12	#8	#4	#1/0					
		18-2		2							
		18-4		2	2						
		20-3			3						
		20-4			4						
		20-5		2	3						
		20-7	4		3						
		24-2				2					
		24-3				3					
	24-5			5							
	24-6		4		2						
	24-A6		3		3						
	28-4				4						
	28-8		1	7							
	28-9	5			4						
	28-15	15									
	32-2				2						
	32-3				3						
	32-4				2						
32-5				5							
32-6		3		3							
32-20	1	19									
36-4				4							
36-16	3		13								
40-5				5							
40-21			21								
Sample Part Number											
970-030	Z1	20-4					P	2	N	-1	




Series 970 PowerTrip™ Connectors and Accessories
Receptacle Connectors
970-030 Solder Cup Hermetic with O-ring Seal

970-030 REAR PANEL MOUNT, HERMETIC RECEPTACLE WITH O-RING SEAL



DIMENSIONS											
Shell Size	A		B Mating Thread	C		D		Ø E Thru Hole		Ø F	
	In.	mm.		In.	mm.	In.	mm.	In.	mm.	In.	mm.
18	1.591	40.41	1.125-.1P-.3L-TS-2A	.972	24.69	1.275	32.38	.146	3.71	1.187	30.15
20	1.779	45.19	1.250-.1P-.3L-TS-2A	1.116	28.35	1.408	35.76	.146	3.71	1.374	34.90
24	2.029	51.54	1.500-.1P-.3L-TS-2A	1.300	33.02	1.585	40.26	.146	3.71	1.562	39.67
28	2.404	61.06	1.750-.1P-.3L-TS-2A	1.604	40.74	1.905	48.39	.170	4.32	1.874	47.60
32	2.529	64.24	2.000-.1P-.3L-TS-2A	1.875	47.63	1.993	50.62	.170	4.32	2.062	52.37
36	2.654	67.41	2.250-.1P-.3L-TS-2A	2.093	53.16	2.081	52.86	.170	4.32	2.302	58.47
40	3.029	76.94	2.500-.1P-.3L-TS-2A	2.310	58.67	2.347	59.61	.170	4.32	2.562	65.07




KEY POSITIONS				
Position	A°	B°	C°	D°
1	80	142	196	293
2	135	170	200	310
3	49	169	200	244
4	66	140	200	257
5	62	145	180	280
6	79	153	197	272

MAX CURRENT RATING	
Contact Size	Max Current
16	10
12	17
8	33
4	60
1/0	125

Series 970 PowerTrip™ Connectors and Accessories
 Receptacle Connectors
 970-025 Hermetic, Solder Cup, Jam-Nut Receptacle



970-025 HERMETIC, REAR PANEL MOUNT JAM-NUT RECEPTACLE



Series 970 PowerTrip™ hermetic solder cup receptacles can be ordered with pin or socket contacts. Mates with 970-001 or 970-011 plug of the same shell size, contact layout and polarization. Compression glass hermetic seal. 100% tested to meet helium leak rate of 1×10^{-7} cc/second at 15 psi pressure differential. Contacts are factory-installed and are non-removable. Standard gold-plated contacts for improved corrosion protection. Silver plated contacts available for contact sizes 0, 4, and 8 only. Jam-nut rear panel mounting, for panel thicknesses from 1/16 inch (1.58mm) to 1/2 inch (12.7mm).

- **Submersible**
- **Harsh Environment**

PRODUCT FACTS
2000 VAC Sea Level DWV Rating
-65°C to +200°C Operating Temperature
6 Feet Water Immersion, 48 Hours
65 dB min. Attenuation, up to 10GHz
500 Cycles Mating Durability
MIL-S 901 Grade A High-Impact Shock
43 g Random Vibration


HOW TO ORDER

SERIES	SHELL MATL AND FINISH	SHELL SIZE - INSERT ARRANGEMENT					CONTACT TYPE	CONTACT PLATING	KEY POSITION							
		Cont. Arr.	Contact Size and Qty													
			#16	#12	#8	#4	#1/0									
970-025 Series 970 Hermetic Jam-nut Receptacle with Solder Cup Termination	Stainless Steel Shell Z1 Passivated ZL Electrodeposited Nickel							P Pin, Solder Cup	1 Silver Plated Contacts	-1 Position 1						
		18-2			2						S Socket, Solder Cup	2 Gold Plated Contacts	-2 Position 2			
		18-4		2	2									-3 Position 3		
		20-3			3										-4 Position 4	
		20-4			4											-5 Position 5
		20-5		2	3											
		20-7	4		3											
		24-2					2									
		24-3					3									
		24-5				5										
		24-6		4		2										
		24-A6		3		3										
		28-4					4									
		28-8			1	7										
		28-9		5			4									
		28-15		15												
		32-2						2								
		32-3						3								
		32-4					2	2								
		32-5						5								
32-6			3			3										
32-20		1	19													
36-4						4										
36-16		3		13												
40-5						5										
40-21				21												
Sample Part Number																
970-025	Z1		32-4				S	2	-1							




Series 970 PowerTrip™ Connectors and Accessories
Receptacle Connectors
 970-025 Jam-Nut Mount, Solder Cup Hermetic

970-025 HERMETIC REAR PANEL MOUNT, JAM-NUT RECEPTACLE



DIMENSIONS										
Shell Size	A Mating Thd.	B Jam-nut Thd.	ø C		D		E		F	
			In.	mm.	In.	mm.	In.	mm.	In.	mm.
18	1.125-.1P-.3L-TS-2A	1.250-18 UNEF-2A	1.733	44.02	1.639	41.63	1.438	36.53	1.212	30.78
20	1.250-.1P-.3L-TS-2A	1.4375-18 UNEF-2A	1.921	48.79	1.827	46.41	1.625	41.28	1.399	35.53
24	1.500-.1P-.3L-TS-2A	1.625-18 UNEF-2A	2.108	53.54	2.014	51.16	1.822	46.28	1.587	40.31
28	1.750-.1P-.3L-TS-2A	1.9375-16 UN-2A	2.425	61.60	2.327	59.11	2.188	55.58	1.899	48.23
32	2.000-.1P-.3L-TS-2A	2.125-16 UN-2A	2.607	66.24	2.513	63.86	2.375	60.33	2.084	53.01
36	2.250-.1P-.3L-TS-2A	2.375-16 UN-2A	2.857	72.57	2.763	70.18	2.625	66.68	2.323	59.00
40	2.500-.1P-.3L-TS-2A	2.625-16 UN-2A	3.107	78.92	3.013	76.53	2.875	73.03	2.548	64.72

KEY POSITIONS				
Position	A°	B°	C°	D°
1	80	142	196	293
2	135	170	200	310
3	49	169	200	244
4	66	140	200	257
5	62	145	180	280
6	79	153	197	272



PANEL CUTOUT				
Shell Size	Diameter		Flat	
	In.	mm.	In.	mm.
	-.000	-.00	-.000	-.00
	+.010	+0.25	+.010	+0.25
18	1.265	32.13	1.217	30.91
20	1.452	36.88	1.409	35.79
24	1.640	41.66	1.596	40.54
28	1.952	49.58	1.910	48.51
32	2.140	54.36	2.092	53.14
36	2.390	60.71	2.342	59.49
40	2.640	67.06	2.557	64.95

Rev 01.28.15

© 2013 Glenair, Inc.

Series 970 PowerTrip™

CAGE Code 06324

Printed in U.S.A.

GLENAIR, INC. • 1211 AIR WAY • GLENDALE, CA 91201-2497 • 818-247-6000 • FAX 818-500-9912
www.glenair.com **44** **E-Mail: sales@glenair.com**


REV. 03.03.21

Series 970 PowerTrip™ Connectors and Accessories Receptacle Connectors

970-007 Jam-Nut, Bulkhead Feedthru Hermetic



970-007 HERMETIC JAM-NUT BULKHEAD FEED-THRU CONNECTOR




Series 970 PowerTrip™ hermetic feed-thru bulkhead receptacles have pin contacts on one side and socket contacts on the other side. Attach mating plug connectors to both sides. Compression glass hermetic seal. 100% tested to meet helium leak rate of 1×10^{-7} cc/second at 15 psi pressure differential. Contacts are factory-installed and are non-removable. Standard contacts are silver plated, or choose gold-plated contacts for improved corrosion protection. Jam-nut rear panel mounting, for panel thicknesses from $\frac{1}{16}$ inch (1.58mm) to $\frac{1}{2}$ inch (12.7mm). 200 PSI maximum pressure rating, bi-directional.

- 1×10^{-7} ccHe/sec
- Harsh Environment

PRODUCT FACTS
2000 VAC Sea Level DWV Rating
-65°C to +200°C Operating Temperature
6 Feet Water Immersion, 48 Hours
65 dB min. Attenuation, up to 10GHz
500 Cycles Mating Durability
MIL-S 901 Grade A High-Impact Shock
43 g Random Vibration

HOW TO ORDER


SERIES	SHELL MATL AND FINISH	SHELL SIZE - INSERT ARRANGEMENT					CONTACT TYPE	CONTACT PLATING	KEY POSITION		
		Cont. Arr.	Contact Size and Qty								
			#16	#12	#8	#4	#1/0				
970-007 Series 970 Hermetic Bulkhead Feed-Thru Connector, with Jam-nut Mounting	Stainless Steel Shell Z1 Passivated ZL Electrodeposited Nickel	18-2			2			P Pin Contacts on Jam-nut Side	1 Silver Plated Contacts	-1 Position 1	
		18-4		2	2						
		20-3				3			S Socket Contacts on Jam-nut Side	2 Gold Plated Contacts	-2 Position 2
		20-4				4					
		20-5			2	3			PP Pins on Both Sides		-3 Position 3
		20-7	4			3					
		24-2					2		SS* Sockets on Both Sides		-4 Position 4
		24-3					3				
		24-5				5					-5 Position 5
		24-6			4		2				
		24-A6			3		3				-6 Position 6
		28-4					4				
		28-8			1	7					
		28-9			5			4			
		28-15			15						
		32-2						2			
		32-3						3			
		32-4					2	2			
		32-5						5			
		32-6				3		3			
32-20		1	19								
36-4						4					
36-16		3			13						
40-5						5					
40-21						21					
Sample Part Number											
970-007	Z1			32-4			S	2	-1		





Series 970 PowerTrip™ Connectors and Accessories
Receptacle Connectors
 970-007 Jam-Nut, Bulkhead Feedthru Hermetic


970-007 HERMETIC FEED-THRU RECEPTACLE



DIMENSIONS										
Shell Size	A Mating Thd.	B Jam-nut Thd.	ø C		D		E		F	
			In.	mm.	In.	mm.	In.	mm.	In.	mm.
18	1.125-.1P-.3L-TS-2A	1.250-18 UNEF-2A	1.733	44.02	1.639	41.63	1.438	36.53	1.212	30.78
20	1.250-.1P-.3L-TS-2A	1.4375-18 UNEF-2A	1.921	48.79	1.827	46.41	1.625	41.28	1.399	35.53
24	1.500-.1P-.3L-TS-2A	1.625-18 UNEF-2A	2.108	53.54	2.014	51.16	1.822	46.42	1.587	40.31
28	1.750-.1P-.3L-TS-2A	1.9375-16 UN-2A	2.425	61.60	2.327	59.11	2.188	55.58	1.899	48.23
32	2.000-.1P-.3L-TS-2A	2.125-16 UN-2A	2.607	66.24	2.513	63.86	2.375	60.33	2.087	53.01
36	2.250-.1P-.3L-TS-2A	2.375-16 UN-2A	2.857	72.57	2.763	70.18	2.625	66.68	2.323	59.00
40	2.500-.1P-.3L-TS-2A	2.625-16 UN-2A	3.107	78.92	3.013	76.53	2.875	73.03	2.548	64.72

E

KEY POSITIONS				
Position	A°	B°	C°	D°
1	80	142	196	293
2	135	170	200	310
3	49	169	200	244
4	66	140	200	257
5	62	145	180	280
6	79	153	197	272



Shell Size	Diameter		Flat	
	In.	mm.	In.	mm.
	-.000 +.010	-.00 +.025	-.000 +.010	-.00 +.025
18	1.265	32.13	1.217	30.91
20	1.452	36.88	1.409	35.79
24	1.640	41.66	1.596	40.54
28	1.952	49.58	1.910	48.51
32	2.140	54.36	2.092	53.14
36	2.390	60.71	2.342	59.49
40	2.640	67.06	2.557	64.95

Series 970 PowerTrip™ Connectors and Accessories
 Receptacle Connectors
 970-026 Dual O-ring, Jam-Nut, Bulkhead Feedthru Hermetic



970-026 HERMETIC BULKHEAD FEED-THRU CONNECTOR




Series 970 PowerTrip™ dual O-ring hermetic feed-thru bulkhead receptacles have pin contacts on one side and socket contacts on the other side. Attach mating plug connectors to both sides. Compression glass hermetic seal. 100% tested to meet helium leak rate of 1×10^{-7} cc/second at 15 psi pressure differential. Contacts are factory installed and non-removable. Standard gold plated contacts for improved corrosion protection. Silver plated contacts available for contact sizes 0, 4, and 8 only. Jam-nut rear panel mount, accommodates panel thicknesses of $\frac{1}{16}$ inch (1.58mm) to $\frac{1}{2}$ inch (12.7mm).

- 1×10^{-7} ccHe/sec
- Harsh Environment

PRODUCT FACTS
2000 VAC Sea Level DWV Rating
-65°C to +200°C Operating Temperature
6 Feet Water Immersion, 48 Hours
65 dB min. Attenuation, up to 10GHz
500 Cycles Mating Durability
MIL-S 901 Grade A High-Impact Shock
43 g Random Vibration

HOW TO ORDER


SERIES	SHELL MATL AND FINISH	SHELL SIZE - INSERT ARRANGEMENT					CONTACT TYPE	CONTACT PLATING	KEY POSITION	
		Cont. Arr.	Contact Size and Qty							
		#16	#12	#8	#4	#1/0				
970-026 Series 970 Dual O-ring Hermetic Bulkhead Feed-Thru Connector, with Jam-nut Mounting	Stainless Steel Shell Z1 Passivated ZL Electrodeposited Nickel			2			P Pin Contacts on Jam-nut Side	1 Silver Plated Contacts	-1 Position 1	
		18-2							-2 Position 2	
		18-4		2	2					-3 Position 3
		20-3			3					-4 Position 4
		20-4			4					-5 Position 5
		20-5		2	3					-6 Position 6
		20-7	4		3					
		24-2				2				
		24-3				3				
		24-5			5					
		24-6		4		2				
		24-A6		3		3				
		28-4				4				
		28-8		1	7					
		28-9	5			4				
		28-15	15							
		32-2							2	
		32-3							3	
		32-4				2			2	
		32-5				5				
32-6		3			3					
32-20	1	19								
36-4					4					
36-16	3		13							
40-5					5					
40-21			21							
Sample Part Number										
970-026	Z1	32-4					S	2	-1	






Series 970 PowerTrip™ Connectors and Accessories
Receptacle Connectors
 970-026 Dual O-ring, Jam-Nut, Bulkhead Feedthru Hermetic

970-026 DUAL O-RING HERMETIC FEED-THRU RECEPTACLE



DIMENSIONS										
Shell Size	A Mating Thd.	B Jam-nut Thd.	ø C		D		E		F	
			In.	mm.	In.	mm.	In.	mm.	In.	mm.
18	1.125-.1P-.3L-TS-2A	1.250-18 UNEF-2A	2.250	57.15	2.125	53.98	1.438	36.53	1.212	30.78
20	1.250-.1P-.3L-TS-2A	1.4375-18 UNEF-2A	2.375	60.33	2.250	57.15	1.625	41.28	1.399	35.53
24	1.500-.1P-.3L-TS-2A	1.625-18 UNEF-2A	2.625	66.68	2.500	63.50	1.822	46.42	1.587	40.31
28	1.750-.1P-.3L-TS-2A	1.9375-16 UN-2A	2.875	73.03	2.700	68.58	2.188	55.58	1.899	48.23
32	2.000-.1P-.3L-TS-2A	2.125-16 UN-2A	3.000	76.20	2.800	71.12	2.375	60.33	2.084	53.00
36	2.250-.1P-.3L-TS-2A	2.375-16 UN-2A	3.125	79.38	3.025	76.84	2.625	66.68	2.323	59.00
40	2.500-.1P-.3L-TS-2A	2.625-16 UN-2A	3.500	88.90	3.300	83.82	2.875	73.03	2.548	54.72

KEY POSITIONS				
Position	A°	B°	C°	D°
1	80	142	196	293
2	135	170	200	310
3	49	169	200	244
4	66	140	200	257
5	62	145	180	280
6	79	153	197	272



Shell Size	Diameter		Flat	
	In.	mm.	In.	mm.
	-0.000 +0.010	-0.00 +0.25	-0.000 +0.010	-0.00 +0.25
18	1.265	32.13	1.217	30.91
20	1.452	36.88	1.409	35.79
24	1.640	41.66	1.596	40.54
28	1.952	49.58	1.910	48.51
32	2.140	54.36	2.092	53.14
36	2.390	60.71	2.342	59.49
40	2.640	67.06	2.557	64.95

CONTACT CONNECTORS


Series 970 PowerTrip™

Connectors and Accessories

970-041 LIGHT WEIGHT HERMETIC, BULKHEAD, JAM NUT FEEDTHROUGH



PowerTrip™



CODE RED

TABLE I: HOW TO ORDER						
Sample Part Number	970-041	ME	28	-4	P	2 -1
Basic Number	970-041 Light Weight Hermetic, Bulkhead, Jam Nut Feedthrough					
Material/Finish	ME = Electroless Nickel, Aluminum NF = Olive Drab Cadmium (+175° C MAX), Aluminum ZR = Black Zinc Nickel (+175° C MAX), Aluminum Z1 = Passivated, Stainless Steel					
Shell Size	See Dimensions Table					
Insert Arrangement	See Below					
Insert Designator	P = Pin Contact On Jamnut Side (Socket Opposite) S = Socket Contact On Jamnut Side (Pin Opposite)					
Contact Plating	2 = Gold					
Key Position	1, 2, 3, 4, 5, or 6 (See Table II)					


MATERIALS / FINISHES

- Sealing Compound - Polymer Encapsulant
- Contacts - Copper Alloy / Gold Over Nickel
- Seal - Interfacial/O-Ring: Fluorosilicone
- Insulator - High Grade Rigid Dielectric
- Shell, Jam Nut - See Table 1

NOTES

- Insert arrangement 28-4, shown for reference. Standard arrangement shown here. Consult factory for additional options.
- Performance
 - See 979-001 for additional product specifications
 - IR: 5000 megohms min @ 500 VDC
 - DWV: 2000 VAC RMS
 - Leak rate: 1×10^{-7} cc/s max helium, 1 ATM
 - Operating temperature range: -65° C to +200° C

INSERT ARRANGEMENTS



CONTACT CONNECTORS


Series 970 PowerTrip™

Connectors and Accessories



970-041 LIGHT WEIGHT HERMETIC, BULKHEAD, JAM NUT FEEDTHROUGH



PowerTrip™



DIMENSIONS														
Shell Size	A Mating Thread	B Jam Nut Thread	ø C		D		E		F		ø G MTG. Hole		H Hole Flat	
			In.	mm.	In.	mm.	In.	mm.	In.	mm.	In.	mm.	In.	mm.
18	1.125-0.1P-0.3L-TS-2A	1.250-18UNEF-2A	1.733	44.02	1.639	41.63	1.438	36.53	1.212	30.78	1.265	32.13	1.217	30.91
20	1.250-0.1P-0.3L-TS-2A	1.4375-18UNEF-2A	1.921	48.79	1.827	46.41	1.625	41.28	1.399	35.53	1.452	36.88	1.409	35.79
24	1.500-0.1P-0.3L-TS-2A	1.625-18UNEF-2A	2.108	53.54	2.014	51.16	1.822	46.28	1.587	40.31	1.640	41.66	1.596	40.54
28	1.750-0.1P-0.3L-TS-2A	1.9375-16UN-2A	2.425	61.60	2.327	59.11	2.188	55.58	1.899	48.23	1.952	49.58	1.910	48.51
32	2.000-0.1P-0.3L-TS-2A	2.125-16UN-2A	2.607	66.24	2.513	63.86	2.375	60.33	2.084	53.00	2.140	54.36	2.092	53.14
36	2.250-0.1P-0.3L-TS-2A	2.375-16UN-2A	2.857	72.57	2.763	70.18	2.625	66.68	2.323	59.00	2.390	60.71	2.342	59.49
40	2.500-0.1P-0.3L-TS-2A	2.625-16UN-2A	3.107	78.92	3.013	76.53	2.875	73.03	2.548	64.72	2.640	67.06	2.557	64.95



RECOMMENDED PANEL HOLE

Position	A°	B°	C°	D°
1	80	142	196	293
2	135	170	200	310
3	49	169	200	244
4	66	140	200	257
5	62	145	180	280
6	79	153	197	272

HOW TO ORDER	
Sample Part Number	970-038 -H2 Z1 32 -5 P 2 -1
Basic Number	970-038 Crimp Removable Receptacle
Mounting	H2 = Wall Mount H7 = Jam-Nut Mount
Finish	Z1 = Stainless steel, passivate ZL = Stainless steel, electrodeposited nickel
Shell Size	See Dimensions Table
Contact Arrangement	See Insert Arrangements Table
Contact Style	P = Pin face S = Socket face
Contact Plating	1 = Silver (0, 4, 8 only) 2 = Gold
Polarization	1, 2, 3, 4, 5, 6 See Key Positions table

MATERIAL AND FINISH


- Shell - Stainless steel, passivate; stainless steel, electrodeposited nickel
- Insulator, Hermetic - Glass
- Insulator, Sockets - Rigid Dielectric
- Contacts, Hermetic - Iron-Nickel Alloy
- Contacts, Sockets - Copper Alloy
- Seals - Fluorosilicone

NOTES

- Performance Characteristics:
 - Hermeticity: <math>< 1 \times 10^{-7}</math> sccHe/sec @ 1 ATM. differential
 - D.W.V.: 2000 VAC pin-to-pin and pin-to shell w/o breakdown
 - I. R.: 5000 MEGOHMS min
 - Current Rating: See Max Current Rating table

MAX CURRENT RATING	
Contact Size	Max Current
16	10
12	17
8	33
4	60
1/0	125


INSERT ARRANGEMENTS



Connectors and Accessories

970-038 Hermetic Crimp Removable Receptacle

970-038-H2 HERMETIC WALL MOUNT



KEY POSITIONS				
Position	A°	B°	C°	D°
1	80	142	196	293
2	135	170	200	310
3	49	169	200	244
4	66	140	200	257
5	62	145	180	280
6	79	153	197	272


DIMENSIONS									
Shell Size	A CPLG Thread 0.1P-0.3L TS-2A		B Flange Width		C Mount Holes		D Holes Through	E Acc. Thread	F Panel Cut-out
	In.	mm.	In.	mm.	In.	mm.			
18	1.125	28.58	1.383	35.13	1.015	25.78	ø.146	1.1250-18 UNEF-2A	ø1.187
20	1.250	31.75	1.508	38.30	1.140	28.96	ø.146	1.2500-18 UNEF-2A	ø1.374
24	1.500	38.10	1.718	43.64	1.281	32.54	ø.146	1.4375-18 UNEF-2A	ø1.562
28	1.750	44.45	2.138	54.31	1.588	40.34	ø.170	1.8125-16 UN-2A	ø1.874
32	2.000	50.80	2.328	59.13	1.734	44.04	ø.170	2.0625-16 UNS-2A	ø2.062
36	2.250	57.15	2.578	65.48	1.984	50.39	ø.170	2.2500-16 UN-2A	ø2.302
40	2.500	63.50	2.828	71.83	2.234	56.74	ø.170	2.5000-16 UN-2A	ø2.562

Series 970 PowerTrip™

Connectors and Accessories

970-038 Hermetic Crimp Removable Receptacle

970-038-H7 HERMETIC JAM-NUT MOUNT



KEY POSITIONS				
Position	A°	B°	C°	D°
1	80	142	196	293
2	135	170	200	310
3	49	169	200	244
4	66	140	200	257
5	62	145	180	280
6	79	153	197	272


DIMENSIONS													
Shell Size	A CPLG Thread 0.1P-0.3L TS-2A		B Panel Mounting Thread	ø C Flange		D Flange Width		E Hex Jam-Nut		F Acc. Thread	Panel Cut-Out		
	In.	mm.		In.	mm.	In.	mm.	In.	mm.		ø G ± .005	H ± .005	
												In.	mm.
18	1.125	28.58	1.2500-18 UNEF-2A	1.723	43.76	1.639	41.63	1.438	36.53	1.1250-18 UNEF-2A	ø1.270	1.222	31.04
20	1.250	31.75	1.4375-18 UNEF-2A	1.921	48.79	1.827	46.41	1.625	41.28	1.2500-18 UNEF-2A	ø1.457	1.414	35.92
24	1.500	38.10	1.6250-18 UNEF-2A	2.108	53.54	2.014	51.16	1.822	46.28	1.4375-18 UNEF-2A	ø1.645	1.601	40.67
28	1.750	44.45	1.9375-16 UN-2A	2.425	61.59	2.327	59.11	2.188	55.58	1.8125-16 UN-2A	ø1.957	1.915	48.64
32	2.000	50.80	2.1250-16 UN-2A	2.607	66.22	2.513	63.83	2.375	60.33	2.0625-16 UNS-2A	ø2.145	2.097	53.26
36	2.250	57.15	2.3750-16 UN-2A	2.857	72.57	2.763	70.18	2.625	66.68	2.2500-16 UN-2A	ø2.395	2.347	59.61
40	2.500	63.50	2.6250-16 UN-2A	3.107	78.92	2.875	73.02	2.875	73.02	2.5000-16 UN-2A	ø2.645	2.562	65.07

Series 970 PowerTrip™ Connectors and Accessories
 Filter Receptacles
 240-970W Square Flange Receptacle



240-970W FILTER RECEPTACLE, SQUARE FLANGE

Series 970 PowerTrip™ filter receptacles feature planar array ceramic capacitors. Solder cup contacts are factory-installed, epoxy sealed and are non-removable. Socket contacts have copper alloy louverband spring for multiple points of electrical contact. Coupling threads are triple-start ACME type. Contacts are gold plated. Fluorosilicone rubber face seal on pin connector. Aluminum or stainless steel shell.






- Planar Array C Filter
- -55° C to +125° C
- 1,250 VDC DWV Rating
- Solder Cup Contacts

INSERTION LOSS			
Insertion Loss, dB minimum, 25°C			
Frequency	CX	CY	CZ
	80K-120K pF	40K-60K pF	30K-45K pF
1 MHz	22	16	13
10 MHz	41	36	33
100 MHz	56	53	52
500 -1000 MHz	60	57	57

HOW TO ORDER

SERIES	SHELL MATL AND FINISH	SHELL SIZE - INSERT ARRANGEMENT					CONTACT TYPE	FILTER TYPE & CAPACITANCE	MOUNTING HOLE	KEY POS.	
		Contact Arr.	Contact Size and Qty								
240-970W Filter Receptacle, Square Flange	ME Aluminum, Electroless Nickel Finish							PS Pin Contact, Solder Cup	CX C Filter 80,000-120,000 pF	N Thru-Hole	1 Pos. 1
		#16	#12	#8	#4	#1/0					
				2							
			2	2							
					3						
					4						
			2	3							
			4		3						
						2					
						3					
					5						
						2					
			4		2						
				3		3					
						4					
			5			4					
							2				
							3				
					2	2					
						5					
			3			3					
						4					
						5					
Sample Part Number											
240-970W	ME		40-5					PS	CY	N	1

240-970W FILTER RECEPTACLE, SQUARE FLANGE




SOLDER CUP DIMENSIONS		
Contact Size	G Typ	
	In. ±.025	mm. ±0.64
16	.500	12.70
12	.500	12.70
8	.600	15.24
4	.800	20.32
1/0	.800	20.32

DIMENSIONS

Shell Size	A Sq.		B Mating Thread	C Accessory Thd	D Bsc		Ø E		E Clinch Nut Thd	Ø F	
	In.	mm.			In.	mm.	In.	mm.		In.	mm.
18	1.383	35.13	1.125-.1P-.3L-TS-2A	1.125-18 UNEF-2A	1.015	25.78	.146	3.71	6-32 UNC-2B	1.187	30.15
20	1.508	38.30	1.250-.1P-.3L-TS-2A	1.250-18 UNEF-2A	1.140	28.96	.146	3.71	6-32 UNC-2B	1.374	34.90
24	1.718	43.64	1.500-.1P-.3L-TS-2A	1.4375-18 UNEF-2A	1.281	32.54	.146	3.71	6-32 UNC-2B	1.562	39.67
28	2.138	54.31	1.750-.1P-.3L-TS-2A	1.8125-16 UN-2A	1.568	39.83	.170	4.32	8-32 UNC-2B	1.874	47.60
32	2.328	59.13	2.000-.1P-.3L-TS-2A	2.0625-16 UNS-2A	1.734	44.04	.170	4.32	8-32 UNC-2B	2.062	52.37
36	2.578	65.48	2.250-.1P-.3L-TS-2A	2.250-16 UN-2A	1.984	50.39	.170	4.32	8-32 UNC-2B	2.302	58.47
40	2.828	71.83	2.500-.1P-.3L-TS-2A	2.500-16 UN-2A	2.234	56.74	.170	4.32	8-32 UNC-2B	2.562	65.07

MATERIALS AND FINISHES

Shells, Jam Nuts	Aluminum alloy or stainless steel
Contacts	High conductivity copper alloy, gold over nickel plating
Insulators	Thermoset epoxy
Interfacial Seal	Fluorosilicone
Clinch Nut	Stainless steel



KEY POSITIONS


Position	A°	B°	C°	D°
1	80	142	196	293
2	135	170	200	310
3	49	169	200	244
4	66	140	200	257
5	62	145	180	280
6	79	153	197	272

Series 970 PowerTrip™ Connectors and Accessories Filter Receptacles 240-970J Jam Nut Receptacle



240-970J FILTER RECEPTACLE, JAM NUT

Series 970 PowerTrip™ filter receptacles feature planar array ceramic capacitors. Solder cup contacts are factory-installed, epoxy sealed and are non-removable. Socket contacts have copper alloy louverband spring for multiple points of electrical contact. Coupling threads are triple-start ACME type. Contacts are gold plated. Fluorosilicone rubber face seal on pin connector. Aluminum or stainless steel shell.



- Planar Array C Filter
- -55° C to +125° C
- 1,250 VDC DWV Rating
- Solder Cup Contacts


INSERTION LOSS			
Insertion Loss, dB minimum, 25°C			
Frequency	CX	CY	CZ
	80K-120K pF	40K-60K pF	30K-45K pF
1 MHz	22	16	13
10 MHz	41	36	33
100 MHz	56	53	52
500 -1000 MHz	60	57	57

HOW TO ORDER

SERIES	SHELL MATL AND FINISH	SHELL SIZE - INSERT ARRANGEMENT					CONTACT TYPE	FILTER TYPE & CAPACITANCE	MOUNTING STYLE	KEY POS.						
		Contact Arr.	Contact Size and Qty													
240-970J Filter Receptacle, Jam Nut	ME Aluminum, Electroless Nickel Finish	18-2	#16	#12	#8	#4	#1/0	PS Pin Contact, Solder Cup	CX C Filter 80,000-120,000 pF	N Standard Mounting	1 Pos. 1					
			18-4		2											
		20-3			3							SS Socket Contact, Solder Cup	CY C Filter 40,000-60,000 pF	2 Pos. 2		
			20-4			4										
		20-5		2	3										CZ C Filter 30,000-45,500 pF	3 Pos. 3
			20-7	4		3										
	24-2	Aluminum, Olive Drab Cadmium				2		4 Pos. 4								
			24-3			3										
			24-5			5										
	24-6	Aluminum, Black Zinc- Nickel Finish		4		2			5 Pos. 5							
			24-A6		3	3										
	28-4	Aluminum, Black Zinc- Nickel Finish				4				6 Pos. 6						
			28-9	5		4										
	32-2	Stainless Steel, Nickel-PTFE Finish					2	Sample Part Number								
			32-3				3									
			32-4			2	2									
	32-5	Stainless Steel, Passivated				5										
			32-6		3		3									
	36-4					4										
	40-5					5										
240-970J	ME	40-5					PS	CY	N	1						



240-970J DIMENSIONS



SOLDER CUP DIMENSIONS


Contact Size	H Typ	
	In.	mm.
16	.500	12.70
12	.500	12.70
8	.600	15.24
4	.800	20.32
1/0	.800	20.32

DIMENSIONS

Shell Size	A Mating Thd.	B Accessory Thd.	C Jam Nut Thd.	$\varnothing D$		E Sq.		F		G Flat	
				In.	mm.	In.	mm.	In.	mm.	In.	mm.
18	1.125-.1P-.3L-TS-2A	1.125-18 UNEF-2A	1.250-18 UNEF-2A	1.733	44.02	1.639	41.63	1.438	36.53	1.212	31.06
20	1.250-.1P-.3L-TS-2A	1.250-18 UNEF-2A	1.4375-18 UNEF-2A	1.921	48.79	1.827	46.41	1.625	41.28	1.399	35.81
24	1.500-.1P-.3L-TS-2A	1.4375-18 UNEF-2A	1.625-18 UNEF-2A	2.108	53.54	2.014	51.16	2.000	50.80	1.587	43.76
28	1.750-.1P-.3L-TS-2A	1.8125-16 UN-2A	1.9375-16 UN-2A	2.425	61.60	2.327	59.11	2.188	55.58	1.899	48.51
32	2.000-.1P-.3L-TS-2A	2.0625-16 UNS-2A	2.125-16 UN-2A	2.607	66.24	2.514	63.86	2.375	60.33	2.084	52.93
36	2.250-.1P-.3L-TS-2A	2.250-16 UN-2A	2.375-16 UN-2A	2.857	72.57	2.763	70.18	2.625	66.68	2.323	59.00
40	2.500-.1P-.3L-TS-2A	2.500-16 UN-2A	2.625-16 UN-2A	3.107	78.92	3.013	76.53	2.875	73.03	2.548	64.72


KEY POSITIONS

Position	A°	B°	C°	D°
1	80	142	196	293
2	135	170	200	310
3	49	169	200	244
4	66	140	200	257
5	62	145	180	280
6	79	153	197	272



PANEL CUTOUT

Shell Size	Diameter		Flat	
	In.	mm.	In.	mm.
	-.000 +.010	-.00 +0.25	-.000 +.010	-.00 +0.25
18	1.254	31.85	1.217	30.91
20	1.441	36.60	1.404	35.66
24	1.629	41.38	1.592	40.64
28	1.941	49.30	1.904	48.36
32	2.129	54.08	2.092	53.14
36	2.379	60.43	2.328	59.13
40	2.629	66.78	2.553	64.85




POWERTRIP™
POWERLINE
FILTERS

POWERLINE FILTERS WITH COMMON MODE CHOKES AND LINE-TO-LINE FILTERING

*Contact factory for high-performance, low heat
dissipation powerline filtering*



Powerline filters suited for filtering DC and AC mains services are typically designed to incorporate both common-mode and differential-mode filters (line-to-line). Common mode chokes capable of screening both incoming and outgoing noise and transients (see example schematic) are ideally suited for incorporation in Series 970 PowerTrip™ filter connectors. All multiple-line filters employ modern filter elements incorporating compensating inductors or coupled chokes. PowerTrip powerline filters are typically supplied as made-to-order (bespoke) solutions. Please contact the factory for application engineering assistance.



Glenair®

Glenair, Inc.
1211 Air Way
Glendale, CA
91201-2497
818-247-6000
sales@glenair.com
www.glenair.com




Series 970 PowerTrip™ Connectors and Accessories

Contacts and Tools

Crimp Contacts

CRIMP CONTACTS

Series 970 PowerTrip™ contacts for size #16 through Size #1/0 wire. Size #8, #4 and #1/0 contacts are high conductivity copper alloy (IACS >90%) with silver or gold plating. Size #12 and #16 contacts are copper alloy with gold over palladium finish. Size #1/0, 4 and 8 socket contacts feature low resistance, high durability louverband springs. Terminate to wire with standard crimp tools. Contacts are snap-in, rear-release and meet the performance requirements of SAE AS39029.



Pin Contact

- LouverBand Springs
- Crimp Termination
- High Conductivity Alloy
- Gold or Silver Plating



Socket Contact

Crimp Contacts


Size	Wire Size	Finish	Pin Contact Part Number	Socket Contact Part Number	Socket Contact Type
16	#16-#20	Gold/Palladium	850-037-16	850-038-16	Split-Tine
12	#12-#14	Gold/Palladium	850-037-12	850-038-12	Split-Tine
8	#8	Silver	850-026-8-8-1	850-027-8-8-1	LouverBand
		Gold	850-026-8-8-2	850-027-8-8-2	LouverBand
	#10	Silver	850-026-8-10-1	850-027-8-10-1	LouverBand
		Gold	850-026-8-10-2	850-027-8-10-2	LouverBand
4	#4	Silver	850-026-4-4-1	850-027-4-4-1	LouverBand
		Gold	850-026-4-4-2	850-027-4-4-2	LouverBand
	#6	Silver	850-026-4-6-1	850-027-4-6-1	LouverBand
		Gold	850-026-4-6-2	850-027-4-6-2	LouverBand
1/0	#1/0	Silver	850-026-0-0-1	850-027-0-0-1	LouverBand
		Gold	850-026-0-0-2	850-027-0-0-2	LouverBand
	#2	Silver	850-026-0-2-1	850-027-0-2-1	LouverBand
		Gold	850-026-0-2-2	850-027-0-2-2	LouverBand

Material and Finish Specifications

Pin, Size #16 and #12	Copper alloy, gold flash over palladium finish
Pin, Size #8, #4 and #1/0	High conductivity copper alloy, gold or silver finish over nickel
Socket, Size #16 and #12	Copper alloy, stainless steel hood, gold flash over palladium finish
Socket, Size #8, #4 and #1/0	High conductivity copper alloy, beryllium copper louverband spring, gold or silver finish over nickel

Tools for Contact Crimping and Installation

Contact Size	Wire Size	Insertion/Extraction Tool	Extraction Tool	Crimp Tool	Positioner	Die Set	Locator
#16	#16 - #20	809-131	—	809-136	859-032	—	—
#12	#12 - #14	809-132	—	809-136	859-032	—	—
#8	#8	—	859-022	859-025	—	859-026	859-029
#8	#10	—	859-022	859-025	—	859-026	859-173
#4	#4 - #6	—	859-023	859-025	—	859-027	859-030
#1/0	#1/0 - #2	—	859-024	859-025	—	859-028	859-031




SIZE 8 CONTACTS	
Current, A	Temperature Rise, °C
0	0
20	4
30	9
46	20
50	23
60	33
80	56
120	88
150	179






Series 970 PowerTrip™ Connectors and Accessories
Size 4 Contact Current Performance

Current De-Rating Curve for PowerTrip™ Size 4 Louverband Contacts



SIZE 4 CONTACTS	
Current, A	Temperature Rise, °C
0	0
40	4
60	10
80	18
100	28
120	40
140	54
200	100
240	176





SIZE 1/0 CONTACTS	
Current A	Temperature Rise, °C
0	0
100	11
125	17
150	22
175	31
200	39
225	48
350	104
425	177













Series 970 PowerTrip™ Connectors and Accessories

Contacts and Tools


Crimp Contacts

PIN CONTACTS




G


SOCKET CONTACTS




850-038-16




850-038-12




850-027-8-8




850-027-8-10




850-027-4-4



850-027-4-6



850-027-0-0




850-027-0-2





Series 970 PowerTrip™ Connectors and Accessories
Contacts and Tools
Crimp Tools

HAND CRIMP TOOL AND POSITIONER FOR #12 AND #16 CONTACTS



A Crimp tool for use with size #16 and #12 Series 970 pin and socket contacts. Use with turret-type positioner 859-032. 9.75 inches OAL, 1.25 pounds.

B Positioner for use with size #12 and #16 contacts. Rotate turret head to blue position for #16 contact termination, yellow position for #12 contacts.

Figure	Wire Size	Part Number	Military Part Number
A	N/A	809-136	M22520/1-01
B	#16 - #20	859-032	M22520/1-02
B	#12 - #14	859-032	M22520/1-02

PNEUMATIC CRIMP TOOL FOR #8, #4 AND #1/0 CONTACTS




C Bench mount pneumatic crimp tool. Heavy duty, four-indent crimp termination. Attach to air supply with quick-disconnect fitting or install 1/4 NPT fitting into tapped port. 90-120 psi air supply. Requires die assemblies and locators, sold separately. Hand actuate with push-button valve trigger on handle. Steel with black wrinkle enamel coating. 13 inches overall length, 9.2 inches tall, 17 pounds (7.7 Kg).

D Indenter Die Assembly. Precision four-indent die with hardened tool steel indenters, stainless steel housing. Separate die assembly required for each contact size.

E Locator. Aluminum locator positions contact at correct depth for crimping. Separate locator required for each contact size.



Contact Size	Wire Size	Crimper (Fig. C)	Die Assembly (Fig. D)	Locator (Fig. E)
8	#10	859-025 M22520/23-01	859-026 M22520/23-02	859-173 N/A
8	#8		859-026 M22520/23-02	859-029 M22520/23-09
4	#4 - #6		859-027 M22520/23-04	859-030 M22520/23-11
1/0	#1/0 - #2		859-028 M22520/23-05	859-031 M22520/23-13



Series 970 PowerTrip™ Connectors and Accessories

Contacts and Tools

Insertion/Removal Tools, Band Tools and Sealing Plugs



Contacts and Tools

CONTACT INSERTION AND REMOVAL TOOLS





Install and remove PowerTrip™ contacts with plastic or Mil-spec metal tools.

Plastic Contact Removal Tools		
Size	Part Number	Color
#1/0	N/A	-
#4	859-136-04	Blue
#8	859-136-08	Red
#12	859-136-12	Yellow
#16	859-136-16	Blue

Metal Contact Removal Tools		
Size	Military Part Number	Part Number
#1/0	M81969/15-03	859-137
#4	M81969/15-02	859-138
#8	M81969/15-01	859-139
#12	M81969/8-210	859-140
#16	M81969/8-208	859-141

Metal Contact Removal Tools		
Size	Military Part Number	Part Number
#1/0		
#4	N/A	N/A
#8		
#12	M81969/8-209	859-142
#16	M81969/8-207	859-143

BAND-MASTER™ ATS SHIELD TERMINATION TOOL AND BANDS




Fast, cost-effective shield termination. Attach cable shield to 440-069 EMI/RFI backshells with stainless steel bands. The **Band-Master™** system offers fast termination and the flexibility to handle a wide range of parts with just one band size. Contact factory about QPL approved bands for aerospace and defense applications.

A Banding tool for use with .250" (6.4mm) width bands. Digital counter improves calibration interval accuracy. Supplied with hardshell case and instruction booklet. 1.18 lbs., 5.75" length.

B .250" (6.4mm) width band. Supplied flat or pre-coiled in two lengths. Stainless steel.


Figure	Description	Part Number
A	Standard Band Installation Tool	601-100

Figure	Length		Part Number		Accommodates Diameter	
	in.	mm.	Flat	Pre-Coiled	in.	mm.
B	14.0	355.6	601-040	601-041	1.88	47.8
B	18.0	457.2	601-049	601-050	2.5	63.5



Contact Glenair or visit our website (www.glenair.com) to view our complete line of **Band-Master™** products, including pneumatic tools for high volume production and calibration kits.

GROMMET SEALING PLUGS



Grommet sealing plugs prevent moisture and contamination from entering unwired connector positions. Molded thermoplastic. Size 12 and size 16 plugs can be inserted with contact insertion tools. Size 8 and larger can be inserted by hand with no tool. Bulk packaged.

Figure	Size	Color	Part Number	Military Part Number
1	#16	Blue	859-036	MS27488-16-3
2	#12	Yellow	859-037	MS27488-12-3
3	#8	Red	859-038	MS27488-8-3
4	#4	Blue	859-039	MS27488-4-3
5	#1/0	Yellow	859-040	MS27488-0-3

G



Series 970 PowerTrip™ Connectors and Accessories
Contacts and Tools
Connector Holding Tools, Backshell Assembly Tools

CONNECTOR HOLDING TOOL

Simplify backshell installation with connector holding tools. Tool prevents connector damage by securely holding the connector mating face in position while tightening a backshell onto connector. Install holding tool onto torque wrench. 3/8" square drive. Heat-treated steel with nickel plating.



A Plug tool for use with 970-001 plug connectors.



B Receptacle tool for use with 970 Series receptacle connectors.

HOW TO ORDER

Shell Size	Fig.	Type	Shell Polarizing Position					
			1	2	3	4	5	6
18	A	Plug	600P005-18P1	600P005-18P2	600P005-18P3	600P005-18P4	600P005-18P5	600P005-18P6
	B	Recep	600P005-18R1	600P005-18R2	600P005-18R3	600P005-18R4	600P005-18R5	600P005-18R6
20	A	Plug	600P005-20P1	600P005-20P2	600P005-20P3	600P005-20P4	600P005-20P5	600P005-20P6
	B	Recep	600P005-20R1	600P005-20R2	600P005-20R3	600P005-20R4	600P005-20R5	600P005-20R6
24	A	Plug	600P005-24P1	600P005-24P2	600P005-24P3	600P005-24P4	600P005-24P5	600P005-24P6
	B	Recep	600P005-24R1	600P005-24R2	600P005-24R3	600P005-24R4	600P005-24R5	600P005-24R6
28	A	Plug	600P005-28P1	600P005-28P2	600P005-28P3	600P005-28P4	600P005-28P5	600P005-28P6
	B	Recep	600P005-28R1	600P005-28R2	600P005-28R3	600P005-28R4	600P005-28R5	600P005-28R6
32	A	Plug	600P005-32P1	600P005-32P2	600P005-32P3	600P005-32P4	600P005-32P5	600P005-32P6
	B	Recep	600P005-32R1	600P005-32R2	600P005-32R3	600P005-32R4	600P005-32R5	600P005-32R6
36	A	Plug	600P005-36P1	600P005-36P2	600P005-36P3	600P005-36P4	600P005-36P5	600P005-36P6
	B	Recep	600P005-36R1	600P005-36R2	600P005-36R3	600P005-36R4	600P005-36R5	600P005-36R6
40	A	Plug	600P005-40P1	600P005-40P2	600P005-40P3	600P005-40P4	600P005-40P5	600P005-40P6
	B	Recep	600P005-40R1	600P005-40R2	600P005-40R3	600P005-40R4	600P005-40R5	600P005-40R6

BACKSHELL ASSEMBLY TOOLS

Glenair assembly tools accomplish proper tightening of adapters and backshells. Torque wrenches, soft jaw pliers, strap wrenches, and circular wrenches speed up assembly and prevent damage to connectors and backshells.



Interconnect Cable Assembly Tools Catalog has assembly tools, shield termination tools, fiber optic termination tools. Contact Glenair or go to www.glenair.com.



Series 970 PowerTrip™

Connectors and Accessories 850-311 Pin Contact Bus Bar/Lug


HOW TO ORDER				
Sample Part Number	850-311	-00	-A	-2
Basic Number	850-311 Pin Contact Bus Bar/Lug			
Contact Size	See Dimensions Table			
Termination Style	A = Internal Thread C = Lug			
Contact Plating	1 = Silver per ASTM B700, .0002 min over nickel 2 = Gold per ASTM B488, .000050 min over nickel			

MATERIAL AND FINISH

- Contact body: High conductivity copper alloy: See Dimensions Table

NOTES

- Contacts are intended to be installed into standard 970 Series powertrip plug and receptacle connectors




Contact Extension From Front Of Shell Flange. 970-003 Square Flange Housing Shown For Reference. Dimension Applies To Standard Length Connectors.

Orientation Of Contacts Shown For Reference. Contacts Are Not Keyed Into The Insert.

(TERMINATION STYLE A AND B) SUGGESTED HARDWARE TORQUE	
Thread Size	Torque (IN-LB)
5/16-24 UNF	90-140
10-32 UNF	20-29
8-36 UNF	11-19

Connectors and Accessories

850-311 Pin Contact Bus Bar/Lug



DIMENSIONS												
Part Number	Contact Size	Termination Style	$\varnothing A$	$\varnothing B$	C	D	E Flat (REF)	F Thread	G	H Max	J .025	
850-311-00-A-*	00	Internal Thread Style "A"	0.406 (10.31)	0.688 (17.48)	0.046 (1.17)	1.500 (38.10)	(1/2")	5/16-24 UNF 2B	0.539 (13.69)	N/A	1.356 (34.44)	1.231 (31.27)
850-311-0-A-*	0		0.357 (9.07)	0.613 (15.57)	0.046 (1.17)	1.376 (34.95)	(1/2")	5/16-24 UNF 2B	0.539 (13.69)		1.232 (31.29)	1.107 (28.12)
850-311-4-A-*	4		0.225 (5.72)	0.415 (10.54)	0.046 (1.17)	1.376 (34.95)	(5/16")	10-32 UNF 2B	0.460 (11.68)			
850-311-8-A-*	8		0.142 (3.61)	0.305 (7.75)	0.031 (0.79)	1.277 (32.44)	(1/4")	8-36 UNF 2B	0.407 (10.34)			
850-311-00-C-*	00	Lug Style "C"	0.406 (10.31)	0.688 (17.48)	0.046 (1.17)	2.640 (67.06)	N/A	N/A	N/A	N/A	2.496 (63.40)	2.371 (60.22)
850-311-0-C-*	0		0.357 (9.07)	0.613 (15.57)	0.046 (1.17)	2.406 (61.11)					2.262 (57.45)	2.137 (54.28)
850-311-4-C-*	4		0.225 (5.72)	0.415 (10.54)	0.046 (1.17)	2.122 (53.90)					1.978 (50.24)	1.853 (47.07)
850-311-8-C-*	8		0.142 (3.61)	0.305 (7.75)	0.031 (0.79)	1.889 (47.98)					1.844 (46.84)	1.719 (43.66)

DIMENSIONS				
Contact Size	Termination Style	K	$\varnothing L$	M Flat
00	Lug Style "C"	.120 (3.05)	.330 (8.38)	.946 (24.03)
0		.115 (2.92)	.330 (8.38)	.836 (21.23)
4		.085 (2.16)	.198 (5.03)	.552 (14.02)
8		.075 (1.90)	.173 (4.39)	.468 (11.89)

Series 970 PowerTrip™

Connectors and Accessories

850-312 Socket Contact Bus Bar/Lug


HOW TO ORDER				
Sample Part Number	850-312	-00	-A	-2
Basic Number	850-312 Socket Contact Bus Bar/Lug			
Contact Size	See Dimensions Table			
Termination Style	A = Internal Thread C = Lug			
Contact Plating	1 = Silver per ASTM B700, .0002 min over nickel 2 = Gold per ASTM B488, .000050 min over nickel			

MATERIAL AND FINISH

- Contact body: High conductivity copper alloy / see Dimensions table



NOTES

- Contacts are intended to be installed into standard 970 Series powertrip plug and receptacle connectors



INTERNAL THREAD

THROUGH HOLE LUG



Contact extension from front of shell flange. 970-003 Square flange housing shown for reference. Dimension applies to standard length connectors.

Orientation of contacts shown for reference. Contacts are not keyed into the insert.

(TERMINATION STYLE A AND B) SUGGESTED HARDWARE TORQUE	
Thread Size	Torque (IN-LB)
5/16-24 UNF	90-140
10-32	20-29
8-36 UNF	11-19


CONTACT CONNECTORS

Series 970 PowerTrip™



Connectors and Accessories

850-312 Socket Contact Bus Bar/Lug



DIMENSIONS												
Part Number	Contact Size	Termination Style	ϕA	ϕB	C	D	E Flat (REF)	F Thread	G	H Max	J.025	
850-311-00-A-*	00	Internal Thread Style "A"	0.406 (10.31)	0.688 (17.48)	0.046 (1.17)	1.500 (38.10)	(1/2")	5/16-24 UNF 2B	0.539 (13.69)	N/A	1.356 (34.44)	1.231 (31.27)
850-311-0-A-*	0		0.357 (9.07)	0.613 (15.57)	0.046 (1.17)	1.376 (34.95)	(1/2")	5/16-24 UNF 2B	0.539 (13.69)		1.232 (31.29)	1.107 (28.12)
850-311-4-A-*	4		0.225 (5.72)	0.415 (10.54)	0.046 (1.17)	1.376 (34.95)	(5/16")	10-32 UNF 2B	0.460 (11.68)			
850-311-8-A-*	8		0.142 (3.61)	0.305 (7.75)	0.031 (0.79)	1.277 (32.44)	(1/4")	8-36 UNF 2B	0.407 (10.34)			
850-311-00-C-*	00	Lug Style "C"	0.406 (10.31)	0.688 (17.48)	0.046 (1.17)	2.640 (67.06)	N/A	N/A	N/A	N/A	2.496 (63.40)	2.371 (60.22)
850-311-0-C-*	0		0.357 (9.07)	0.613 (15.57)	0.046 (1.17)	2.406 (61.11)					2.262 (57.45)	2.137 (54.28)
850-311-4-C-*	4		0.225 (5.72)	0.415 (10.54)	0.046 (1.17)	2.122 (53.90)					1.978 (50.24)	1.853 (47.07)
850-311-8-C-*	8		0.142 (3.61)	0.305 (7.75)	0.031 (0.79)	1.889 (47.98)					1.844 (46.84)	1.719 (43.66)

DIMENSIONS				
Contact Size	Termination Style	K	ϕL	M Flat
00	Lug Style "C"	.120 (3.05)	.330 (8.38)	.946 (24.03)
0		.115 (2.92)	.330 (8.38)	.836 (21.23)
4		.085 (2.16)	.198 (5.03)	.552 (14.02)
8		.075 (1.90)	.173 (4.39)	.468 (11.89)

BACKSHELLS AND ACCESSORIES FOR SERIES 970 CONNECTORS



Shrink Boot Adapters

These spin-coupling adapters are available in straight, 45° and 90° versions. Use with unshielded cable.

310-001 Page 52



EMI Band-Master™ Adapters

These spin-coupling banding adapters have a knurled platform for EMI shield attachment and boot groove.

440-069 Page 58



Heatshrink Boots

Rugged boots provide strain relief and environmental protection. Available in low-toxicity material.

770-003 Page 54



Strain Relief Clamp

Open frame cable clamp is designed for use with large, heavy power cable. Optional wire support bushing.

620PS076 Page 56



Submersible Backshell

Heavy duty environmental backshell features saddle clamp or wire mesh cordgrip for strain relief.

370-024 Page 60



EMI/RFI Backshell

Non-environmental backshell with ground rings for cable shield termination, heavy duty saddle bar clamp.

380-105 Page 64



Submersible EMI Backshell

Heavy duty environmental backshell features ground rings, silicone O-rings and cable gland.

390-055 Page 67



Submersible EMI Backshell

MIL-DTL-28840 type heavy duty backshell, straight exit, with saddle bar strain relief.

390PS036 Page 72



Submersible EMI Backshell

MIL-DTL-28840 type heavy duty backshell, straight exit, with wire mesh cord grip.

390PS086 Page 70



Protective Covers

Thread-on metal covers with a variety of attachments.

660PS097/098

Page 76




Bean Rubber Covers

Black rubber covers with multiple attachment styles.

780-001/002

Page 79



Mounting Gaskets

Elastomeric gaskets for square flange receptacles.

930-014

Page 74



Series 970 PowerTrip™ Connectors and Accessories

310-001 Heatshrink Boot Adapters

310-001 BOOT ADAPTERS



Attach Series 77 heatshrink boots to PowerTrip connectors with spin-coupling 310-001 boot adapters. These adapters feature self-locking ratchet to prevent loosening under vibration. Boot groove accepts standard lipped heatshrink boots.

How To Order Adapters with Boots

Add "T" to the adapter part numbers in the table below. The adapter and boot will be supplied as a kit.

Example: [310PS001ME18T](#)




Fig. 1
Straight (Style S)




Fig. 2
45° (Style M)




Fig. 3
90° (Style N)

HOW TO ORDER

FIG.	TYPE	SHELL SIZE	ALUMINUM WITH NICKEL PLATING (ME)	ALUMINUM WITH NICKEL-PTFE PLATING (MT)	ALUMINUM WITH OLIVE DRAB CADMIUM PLATING (NF)	ALUMINUM WITH BLACK ZINC-NICKEL PLATING (ZR)	PASSIVATED STAINLESS STEEL (Z1)
Fig. 1	Straight	18	310PS001ME18	310PS001MT18	310PS001NF18	310PS001ZR18	310PS001Z118
		20	310PS001ME20	310PS001MT20	310PS001NF20	310PS001ZR20	310PS001Z120
		24	310PS001ME24	310PS001MT24	310PS001NF24	310PS001ZR24	310PS001Z124
		28	310PS001ME28	310PS001MT28	310PS001NF28	310PS001ZR28	310PS001Z128
		32	310PS001ME32	310PS001MT32	310PS001NF32	310PS001ZR32	310PS001Z132
		36	310PS001ME36	310PS001MT36	310PS001NF36	310PS001ZR36	310PS001Z136
		40	310PS001ME40	310PS001MT40	310PS001NF40	310PS001ZR40	310PS001Z140
Fig. 2	45°	18	310PM001ME18	310PM001MT18	310PM001NF18	310PM001ZR18	310PM001Z118
		20	310PM001ME20	310PM001MT20	310PM001NF20	310PM001ZR20	310PM001Z120
		24	310PM001ME24	310PM001MT24	310PM001NF24	310PM001ZR24	310PM001Z124
		28	310PM001ME28	310PM001MT28	310PM001NF28	310PM001ZR28	310PM001Z128
		32	310PM001ME32	310PM001MT32	310PM001NF32	310PM001ZR32	310PM001Z132
		36	310PM001ME36	310PM001MT36	310PM001NF36	310PM001ZR36	310PM001Z136
		40	310PM001ME40	310PM001MT40	310PM001NF40	310PM001ZR40	310PM001Z140
Fig. 3	90°	18	310PN001ME18	310PN001MT18	310PN001NF18	310PN001ZR18	310PN001Z118
		20	310PN001ME20	310PN001MT20	310PN001NF20	310PN001ZR20	310PN001Z120
		24	310PN001ME24	310PN001MT24	310PN001NF24	310PN001ZR24	310PN001Z124
		28	310PN001ME28	310PN001MT28	310PN001NF28	310PN001ZR28	310PN001Z128
		32	310PN001ME32	310PN001MT32	310PN001NF32	310PN001ZR32	310PN001Z132
		36	310PN001ME36	310PN001MT36	310PN001NF36	310PN001ZR36	310PN001Z136
		40	310PN001ME40	310PN001MT40	310PN001NF40	310PN001ZR40	310PN001Z140


Series 970 PowerTrip™ Connectors and Accessories

Accessories

310-001 Heatshrink Boot Adapters



310-001 BOOT ADAPTERS



DIMENSIONS																			
Shell Size	A Thread	ø B Max.		C Max.		ø D Min.		ø E Max.		F Max.		G Max.		H Max.		J Max.		R Max.	
		In.	mm.	In.	mm.	In.	mm.	In.	mm.	In.	mm.	In.	mm.	In.	mm.	In.	mm.	In.	mm.
18	1.125-18 UNEF-2B	1.39	35.3	1.250	31.8	.724	18.4	1.005	25.5	.750	19.1	1.00	25.4	1.38	35.1	1.63	41.4	.88	22.4
20	1.250-18 UNEF-2B	1.53	38.9	1.250	31.8	.858	21.8	1.139	28.9	.812	20.6	1.06	26.9	1.50	38.1	1.75	44.5	1.00	25.4
24	1.4375-18 UNEF-2B	1.72	43.7	1.250	31.8	1.043	26.5	1.324	33.6	.937	23.8	1.19	30.2	1.75	44.5	2.00	50.8	1.25	31.8
28	1.8125-16 UN-2B	2.13	54.1	1.250	31.8	1.353	34.4	1.625	41.2	1.000	25.4	1.25	31.8	2.19	55.7	2.44	62.0	1.50	38.1
32	2.0625-16 UNS-2B	2.35	59.7	1.315	33.4	1.620	41.4	1.901	48.3	1.130	28.7	1.38	35.1	2.50	63.5	2.75	69.9	1.75	44.5
36	2.250-16 UN-2B	2.59	65.8	1.315	33.4	1.823	46.3	2.104	53.4	1.500	38.1	1.75	44.5	2.63	66.8	2.88	73.2	2.25	57.2
40	2.500-16 UN-2B	2.87	70.6	1.315	33.4	2.050	52.1	2.331	59.2	1.500	38.1	1.75	44.5	2.63	66.8	2.88	73.2	2.25	57.2

MATERIALS AND FINISHES
Coupling nut, backshell: aluminum or stainless steel. See How To Order for material & finish options.
Anti-decoupling spring, bushing: high-temperature thermoplastic

INSTALLATION TORQUE	
Shell Size	Recommended Installation Torque Inch-Pounds ± 5
18	116
20, 24	136
28, 32, 36	148
40	164



Series 970 PowerTrip™ Connectors and Accessories

770-003S Heatshrink Boots

HEATSHRINK BOOTS



About User-Installed Adhesive

Heat-shrink boots are not watertight unless equipped with pre-coated or user-installed adhesives. When heat is applied to the boot, the adhesive melts and fixes the boot to the adapter and cable jacket to provide the necessary sealing as well as mechanical strain-relief. For maximum performance Glenair recommends Type U user-installed two-part epoxy adhesive which offers reduced boot installation time and easier installation. Pre-coated boots require additional care to install because the boot must be heated sufficiently to activate the epoxy, at the risk of overheating the overall assembly. A single 50 ml duo syringe can coat many boots. The duo syringe can be re-capped for re-use. Inexpensive mixing nozzles must be discarded after each use.

NOTE: Glenair high-performance two part epoxy meets VG95343 part 15.

See next page for ordering information on user-installed two part epoxy adhesive.



Series 77 "Full Nelson" Shrink Boot Catalog has additional boot styles, technical information, installation instructions and other heatshrink products. Contact Glenair or go to www.glenair.com.

Heatshrink boots provide strain relief and environmental protection. Shape-memory polymer returns to as-molded shape when heat is applied. Use with 310-001 unshielded boot adapters or 440-069 **Band-Master™** EMI adapters. Boot lip fits adapter groove for precise fit. Semi-rigid high performance elastomer resists high temperature and withstands exposure to petroleum-based fluids and fuels. Also available with non-halogenated flame-retardant polyolefin for use where limited fire hazard is required.

MATERIAL SELECTION GUIDE

- 1 High Performance Elastomer** -75°C to +150°C. Semi-rigid high performance elastomer combines excellent resistance to fuels, oils and solvents with superior performance at extreme temperatures. Material meets the requirements of VG95343 Type 6, BSG 198-5-DE, EN62329-102 and SAE AS5258 Type H. These boots are recommended for demanding applications such as military vehicles and petrochemical exploration.
- 2 Zero Halogen Polyolefin** -30°C to +135°C. Low Smoke Zero Halogen (LSZH) polyolefin boots meet low smoke and toxicity requirements of shipboard, transit and aircraft systems. Oxygen index greater than 30%, smoke index less than 20, and toxicity index under 3 per 100 grams. Material meets requirements of NAVSEA 5617649, VG95343 Part 29, BSG 198-5-DF, EN62329-101 and SAE AS5258 Type G. Good resistance to oils, fuels and solvents.

PRE-COATED ADHESIVE SELECTION GUIDE

- W1 Low Smoke Zero halogen (LSZH) polyamide hot melt adhesive Coating.** Bonds well to a variety of substrates. Good creep resistance at elevated temperatures. Excellent bond strength at low temperature. Good resistance to fuels and oils. -55°C to +125°C. Compatible with Type 1 and Type 2 boot materials.
- R High Temperature Epoxy Adhesive Coating.** Glenair's highest performance pre-coated adhesive. The material requires careful installation using trained operators. -75°C to 150°C. Withstands prolonged high temperature immersion in fuels and oils. Excellent peel adhesion on a wide range of materials. *Compatible with Type 1 boot material only.*


HOW TO ORDER

SERIES	MATERIAL	BOOT SIZE	ADHESIVE LINING																																																							
770-003S Heatshrink Boot, Lipped, Straight	1 High Performance Elastomer, Semi-Rigid, -75°C to +150°C		<p>Omit for no adhesive lining.</p> <p>W1 Hot Melt Adhesive Low Smoke, Zero Halogen -55°C to +125°C</p> <p>R High Temperature Epoxy Adhesive -75°C to +150°C. <i>Use with Type 1 High Performance Elastomer only. Not for use with Type 2 material.</i></p>																																																							
				<p style="text-align: center;">Adapter Diameter</p> <table border="1"> <thead> <tr> <th>Boot Size</th> <th colspan="2">Inches</th> <th colspan="2">mm.</th> </tr> <tr> <th></th> <th>Min.</th> <th>Max.</th> <th>Min.</th> <th>Max.</th> </tr> </thead> <tbody> <tr> <td>02</td> <td>.350</td> <td>.600</td> <td>8.9</td> <td>15.2</td> </tr> <tr> <td>03</td> <td>.450</td> <td>.850</td> <td>11.4</td> <td>21.6</td> </tr> <tr> <td>04</td> <td>.600</td> <td>1.000</td> <td>15.2</td> <td>25.4</td> </tr> <tr> <td>05</td> <td>.750</td> <td>1.200</td> <td>19.1</td> <td>30.5</td> </tr> <tr> <td>06</td> <td>.900</td> <td>1.350</td> <td>22.9</td> <td>34.3</td> </tr> <tr> <td>07</td> <td>1.250</td> <td>1.650</td> <td>31.8</td> <td>41.9</td> </tr> <tr> <td>08</td> <td>1.400</td> <td>2.250</td> <td>35.6</td> <td>57.2</td> </tr> <tr> <td>09</td> <td>1.870</td> <td>2.470</td> <td>47.5</td> <td>62.7</td> </tr> <tr> <td>10</td> <td>2.400</td> <td>3.250</td> <td>61.0</td> <td>82.6</td> </tr> </tbody> </table>		Boot Size	Inches		mm.			Min.	Max.	Min.	Max.	02	.350	.600	8.9	15.2	03	.450	.850	11.4	21.6	04	.600	1.000	15.2	25.4	05	.750	1.200	19.1	30.5	06	.900	1.350	22.9	34.3	07	1.250	1.650	31.8	41.9	08	1.400	2.250	35.6	57.2	09	1.870	2.470	47.5	62.7	10	2.400	3.250
	Boot Size	Inches		mm.																																																						
		Min.		Max.	Min.	Max.																																																				
	02	.350		.600	8.9	15.2																																																				
	03	.450		.850	11.4	21.6																																																				
	04	.600		1.000	15.2	25.4																																																				
	05	.750		1.200	19.1	30.5																																																				
	06	.900		1.350	22.9	34.3																																																				
	07	1.250		1.650	31.8	41.9																																																				
	08	1.400		2.250	35.6	57.2																																																				
09	1.870	2.470	47.5	62.7																																																						
10	2.400	3.250	61.0	82.6																																																						
SAMPLE PART NUMBER																																																										
770-003S	2	06	R																																																							

Series 970 PowerTrip™ Connectors and Accessories Accessories 770-003S Heatshrink Boots




HEATSHRINK BOOT DIMENSIONS



Boot Size	A Min.		B Max.		C ± 20%		D ± 10%		E Ref.		F ± 30%		G Max.	
	In.	mm.	In.	mm.	In.	mm.	In.	mm.	In.	mm.	In.	mm.	In.	mm.
00	.354	9.0	.079	2.0	.028	0.7	.984	25.0	.551	14.0	.039	1.0	.217	5.5
01	.472	12.0	.118	3.0	.028	0.7	.984	25.0	.551	14.0	.043	1.1	.276	7.0
02	.669	17.0	.138	3.5	.028	0.7	1.181	30.0	.728	18.5	.051	1.3	.276	7.0
03	.945	24.0	.197	5.0	.035	0.9	1.496	38.0	.748	19.0	.063	1.6	.413	10.5
04	1.181	30.0	.236	6.0	.039	1.0	2.165	55.0	1.181	30.0	.071	1.8	.551	14.0
05	1.260	32.0	.276	7.0	.047	1.2	2.638	67.0	1.299	33.0	.071	1.8	.709	18.0
06	1.417	36.0	.335	8.5	.047	1.2	3.150	80.0	1.575	40.0	.079	2.0	.866	22.0
07	1.693	43.0	.394	10.0	.051	1.3	3.898	99.0	2.165	55.0	.087	2.2	1.102	28.0
08	2.362	60.0	.591	15.0	.063	1.6	5.118	130.0	1.969	50.0	.130	3.3	1.378	35.0
09	2.599	66.0	.661	16.8	.079	2.0	6.693	170.0	3.543	90.0	.150	3.8	1.752	44.5
10	3.400	86.4	1.060	26.9	.130	3.3	7.700	195.6	4.005	102.0	.160	4.1	2.250	57.2

BOOT IDENTIFICATION MARKING

Heatshrink boots are identified with molded-in lettering. This lettering shows the boot type, boot size and orientation. Position the boot so that the lipped "A" end is toward the adapter and the "C" end is toward the cable. Assembly instructions are in the **Series 77 "Full Nelson" Environmental Shrink Boots** catalog, available at www.glenair.com.



USER-INSTALLED BOOT ADHESIVE, DISPENSING GUN AND MIXING NOZZLE



Part Number
779-001



Part Number
779-002



Part Number	Count Per Pack
779-003	12

High performance flexible two part thermoset epoxy provides high strength flexible bond from -55° to 150°C. 50 ml duo syringe fits standard dispensing guns. Use with square green mixing nozzle sold separately. 12 hour cure time at 20°C, 1 hour at 85°C, 30 minutes at 150°C. Apply to inside of boot with wooden spatula. 18 month shelf life.

Twin push-rod 1:1 ratio epoxy dispensing gun for use with duo syringe epoxy and mixing nozzle sold separately. Durable heavy-duty plastic. Gun type hand grip with ratcheting trigger to advance push-rods.

1:1 ratio mixing nozzle attaches to duo syringe with 1/2 turn and locks into place. Nozzle provides consistent mixing of resin and hardener. Kit consists of (12) nozzles.



Series 970 PowerTrip™ Connectors and Accessories Accessories 620PS076 Strain Relief Clamp

620PS076 STRAIN RELIEF CLAMP



Spin coupling strain relief clamp with anti-decoupling ratchet prevents loosening under vibration. Fits standard Series 970 connectors. Heavy duty saddle clamp with telescoping screws. Available rigid dielectric bushing provides additional wire support. Aluminum alloy or stainless steel coupling nut, cable clamp and saddle bars. Stainless steel screws, high temperature thermoplastic anti-decoupling device and wire support bushing.

Optional **Wire Support Bushing** holds wires in place to prevent contact splay or grommet distortion. **Not available for layouts with size #12 or #16 contacts.**



HOW TO ORDER

SHELL SIZE	WIRE SUPPORT BUSHING	LAYOUT	MATERIAL/FINISH OPTION				
			ALUM/ NICKEL (ME)	ALUM/ NICKEL-PTFE (MT)	ALUM/ OD CADMIUM (NF)	ALUM/ BLACK ZINC- NICKEL (ZR)	SST/ PASSIVATE (Z1)
18	No Bushing	All	620PS076ME18	620PS076MT18	620PS076NF18	620PS076ZR18	620PS076Z118
	Bushing Included	18-2	620PS076ME18B2	620PS076MT18B2	620PS076NF18B2	620PS076ZR18B2	620PS076Z118B2
20	No Bushing	All	620PS076ME20	620PS076MT20	620PS076NF20	620PS076ZR20	620PS076Z120
	Bushing Included	20-3	620PS076ME20B3	620PS076MT20B3	620PS076NF20B3	620PS076ZR20B3	620PS076Z120B3
		20-4	620PS076ME20B4	620PS076MT20B4	620PS076NF20B4	620PS076ZR20B4	620PS076Z120B4
24	No Bushing	All	620PS076ME24	620PS076MT24	620PS076NF24	620PS076ZR24	620PS076Z124
	Bushing Included	24-2	620PS076ME24B2	620PS076MT24B2	620PS076NF24B2	620PS076ZR24B2	620PS076Z124B2
		24-3	620PS076ME24B3	620PS076MT24B3	620PS076NF24B3	620PS076ZR24B3	620PS076Z124B3
		24-5	620PS076ME24B5	620PS076MT24B5	620PS076NF24B5	620PS076ZR24B5	620PS076Z124B5
28	No Bushing	All	620PS076ME28	620PS076MT28	620PS076NF28	620PS076ZR28	620PS076Z128
	Bushing Included	28-4	620PS076ME28B4	620PS076MT28B4	620PS076NF28B4	620PS076ZR28B4	620PS076Z128B4
32	No Bushing	All	620PS076ME32	620PS076MT32	620PS076NF32	620PS076ZR32	620PS076Z132
	Bushing Included	32-2	620PS076ME32B2	620PS076MT32B2	620PS076NF32B2	620PS076ZR32B2	620PS076Z132B2
		32-3	620PS076ME32B3	620PS076MT32B3	620PS076NF32B3	620PS076ZR32B3	620PS076Z132B3
		32-5	620PS076ME32B5	620PS076MT32B5	620PS076NF32B5	620PS076ZR32B5	620PS076Z132B5
36	No Bushing	All	620PS076ME36	620PS076MT36	620PS076NF36	620PS076ZR36	620PS076Z136
	Bushing Included	36-4	620PS076ME36B4	620PS076MT36B4	620PS076NF36B4	620PS076ZR36B4	620PS076Z136B4
40	No Bushing	All	620PS076ME40	620PS076MT40	620PS076NF40	620PS076ZR40	620PS076Z140
	Bushing Included	40-5	620PS076ME40B5	620PS076MT40B5	620PS076NF40B5	620PS076ZR40B5	620PS076Z140B5

MATERIAL & FINISH SELECTION GUIDE


Property	Alum/ Nickel (ME)	Alum/ Nickel-PTFE (MT)	Alum/ Olive Drab Cadmium (NF)	Alum/ Black Zinc-Nickel (ZR)	SST/ Passivate
Corrosion Resistance	Fair	Excellent	Excellent	Excellent	Excellent
Temperature Range	-65°C to +200°C	-65°C to +200°C	-65°C to +175°C	-65°C to +175°C	-65°C to +200°C
Salt Spray Hours	96	1000	1000	1000	2000
Conductivity	Excellent	Excellent	Good	Good	Fair
Relative Cost	\$\$	\$\$\$	\$\$	\$\$\$	\$\$\$\$
RoHS Compliant*	Yes	Yes	No	Yes	Yes

* Does not contain cadmium or hexavalent chromium. Meets EU requirements.


Series 970 PowerTrip™ Connectors and Accessories
Accessories
 620PS076 Strain Relief Clamp



620PS076 STRAIN RELIEF CLAMP



DIMENSIONS											
Shell Size	A Thread	Ø B Max.		C ± .031 (0.79)		D Max.		E Max.		F Ref.	
		In.	mm.	In.	mm.	In.	mm.	In.	mm.	In.	mm.
18	1.125-18 UNEF-2B	1.39	35.3	.438	11.13	1.500	38.10	1.83	46.48	.63	16.0
20	1.250-18 UNEF-2B	1.53	38.9	.625	15.88	1.687	42.85	1.83	46.48	.63	16.0
24	1.4375-18 UNEF-2B	1.72	43.7	.688	17.48	1.921	48.79	2.03	51.56	.63	16.0
28	1.8125-16 UN-2B	2.13	54.1	.938	23.83	2.355	59.82	2.13	54.10	.63	16.0
32	2.0625-16 UNS-2B	2.35	59.7	1.062	26.97	2.716	68.99	2.53	64.26	.75	19.1
36	2.250-16 UN-2B	2.59	65.8	1.438	36.53	2.869	72.87	2.53	64.26	.75	19.1
40	2.500-16 UN-2B	2.87	70.6	1.438	36.53	3.066	77.88	2.53	64.26	.75	19.1



BUSHING DIMENSIONS		
Wire Size	X Ref.	
	In.	mm.
#8 AWG	.217	5.51
#4 AWG	.331	8.41
#1/0 AWG	.500	12.70

MATERIALS AND FINISHES
Coupling nut, clamp, saddle bars: aluminum or stainless steel. See <i>How To Order</i> for material & finish options.
Anti-decoupling spring: high-temperature thermoplastic
Wire support bushing: high-temperature thermoplastic

INSTALLATION TORQUE	
Shell Size	Recommended Installation Torque Inch-Pounds ± 5
18	116
20, 24	136
28, 32, 36	148
40	164





Series 970 PowerTrip™ Connectors and Accessories Accessories

440-069 EMI/RFI Adapter

440-069 EMI/RFI ADAPTER, BAND-MASTER™ SHIELD TERMINATION

Spin coupling EMI/RFI adapter with anti-decoupling ratchet prevents loosening under vibration. Fits standard Series 970 connectors. Terminate cable shield to backshell with **Band-Master™ ATS** (Advanced Termination System) stainless steel band. Optional heatshrink boot provides strain relief and environmental seal. Backshell features splined connector interface for improved mechanical and electrical performance.










MATERIALS AND FINISHES

Adapter: aluminum or stainless steel. See **How To Order** for material & finish options.
Anti-decoupling spring: high-grade engineering thermoplastic

INSTALLATION TORQUE

Shell Size	Recommended Installation Torque Inch-Pounds ± 5
18	116
20, 24	136
28, 32, 36	148
40	164

HOW TO ORDER


SERIES	SHELL MATERIAL / FINISH	SHELL SIZE	CABLE ENTRY CODE	LENGTH CODE	OPTIONAL BAND STRAP	OPTIONAL SHRINK BOOT																																											
440PS069 Straight Exit 	ME Aluminum / Electroless Nickel RoHS Compliant NF Aluminum / Cadmium with Olive Drab Chromate	18 20 24 28 32 36 40		Omit for 45° and 90° styles. The Length Code is the length of the adapter in ½ inch increments. Minimum length is 2 inches.	K Adapter supplied with pre-coiled stainless steel shield termination band Omit if bands will be purchased separately. Refer to Band-Master strap and tool ordering information in this catalog.	T Adapter supplied with standard heatshrink boot. S Adapter supplied with low-smoke, zero halogen heatshrink boot. Omit if boots will be purchased separately. Refer to heatshrink boot ordering information in this catalog.																																											
							<table border="1"> <thead> <tr> <th colspan="2">Cable Entry</th> </tr> <tr> <th>Code</th> <th>In. mm.</th> </tr> </thead> <tbody> <tr><td>02</td><td>.250 6.4</td></tr> <tr><td>03</td><td>.375 9.5</td></tr> <tr><td>04</td><td>.500 12.7</td></tr> <tr><td>05</td><td>.625 15.9</td></tr> <tr><td>06</td><td>.750 19.1</td></tr> <tr><td>07</td><td>.875 22.2</td></tr> <tr><td>08</td><td>1.000 25.4</td></tr> <tr><td>09</td><td>1.125 28.6</td></tr> <tr><td>10</td><td>1.250 31.8</td></tr> <tr><td>11</td><td>1.375 34.9</td></tr> <tr><td>12</td><td>1.500 38.1</td></tr> <tr><td>13</td><td>1.625 41.3</td></tr> <tr><td>14</td><td>1.750 44.5</td></tr> <tr><td>15</td><td>1.875 47.6</td></tr> <tr><td>16</td><td>2.000 50.8</td></tr> <tr><td>17</td><td>2.125 54.0</td></tr> <tr><td>18</td><td>2.250 57.2</td></tr> <tr><td>19</td><td>2.375 60.3</td></tr> <tr><td>20</td><td>2.500 63.5</td></tr> </tbody> </table>	Cable Entry		Code	In. mm.	02	.250 6.4	03	.375 9.5	04	.500 12.7	05	.625 15.9	06	.750 19.1	07	.875 22.2	08	1.000 25.4	09	1.125 28.6	10	1.250 31.8	11	1.375 34.9	12	1.500 38.1	13	1.625 41.3	14	1.750 44.5	15	1.875 47.6	16	2.000 50.8	17	2.125 54.0	18	2.250 57.2	19	2.375 60.3	20	2.500 63.5
Cable Entry																																																	
Code	In. mm.																																																
02	.250 6.4																																																
03	.375 9.5																																																
04	.500 12.7																																																
05	.625 15.9																																																
06	.750 19.1																																																
07	.875 22.2																																																
08	1.000 25.4																																																
09	1.125 28.6																																																
10	1.250 31.8																																																
11	1.375 34.9																																																
12	1.500 38.1																																																
13	1.625 41.3																																																
14	1.750 44.5																																																
15	1.875 47.6																																																
16	2.000 50.8																																																
17	2.125 54.0																																																
18	2.250 57.2																																																
19	2.375 60.3																																																
20	2.500 63.5																																																
440PM069 45° Exit 	NFP Aluminum / Cadmium with Olive Drab Chromate, Nickel-plated Shield Termination Area, Polysulfide Barrier (See Application Note) ZR Aluminum / Zinc-Nickel with Non-Reflective Black Chromate RoHS Compliant	18 20 24 28 32 36 40		<table border="1"> <thead> <tr> <th rowspan="2">Code</th> <th colspan="2">Length</th> </tr> <tr> <th>In.</th> <th>mm.</th> </tr> </thead> <tbody> <tr><td>-4</td><td>2.0</td><td>51</td></tr> <tr><td>-5</td><td>2.5</td><td>64</td></tr> <tr><td>-6</td><td>3.0</td><td>76</td></tr> <tr><td>-7</td><td>3.5</td><td>89</td></tr> <tr><td>-8</td><td>4.0</td><td>102</td></tr> <tr><td>-9</td><td>4.5</td><td>114</td></tr> <tr><td>-10</td><td>5.0</td><td>127</td></tr> <tr><td>-11</td><td>5.5</td><td>140</td></tr> <tr><td>-12</td><td>6.0</td><td>152</td></tr> <tr><td>-13</td><td>6.5</td><td>165</td></tr> <tr><td>-14</td><td>7.0</td><td>178</td></tr> <tr><td>-15</td><td>7.5</td><td>191</td></tr> <tr><td>-16</td><td>8.0</td><td>203</td></tr> </tbody> </table>	Code	Length		In.	mm.	-4	2.0	51	-5	2.5	64	-6	3.0	76	-7	3.5	89	-8	4.0	102	-9	4.5	114	-10	5.0	127	-11	5.5	140	-12	6.0	152	-13	6.5	165	-14	7.0	178	-15	7.5	191	-16	8.0	203	 
						Code	Length																																										
In.	mm.																																																
-4	2.0	51																																															
-5	2.5	64																																															
-6	3.0	76																																															
-7	3.5	89																																															
-8	4.0	102																																															
-9	4.5	114																																															
-10	5.0	127																																															
-11	5.5	140																																															
-12	6.0	152																																															
-13	6.5	165																																															
-14	7.0	178																																															
-15	7.5	191																																															
-16	8.0	203																																															
440PN069 90° Exit 	MT Aluminum / Nickel-PTFE RoHS Compliant Z1 Stainless Steel / Passivated RoHS Compliant																																																
Sample Part Number																																																	
440PH069	NF	24	07																																														

Series 970 PowerTrip™ Connectors and Accessories
Accessories
440-069 EMI/RFI Adapter




440-069 EMI/RFI ADAPTER, BAND-MASTER™ SHIELD TERMINATION

Shell Size	A Thread	ø B Max.		ø X Min.	
		In.	mm.	In.	mm.
18	1.125-18 UNEF-2B	1.39	35.3	.724	18.4
20	1.250-18 UNEF-2B	1.53	38.9	.858	21.8
24	1.4375-18 UNEF-2B	1.72	43.7	1.043	26.5
28	1.8125-16 UN-2B	2.13	54.1	1.353	34.4
32	2.0625-16 UNS-2B	2.35	59.7	1.620	41.2
36	2.250-16 UN-2B	2.59	65.8	1.823	46.3
40	2.500-16 UN-2B	2.87	70.6	2.050	52.1




45° AND 90° DIMENSIONS



Shell Size	C Max.		D Max.		E Max.		F Max.	
	In.	mm.	In.	mm.	In.	mm.	In.	mm.
18	1.250	31.8	2.468	62.7	1.906	48.4	1.812	46.0
20	1.312	33.3	2.657	67.5	2.031	51.6	1.938	49.2
24	1.406	35.7	3.063	77.8	2.281	57.9	2.188	55.6
28	1.500	38.1	3.656	92.9	2.531	64.3	2.625	66.7
32	1.675	42.5	3.845	97.7	2.625	66.7	2.895	73.5
36	1.799	45.7	4.230	107.4	2.875	73.0	3.145	79.9
40	1.861	47.3	4.459	113.3	3.025	76.8	3.295	83.7

CABLE ENTRY DIMENSIONS



Cable Entry Code	ø N		ø P		ø R		Heatshrink Boot Ref.*
	In.	mm.	In.	mm.	In.	mm.	
02	.250	6.4	.375	9.53	.437	11.10	770-003S112
03	.375	9.5	.500	12.70	.562	14.27	770-001S103
04	.500	12.7	.625	15.88	.687	17.45	770-001S104
05	.625	15.9	.750	19.05	.812	20.62	770-001S104
06	.750	19.1	.875	22.23	.937	23.80	770-001S105
07	.875	22.2	1.000	25.40	1.062	26.97	770-001S105
08	1.000	25.4	1.125	28.58	1.187	30.15	770-001S106
09	1.125	28.6	1.250	31.75	1.312	33.32	770-001S107
10	1.250	31.8	1.375	34.93	1.437	36.50	770-001S107
11	1.375	34.9	1.500	38.10	1.562	39.67	770-001S107
12	1.500	38.1	1.625	41.28	1.687	42.85	770-001S108
13	1.625	41.3	1.750	44.45	1.812	46.02	770-001S108
14	1.750	44.5	1.875	47.63	1.937	49.20	770-001S108
15	1.875	47.6	2.000	50.80	2.062	52.37	770-001S109
16	2.000	50.8	2.125	53.98	2.187	55.55	770-001S109
17	2.125	54.0	2.250	57.15	2.313	58.75	770-003S110
18	2.250	57.2	2.375	60.37	2.438	61.93	770-003S110
19	2.375	60.3	2.500	63.50	2.563	65.10	770-003S110
20	2.500	63.5	2.625	66.68	2.688	68.28	770-003S110

* Heatshrink boot part number specifies standard material. For low-smoke, zero halogen change "S1" to "S2".




Series 970 PowerTrip™ Connectors and Accessories Accessories

440-069 EMI/RFI Adapter

ALTERNATE CONFIGURATION FOR LARGE CABLES

If the cable entry diameter exceeds the diameter of the backshell shown in the table at right, the backshell will be supplied with a **transition adapter**. The clamp and adapters are first installed over the cable jacket, and then are threaded onto the transition adapter. On straight exit backshells, the transition adapter does not affect the length. On 45° and 90° versions the transition adapter adds 1.00 inch (25.4mm) maximum to the backshell length.

Shell Size	Backshell Inside Diameter	
	In.	mm.
18	.72	18.3
20	.85	21.7
24	1.04	26.4
28	1.35	34.3
32	1.62	41.1
36	1.82	46.3
40	2.05	52.0




APPLICATION NOTE: POLYSULFIDE BARRIER FOR GALVANIC CORROSION PROTECTION

Olive drab (OD) cadmium (Cd) over electroless nickel (EN) is available in two versions. The standard version, designated as Glenair code **NF**, is a uniform Cd/EN finish over the entire part. A second version, designated as Glenair code **NFP**, is selectively plated with electroless nickel in the knurled shield attachment area. A polysulfide barrier separates the electroless nickel area from the cadmium plated area. This selectively plated version prevents galvanic corrosion that could potentially occur if nickel-coated shield braid is attached to a cadmium plated surface.

The Polysulfide Process

First, the part is plated with electroless nickel. Next, a tape mask is applied to the shield termination area. Following cadmium plating and chromate conversion coating, the tape is removed, exposing the electroless nickel. Polysulfide is applied with a brush to completely seal the transition area between the nickel and cadmium. The final step is to oven cure the polysulfide.



Series 970 PowerTrip™ Connectors and Accessories

Accessories

370-024 Submersible Backshell



SUBMERSIBLE BACKSHELL









Heavy duty backshell features positive detent self-locking spin coupling for high vibration environments. For use with unshielded, jacketed power cable. Splined connector interface. Heavy duty cable clamps fit most cable sizes, or choose wire mesh stainless steel cordgrip. Withstands six feet water immersion for 48 hours. Aluminum or stainless steel with silicone gland. Stainless steel telescoping clamp screws. Meets environmental, electrical and mechanical requirements of AS85049 Category 1A Heavy Duty.

MATERIALS AND FINISHES
Adapters, elbows, follower, coupling nut: aluminum or stainless steel. See How To Order for material & finish options.
Hardware: stainless steel
Wire Mesh Cordgrip: stainless steel
Screws: stainless steel
Grommet, O-rings: fluorosilicone

INSTALLATION TORQUE	
Shell Size	Recommended Installation Torque Inch-Pounds ± 5
18	116
20, 24	136
28, 32, 36	148
40	164

HOW TO ORDER


SERIES	SHELL MATERIAL / FINISH	SHELL SIZE	CABLE ENTRY CODE	LENGTH CODE																																																																
370PS024 Straight Exit 	ME Aluminum / Electroless Nickel RoHS Compliant NF Aluminum / Cadmium with Olive Drab Chromate ZR Aluminum / Zinc-Nickel with Non-Reflective Black Chromate RoHS Compliant	18 20 24 28 32 36 40	 Saddle Clamp	(Omit for 45° and 90° styles. Applies to 370PS024 straight exit only) The Length Code is the length of the adapter in 1/2 inch increments <table border="1"> <thead> <tr> <th rowspan="2">Code</th> <th colspan="2">Length</th> </tr> <tr> <th>In.</th> <th>mm.</th> </tr> </thead> <tbody> <tr><td>6</td><td>3.0</td><td>76</td></tr> <tr><td>7</td><td>3.5</td><td>89</td></tr> <tr><td>8</td><td>4.0</td><td>102</td></tr> <tr><td>9</td><td>4.5</td><td>114</td></tr> <tr><td>10</td><td>5.0</td><td>127</td></tr> <tr><td>11</td><td>5.5</td><td>140</td></tr> <tr><td>12</td><td>6.0</td><td>152</td></tr> <tr><td>13</td><td>6.5</td><td>165</td></tr> <tr><td>14</td><td>7.0</td><td>178</td></tr> <tr><td>15</td><td>7.5</td><td>191</td></tr> <tr><td>16</td><td>8.0</td><td>203</td></tr> </tbody> </table>	Code	Length		In.	mm.	6	3.0	76	7	3.5	89	8	4.0	102	9	4.5	114	10	5.0	127	11	5.5	140	12	6.0	152	13	6.5	165	14	7.0	178	15	7.5	191	16	8.0	203																										
						Code	Length																																																													
					In.		mm.																																																													
					6	3.0	76																																																													
7	3.5	89																																																																		
8	4.0	102																																																																		
9	4.5	114																																																																		
10	5.0	127																																																																		
11	5.5	140																																																																		
12	6.0	152																																																																		
13	6.5	165																																																																		
14	7.0	178																																																																		
15	7.5	191																																																																		
16	8.0	203																																																																		
370PM024 45° Exit 	MT Aluminum / Nickel-PTFE RoHS Compliant Z1 Stainless Steel / Passivated RoHS Compliant	18 20 24 28 32 36 40	 Wire Mesh Cordgrip	<table border="1"> <thead> <tr> <th rowspan="2">Code</th> <th colspan="2">Cable Diameter Min.</th> <th colspan="2">Cable Diameter Max.</th> </tr> <tr> <th>In.</th> <th>mm.</th> <th>In.</th> <th>mm.</th> </tr> </thead> <tbody> <tr><td>06H</td><td>.250</td><td>6.4</td><td>.437</td><td>11.1</td></tr> <tr><td>08H</td><td>.387</td><td>9.8</td><td>.562</td><td>14.3</td></tr> <tr><td>10H</td><td>.350</td><td>8.9</td><td>.625</td><td>15.9</td></tr> <tr><td>12H</td><td>.500</td><td>12.7</td><td>.750</td><td>19.1</td></tr> <tr><td>16H</td><td>.625</td><td>15.9</td><td>.937</td><td>23.8</td></tr> <tr><td>20H</td><td>.875</td><td>22.2</td><td>1.250</td><td>31.8</td></tr> <tr><td>24H</td><td>1.000</td><td>25.4</td><td>1.375</td><td>34.9</td></tr> <tr><td>28H</td><td>1.250</td><td>31.8</td><td>1.625</td><td>41.3</td></tr> <tr><td>32H</td><td>1.437</td><td>36.5</td><td>1.875</td><td>47.6</td></tr> <tr><td>36H</td><td>1.625</td><td>41.3</td><td>2.125</td><td>54.0</td></tr> <tr><td>40H</td><td>1.875</td><td>47.6</td><td>2.375</td><td>60.3</td></tr> </tbody> </table>	Code	Cable Diameter Min.		Cable Diameter Max.		In.	mm.	In.	mm.	06H	.250	6.4	.437	11.1	08H	.387	9.8	.562	14.3	10H	.350	8.9	.625	15.9	12H	.500	12.7	.750	19.1	16H	.625	15.9	.937	23.8	20H	.875	22.2	1.250	31.8	24H	1.000	25.4	1.375	34.9	28H	1.250	31.8	1.625	41.3	32H	1.437	36.5	1.875	47.6	36H	1.625	41.3	2.125	54.0	40H	1.875	47.6	2.375	60.3
						Code	Cable Diameter Min.		Cable Diameter Max.																																																											
					In.		mm.	In.	mm.																																																											
					06H	.250	6.4	.437	11.1																																																											
08H	.387	9.8	.562	14.3																																																																
10H	.350	8.9	.625	15.9																																																																
12H	.500	12.7	.750	19.1																																																																
16H	.625	15.9	.937	23.8																																																																
20H	.875	22.2	1.250	31.8																																																																
24H	1.000	25.4	1.375	34.9																																																																
28H	1.250	31.8	1.625	41.3																																																																
32H	1.437	36.5	1.875	47.6																																																																
36H	1.625	41.3	2.125	54.0																																																																
40H	1.875	47.6	2.375	60.3																																																																
370PN024 90° Exit 	MT Aluminum / Nickel-PTFE RoHS Compliant Z1 Stainless Steel / Passivated RoHS Compliant	18 20 24 28 32 36 40	 Wire Mesh Cordgrip	<table border="1"> <thead> <tr> <th rowspan="2">Code</th> <th colspan="2">Cable Diameter Min.</th> <th colspan="2">Cable Diameter Max.</th> </tr> <tr> <th>In.</th> <th>mm.</th> <th>In.</th> <th>mm.</th> </tr> </thead> <tbody> <tr><td>06K</td><td>.310</td><td>7.8</td><td>.438</td><td>11.1</td></tr> <tr><td>08K</td><td>.438</td><td>11.1</td><td>.500</td><td>12.7</td></tr> <tr><td>10K</td><td>.500</td><td>12.7</td><td>.625</td><td>15.8</td></tr> <tr><td>12K</td><td>.625</td><td>15.9</td><td>.750</td><td>19.1</td></tr> <tr><td>14K</td><td>.750</td><td>19.1</td><td>.875</td><td>22.2</td></tr> <tr><td>16K</td><td>.875</td><td>22.2</td><td>1.000</td><td>25.4</td></tr> <tr><td>20K</td><td>1.000</td><td>25.4</td><td>1.250</td><td>31.8</td></tr> <tr><td>24K</td><td>1.125</td><td>28.6</td><td>1.375</td><td>34.9</td></tr> <tr><td>28K</td><td>1.375</td><td>34.9</td><td>1.625</td><td>41.2</td></tr> <tr><td>32K</td><td>1.625</td><td>41.3</td><td>1.875</td><td>47.6</td></tr> <tr><td>40K</td><td>2.125</td><td>53.9</td><td>2.375</td><td>60.3</td></tr> </tbody> </table>	Code	Cable Diameter Min.		Cable Diameter Max.		In.	mm.	In.	mm.	06K	.310	7.8	.438	11.1	08K	.438	11.1	.500	12.7	10K	.500	12.7	.625	15.8	12K	.625	15.9	.750	19.1	14K	.750	19.1	.875	22.2	16K	.875	22.2	1.000	25.4	20K	1.000	25.4	1.250	31.8	24K	1.125	28.6	1.375	34.9	28K	1.375	34.9	1.625	41.2	32K	1.625	41.3	1.875	47.6	40K	2.125	53.9	2.375	60.3
						Code	Cable Diameter Min.		Cable Diameter Max.																																																											
					In.		mm.	In.	mm.																																																											
					06K	.310	7.8	.438	11.1																																																											
08K	.438	11.1	.500	12.7																																																																
10K	.500	12.7	.625	15.8																																																																
12K	.625	15.9	.750	19.1																																																																
14K	.750	19.1	.875	22.2																																																																
16K	.875	22.2	1.000	25.4																																																																
20K	1.000	25.4	1.250	31.8																																																																
24K	1.125	28.6	1.375	34.9																																																																
28K	1.375	34.9	1.625	41.2																																																																
32K	1.625	41.3	1.875	47.6																																																																
40K	2.125	53.9	2.375	60.3																																																																
Sample Part Number																																																																				
370PS024	MT	32	20H	10																																																																




Series 970 PowerTrip™ Connectors and Accessories Accessories 370-024 Submersible Backshell

SUBMERSIBLE BACKSHELL: 370PS024 STRAIGHT EXIT

Shell Size	A Thread	ø B Max.	
		In.	mm.
18	1.125-18 UNEF-2B	1.39	35.3
20	1.250-18 UNEF-2B	1.53	38.9
24	1.4375-18 UNEF-2B	1.72	43.7
28	1.8125-16 UN-2B	2.13	54.1
32	2.0625-16 UNS-2B	2.35	59.7
36	2.250-16 UN-2B	2.59	65.8
40	2.500-16 UN-2B	2.87	70.6




370PM024 45° EXIT DIMENSIONS



Shell Size	A Thread Class 2B	ø B Max.		C Max.		D Max.	
		In.	mm.	In.	mm.	In.	mm.
18	1.125-18 UNEF	1.39	35.3	1.250	31.8	2.468	62.7
20	1.250-18 UNEF	1.53	38.9	1.312	33.3	2.657	67.5
24	1.4375-18 UNEF	1.72	43.7	1.406	35.7	3.063	77.8
28	1.8125-16 UN	2.13	54.1	1.500	38.1	3.656	92.9
32	2.0625-16 UNS	2.35	59.7	1.675	42.5	3.845	97.7
36	2.250-16 UN	2.59	65.8	1.799	45.7	4.230	107.4
40	2.500-16 UN	2.87	70.6	1.861	47.3	4.459	113.3

370PN024 90° EXIT




Shell Size	A Thread Class 2B	ø B Max.		E Max.		F Max.	
		In.	mm.	In.	mm.	In.	mm.
18	1.125-18 UNEF	1.39	35.3	1.906	48.4	1.812	46.0
20	1.250-18 UNEF	1.53	38.9	2.031	51.6	1.938	49.2
24	1.4375-18 UNEF	1.72	43.7	2.281	57.9	2.188	55.6
28	1.8125-16 UN	2.13	54.1	2.531	64.3	2.625	66.7
32	2.0625-16 UNS	2.35	59.7	2.625	66.7	2.895	73.5
36	2.250-16 UN	2.59	65.8	2.875	73.0	3.145	79.9
40	2.500-16 UN	2.87	70.6	3.025	76.8	3.295	83.7

Series 970 PowerTrip™ Connectors and Accessories

370-024 Submersible Backshell




SADDLE CLAMP DIMENSIONS



Clamp Size	Cable Range				A Thread Class 2B	B Max.		C Max.	
	Min. In.	Min. mm.	Max. In.	Max. mm.		In.	mm.	In.	mm.
06H	.250	6.4	.437	11.1	.750-20UNEF	1.301	33.04	1.145	29.1
08H	.387	9.8	.562	14.3	.875-20UNEF	1.301	33.04	1.332	33.8
10H	.350	8.9	.625	15.9	1.000-20UNEF	1.301	33.04	1.332	33.8
12H	.500	12.7	.750	19.1	1.1875-18UNEF	1.332	33.83	1.551	39.4
16H	.625	15.9	.937	23.8	1.4375-18UNEF	1.426	36.22	1.770	45.0
20H	.875	22.2	1.250	31.8	1.750-18UNS	1.613	40.97	2.113	53.7
24H	1.000	25.4	1.375	34.9	2.000-18UNS	1.645	41.78	2.363	60.0
28H	1.250	31.8	1.625	41.3	2.250-16UN	1.920	48.77	2.770	70.4
32H	1.437	36.5	1.875	47.6	2.500-16UN	1.920	48.77	3.020	76.7
36H	1.625	41.3	2.125	54.0	2.750-16UN	2.060	53.32	3.250	82.6
40H	1.875	47.6	2.375	60.3	3.000-16UN	2.060	53.32	3.500	88.9

WIRE MESH GRIP DIMENSIONS




Grip Size	Cable Range				Ø A Max.		B Approx.	
	Min. In.	Min. mm.	Max. In.	Max. mm.	In.	mm.	In.	mm.
06K	.310	7.8	.438	11.1	.942	23.9	4.000	101
08K	.438	11.1	.500	12.7	1.067	27.1	4.120	105
10K	.500	12.7	.625	15.8	1.192	30.3	4.370	111
12K	.625	15.9	.750	19.1	1.380	35.1	5.000	127
14K	.750	19.1	.875	22.2	1.563	39.7	6.000	152
16K	.875	22.2	1.000	25.4	1.563	39.7	6.250	158
20K	1.000	25.4	1.250	31.8	1.875	47.6	7.250	184
24K	1.125	28.6	1.375	34.9	2.225	57.3	8.000	203
28K	1.375	34.9	1.625	41.2	2.505	63.6	8.500	216
32K	1.625	41.3	1.875	47.6	2.755	70.0	9.000	229
40K	2.125	53.9	2.375	60.3	3.225	82.7	9.500	241

ALTERNATE CONFIGURATION FOR LARGE CABLES

If the cable range exceeds the inside diameter of the backshell shown in the table at right, the backshell will be supplied with a **transition adapter** and a second coupling nut. This style of backshell is called a **Style 2**. The transition adapter attaches to the connector. The backshell and clamp fit over the cable jacket. On straight exit backshells, the transition adapter does not affect the length. On 45° and 90° versions the transition adapter adds 1.00 inch (25.4mm) maximum to the backshell length.

Shell Size	Backshell Inside Diameter	
	In.	mm.
18	.72	18.3
20	.85	21.7
24	1.04	26.4
28	1.35	34.3
32	1.62	41.1
36	1.82	46.3
40	2.05	52.0





Series 970 PowerTrip™ Connectors and Accessories

380-105 EMI/RFI Backshell (Non-Environmental)

380P*105 EMI/RFI BACKSHELL



EMI/RFI backshell features ground rings for cable braid shield termination. Spin coupling with anti-decoupling ratchet. Splined connector interface. Heavy duty saddle clamp. Aluminum or stainless steel. Stainless steel telescoping clamp screws. Meets environmental, electrical and mechanical requirements of AS85049 Category 3A Heavy Duty. Assembly procedure conforms to Glenair Type F shield terminations.

MATERIALS AND FINISHES





Adapters, crimp rings, follower, coupling nut: aluminum or stainless steel. See **How To Order** for finish options.

Hardware: stainless steel

INSTALLATION TORQUE

Shell Size	Recommended Installation Torque Inch-Pounds ± 5
18	116
20, 24	136
28, 32, 36	148
40	164

HOW TO ORDER

SERIES	SHELL MATERIAL / FINISH	SHELL SIZE	STRAIN RELIEF CODE	LENGTH CODE																																																																																			
380PS105 Straight Exit 	ME Aluminum / Electroless Nickel RoHS Compliant NF Aluminum / Cadmium with Olive Drab Chromate ZR Aluminum / Zinc-Nickel with Non-Reflective Black Chromate RoHS Compliant	18 20 24 28 32 36 40	 Saddle Clamp	(Omit for 45° and 90° styles. Applies to 380PS105 straight exit only) The Length Code is the length of the adapter in 1/2 inch increments																																																																																			
					<table border="1"> <thead> <tr> <th rowspan="2">Code</th> <th colspan="2">Cable Diameter</th> <th rowspan="2">Code</th> <th colspan="2">Length</th> </tr> <tr> <th>Min.</th> <th>Max.</th> <th>In.</th> <th>mm.</th> </tr> </thead> <tbody> <tr> <td>06H</td> <td>.250</td> <td>6.4</td> <td>.437</td> <td>11.1</td> <td>8</td> <td>3.0</td> <td>76</td> </tr> <tr> <td>08H</td> <td>.312</td> <td>7.9</td> <td>.562</td> <td>14.3</td> <td>9</td> <td>3.5</td> <td>89</td> </tr> <tr> <td>10H</td> <td>.350</td> <td>8.9</td> <td>.625</td> <td>15.9</td> <td>10</td> <td>4.0</td> <td>102</td> </tr> <tr> <td>12H</td> <td>.500</td> <td>12.7</td> <td>.750</td> <td>19.1</td> <td>11</td> <td>4.5</td> <td>114</td> </tr> <tr> <td>16H</td> <td>.625</td> <td>15.9</td> <td>.937</td> <td>23.8</td> <td>12</td> <td>5.0</td> <td>127</td> </tr> <tr> <td>20H</td> <td>.875</td> <td>22.2</td> <td>1.250</td> <td>31.8</td> <td>13</td> <td>5.5</td> <td>140</td> </tr> <tr> <td>24H</td> <td>1.000</td> <td>25.4</td> <td>1.375</td> <td>34.9</td> <td>14</td> <td>6.0</td> <td>152</td> </tr> <tr> <td>28H</td> <td>1.250</td> <td>31.8</td> <td>1.625</td> <td>41.3</td> <td>15</td> <td>6.5</td> <td>165</td> </tr> <tr> <td>32H</td> <td>1.437</td> <td>36.5</td> <td>1.875</td> <td>47.6</td> <td>16</td> <td>7.0</td> <td>178</td> </tr> </tbody> </table>	Code	Cable Diameter		Code	Length		Min.	Max.	In.	mm.	06H	.250	6.4	.437	11.1	8	3.0	76	08H	.312	7.9	.562	14.3	9	3.5	89	10H	.350	8.9	.625	15.9	10	4.0	102	12H	.500	12.7	.750	19.1	11	4.5	114	16H	.625	15.9	.937	23.8	12	5.0	127	20H	.875	22.2	1.250	31.8	13	5.5	140	24H	1.000	25.4	1.375	34.9	14	6.0	152	28H	1.250	31.8	1.625	41.3	15	6.5	165	32H	1.437	36.5	1.875	47.6	16	7.0	178
				Code	Cable Diameter		Code	Length																																																																															
Min.	Max.	In.	mm.																																																																																				
06H	.250	6.4	.437	11.1	8	3.0	76																																																																																
08H	.312	7.9	.562	14.3	9	3.5	89																																																																																
10H	.350	8.9	.625	15.9	10	4.0	102																																																																																
12H	.500	12.7	.750	19.1	11	4.5	114																																																																																
16H	.625	15.9	.937	23.8	12	5.0	127																																																																																
20H	.875	22.2	1.250	31.8	13	5.5	140																																																																																
24H	1.000	25.4	1.375	34.9	14	6.0	152																																																																																
28H	1.250	31.8	1.625	41.3	15	6.5	165																																																																																
32H	1.437	36.5	1.875	47.6	16	7.0	178																																																																																
380PM105 45° Exit 	MT Aluminum / Nickel-PTFE RoHS Compliant Z1 Stainless Steel / Passivated RoHS Compliant																																																																																						
380PN105 90° Exit 																																																																																							
Sample Part Number																																																																																							
380PS105	ZR	24	12H	8																																																																																			


Series 970 PowerTrip™ Connectors and Accessories Accessories

380-105 EMI/RFI Backshell (Non-Environmental)




380PS105 STRAIGHT EXIT EMI/RFI BACKSHELL

Shell Size	A Thread	ø B Max.	
		In.	mm.
18	1.125-18 UNEF-2B	1.39	35.3
20	1.250-18 UNEF-2B	1.53	38.9
24	1.4375-18 UNEF-2B	1.72	43.7
28	1.8125-16 UN-2B	2.13	54.1
32	2.0625-16 UNS-2B	2.35	59.7
36	2.250-16 UN-2B	2.59	65.8
40	2.500-16 UN-2B	2.87	70.6




380PM105 45° EXIT DIMENSIONS



Shell Size	A Thread Class 2B	ø B Max.		C Max.		D Max.	
		In.	mm.	In.	mm.	In.	mm.
18	1.125-18 UNEF	1.39	35.3	1.250	31.8	1.156	29.4
20	1.250-18 UNEF	1.53	38.9	1.312	33.3	1.219	31.0
24	1.4375-18 UNEF	1.72	43.7	1.406	35.7	1.312	33.3
28	1.8125-16 UN	2.13	54.1	1.500	38.1	1.625	41.3
32	2.0625-16 UNS	2.35	59.7	1.675	42.5	1.945	49.4
36	2.250-16 UN	2.59	65.8	1.799	45.7	2.069	52.6
40	2.500-16 UN	2.87	70.6	1.861	47.3	2.131	54.1

380PN105 90° EXIT




Shell Size	A Thread Class 2B	ø B Max.		E Max.		F Max.	
		In.	mm.	In.	mm.	In.	mm.
18	1.125-18 UNEF	1.39	35.3	1.906	48.4	1.812	46.0
20	1.250-18 UNEF	1.53	38.9	2.031	51.6	1.938	49.2
24	1.4375-18 UNEF	1.72	43.7	2.281	57.9	2.188	55.6
28	1.8125-16 UN	2.13	54.1	2.531	64.3	2.625	66.7
32	2.0625-16 UNS	2.35	59.7	2.625	66.7	2.895	73.5
36	2.250-16 UN	2.59	65.8	2.875	73.0	3.145	79.9
40	2.500-16 UN	2.87	70.6	3.025	76.8	3.295	83.7



Accessories

380P*105 EMI/RFI Backshell (Non-Environmental)

SADDLE CLAMP DIMENSIONS




Clamp Size	Cable Range				A Thread Class 2B	B Max.		C Max.	
	Min.		Max.			In.	mm.	In.	mm.
	In.	mm.	In.	mm.					
06H	.250	6.4	.437	11.1	.750-20UNEF	1.301	33.04	1.145	29.1
08H	.312	7.9	.562	14.3	.875-20UNEF	1.301	33.04	1.332	33.8
10H	.350	8.9	.625	15.9	1.000-20UNEF	1.301	33.04	1.332	33.8
12H	.500	12.7	.750	19.1	1.1875-18UNEF	1.332	33.83	1.551	39.4
16H	.625	15.9	.937	23.8	1.4375-18UNEF	1.426	36.22	1.770	45.0
20H	.875	22.2	1.250	31.8	1.750-18UNS	1.613	40.97	2.113	53.7
24H	1.000	25.4	1.375	34.9	2.000-18UNS	1.645	41.78	2.363	60.0
28H	1.250	31.8	1.625	41.3	2.250-16UN	1.920	48.77	2.770	70.4
32H	1.437	36.5	1.875	47.6	2.500-16UN	1.920	48.77	3.020	76.7

ALTERNATE CONFIGURATION FOR LARGE CABLES

If the cable range exceeds the inside diameter of the backshell shown in the table at right, the backshell will be supplied with a **transition adapter** and a second coupling nut. This style of backshell is called a **Style 2**. The transition adapter attaches to the connector. The backshell and clamp fit over the cable jacket. On straight exit backshells, the transition adapter does not affect the length. On 45° and 90° versions the transition adapter adds 1.00 inch (25.4mm) maximum to the backshell length.

Shell Size	Backshell Inside Diameter	
	In.	mm.
18	.72	18.3
20	.85	21.7
24	1.04	26.4
28	1.35	34.3
32	1.62	41.1
36	1.82	46.3
40	2.05	52.0



Series 970 PowerTrip™ Connectors and Accessories

390-055 EMI/RFI Submersible Backshell



SUBMERSIBLE EMI BACKSHELL









Heavy duty backshell features positive detent self-locking spin coupling for high vibration environments. For use with shielded, jacketed power cable. Splined connector interface. Terminate cable shield to inner and outer ground rings. Heavy duty cable clamps fit most cable sizes, or choose wire mesh stainless steel cordgrip. Withstands six feet water immersion for 48 hours. Aluminum or stainless steel with silicone O-rings and gland. Stainless steel telescoping clamp screws. Meets environmental, electrical and mechanical requirements of AS85049 Category 1A Heavy Duty.

MATERIALS AND FINISHES
Adapters, elbows, follower, coupling nut: aluminum or stainless steel. See How To Order for material & finish options.
Hardware: stainless steel
Wire Mesh Cordgrip: stainless steel
Screws: stainless steel
Grommet, O-rings: fluorosilicone

INSTALLATION TORQUE	
Shell Size	Recommended Installation Torque Inch-Pounds ± 5
18	116
20, 24	136
28, 32, 36	148
40	164

HOW TO ORDER


SERIES	SHELL MATERIAL / FINISH	SHELL SIZE	STRAIN RELIEF TYPE AND SIZE	LENGTH CODE																																						
390PS055 Straight Exit 	ME Aluminum / Electroless Nickel RoHS Compliant NF Aluminum / Cadmium with Olive Drab Chromate ZR Aluminum / Zinc-Nickel with Non-Reflective Black Chromate RoHS Compliant MT Aluminum / Nickel-PTFE RoHS Compliant Z1 Stainless Steel / Passivated RoHS Compliant	18 20 24 28 32 36 40	Heavy Duty Saddle Clamp  Wire Mesh Cordgrip 	<p><i>Omit for 45° and 90° styles. The Length Code is the length of the front adapter in 1/2 inch increments</i></p> <table border="1"> <thead> <tr> <th rowspan="2">Code</th> <th colspan="2">Length</th> </tr> <tr> <th>In.</th> <th>mm.</th> </tr> </thead> <tbody> <tr><td>6</td><td>3.0</td><td>76</td></tr> <tr><td>7</td><td>3.5</td><td>89</td></tr> <tr><td>8</td><td>4.0</td><td>102</td></tr> <tr><td>9</td><td>4.5</td><td>114</td></tr> <tr><td>10</td><td>5.0</td><td>127</td></tr> <tr><td>11</td><td>5.5</td><td>140</td></tr> <tr><td>12</td><td>6.0</td><td>152</td></tr> <tr><td>13</td><td>6.5</td><td>165</td></tr> <tr><td>14</td><td>7.0</td><td>178</td></tr> <tr><td>15</td><td>7.5</td><td>191</td></tr> <tr><td>16</td><td>8.0</td><td>203</td></tr> </tbody> </table> 	Code	Length		In.	mm.	6	3.0	76	7	3.5	89	8	4.0	102	9	4.5	114	10	5.0	127	11	5.5	140	12	6.0	152	13	6.5	165	14	7.0	178	15	7.5	191	16	8.0	203
						Code	Length																																			
					In.		mm.																																			
6	3.0	76																																								
7	3.5	89																																								
8	4.0	102																																								
9	4.5	114																																								
10	5.0	127																																								
11	5.5	140																																								
12	6.0	152																																								
13	6.5	165																																								
14	7.0	178																																								
15	7.5	191																																								
16	8.0	203																																								
390PM055 45° Exit 																																										
390PN055 90° Exit 																																										
Sample Part Number																																										
390PS055	ME	20	08K	9																																						




Series 970 PowerTrip™ Connectors and Accessories Accessories 390-055 EMI/RFI Submersible Backshell

390PS055 STRAIGHT EXIT

Shell Size	A Thread	ø B Max.	
		In.	mm.
18	1.125-18 UNEF-2B	1.39	35.3
20	1.250-18 UNEF-2B	1.53	38.9
24	1.4375-18 UNEF-2B	1.72	43.7
28	1.8125-16 UN-2B	2.13	54.1
32	2.0625-16 UNS-2B	2.35	59.7
36	2.250-16 UN-2B	2.59	65.8
40	2.500-16 UN-2B	2.87	70.6




390PM055 45° EXIT



Shell Size	A Thread Class 2B	ø B Max.		C Max.		D Max.	
		In.	mm.	In.	mm.	In.	mm.
18	1.125-18 UNEF	1.39	35.3	1.250	31.8	2.468	62.7
20	1.250-18 UNEF	1.53	38.9	1.312	33.3	2.657	67.5
24	1.4375-18 UNEF	1.72	43.7	1.406	35.7	3.063	77.8
28	1.8125-16 UN	2.13	54.1	1.500	38.1	3.656	92.9
32	2.0625-16 UNS	2.35	59.7	1.675	42.5	3.845	97.7
36	2.250-16 UN	2.59	65.8	1.799	45.7	4.230	107.4
40	2.500-16 UN	2.87	70.6	1.861	47.3	4.459	113.3

390PN055 90° EXIT



Shell Size	A Thread Class 2B	ø B Max.		E Max.		F Max.	
		In.	mm.	In.	mm.	In.	mm.
18	1.125-18 UNEF	1.39	35.3	1.906	48.4	1.812	46.0
20	1.250-18 UNEF	1.53	38.9	2.031	51.6	1.938	49.2
24	1.4375-18 UNEF	1.72	43.7	2.281	57.9	2.188	55.6
28	1.8125-16 UN	2.13	54.1	2.531	64.3	2.625	66.7
32	2.0625-16 UNS	2.35	59.7	2.625	66.7	2.895	73.5
36	2.250-16 UN	2.59	65.8	2.875	73.0	3.145	79.9
40	2.500-16 UN	2.87	70.6	3.025	76.8	3.295	83.7


Series 970 PowerTrip™ Connectors and Accessories

Accessories

390-055 EMI/RFI Submersible Backshell




SADDLE CLAMP DIMENSIONS



Clamp Size	Cable Range				A Thread Class 2B	B Max.		C Max.	
	Min.		Max.			In.	mm.	In.	mm.
	In.	mm.	In.	mm.					
06H	.250	6.4	.437	11.1	.750-20UNEF	1.301	33.04	1.145	29.1
08H	.387	9.8	.562	14.3	.875-20UNEF	1.301	33.04	1.332	33.8
10H	.350	8.9	.625	15.9	1.000-20UNEF	1.301	33.04	1.332	33.8
12H	.500	12.7	.750	19.1	1.1875-18UNEF	1.332	33.83	1.551	39.4
16H	.625	15.9	.937	23.8	1.4375-18UNEF	1.426	36.22	1.770	45.0
20H	.875	22.2	1.250	31.8	1.750-18UNS	1.613	40.97	2.113	53.7
24H	1.000	25.4	1.375	34.9	2.000-18UNS	1.645	41.78	2.363	60.0
28H	1.250	31.8	1.625	41.3	2.250-16UN	1.920	48.77	2.770	70.4
32H	1.437	36.5	1.875	47.6	2.500-16UN	1.920	48.77	3.020	76.7
36H	1.625	41.3	2.125	54.0	2.750-16UN	2.060	53.32	3.250	82.6
40H	1.875	47.6	2.375	60.3	3.000-16UN	2.060	53.32	3.500	88.9

WIRE MESH GRIP DIMENSIONS




Grip Size	Cable Range				Ø A Max.		B Approx.	
	Min.		Max.		In.	mm.	In.	mm.
	In.	mm.	In.	mm.				
06K	.310	7.8	.438	11.1	.942	23.9	4.000	101
08K	.438	11.1	.500	12.7	1.067	27.1	4.120	105
10K	.500	12.7	.625	15.8	1.192	30.3	4.370	111
12K	.625	15.9	.750	19.1	1.380	35.1	5.000	127
14K	.750	19.1	.875	22.2	1.563	39.7	6.000	152
16K	.875	22.2	1.000	25.4	1.563	39.7	6.250	158
20K	1.000	25.4	1.250	31.8	1.875	47.6	7.250	184
24K	1.125	28.6	1.375	34.9	2.225	57.3	8.000	203
28K	1.375	34.9	1.625	41.2	2.505	63.6	8.500	216
32K	1.625	41.3	1.875	47.6	2.755	70.0	9.000	229
40K	2.125	53.9	2.375	60.3	3.225	82.7	9.500	241

ALTERNATE CONFIGURATION FOR LARGE CABLES

If the cable diameter exceeds the diameter of the backshell shown in the table at right, the backshell will be supplied with a **transition adapter**. The clamp and adapters are first installed over the cable jacket, and then are threaded onto the transition adapter.

On straight exit backshells, the transition adapter does not affect the length. On 45° and 90° versions the transition adapter adds 1.00 inch (25.4mm) maximum to the backshell length.

Shell Size	Backshell Inside Diameter	
	In.	mm.
18	.72	18.3
20	.85	21.7
24	1.04	26.4
28	1.35	34.3
32	1.62	41.1
36	1.82	46.3
40	2.05	52.0





Series 970 PowerTrip™ Connectors and Accessories Accessories

390PS086 EMI/RFI Submersible Backshell

390PS086 SUBMERSIBLE HEAVY DUTY BACKSHELL WITH WIRE MESH CORDGRIP

Heavy duty backshell fits Series 970 connectors and withstands MIL-S-901 grade A high impact shock. Splined connector interface. Terminate cable shield to inner and outer ground rings. Stainless steel wire mesh cordgrip provides strain relief to heavy duty power cables. Withstands six feet water immersion for 48 hours. Aluminum or stainless steel with silicone O-rings and cable gland. Meets environmental, electrical and mechanical requirements of MIL-DTL-28840.



MATERIALS AND FINISHES

Adapters, crimp rings, follower, coupling nut:
aluminum or stainless steel. See table for
finish options.

Hardware: stainless steel

Cable sealing gland, O-rings: silicone

Wire mesh cordgrip: stainless steel

INSTALLATION TORQUE

Shell Size	Recommended Installation Torque Inch-Pounds ± 5
18	116
20, 24	136
28, 32, 36	148
40	164

HOW TO ORDER


SHELL SIZE	CABLE RANGE				ALUMINUM/ NICKEL	ALUMINUM/ NICKEL-PTFE	ALUMINUM/ OD CADMIUM	ALUMINUM/ BLACK ZINC- NICKEL	STAINLESS STEEL/ PASSIVATED
	Min.		Max.						
	In.	mm.	In.	mm.					
18	.500	12.70	.625	15.88	390PS086ME1810	390PS086MT1810	390PS086NF1810	390PS086ZR1810	390PS086Z1810
	.625	15.88	.750	19.05	390PS086ME1812	390PS086MT1812	390PS086NF1812	390PS086ZR1812	390PS086Z1812
	.750	19.05	.875	22.23	390PS086ME1814	390PS086MT1814	390PS086NF1814	390PS086ZR1814	390PS086Z1814
20	.500	12.70	.625	15.88	390PS086ME2010	390PS086MT2010	390PS086NF2010	390PS086ZR2010	390PS086Z2010
	.625	15.88	.750	19.05	390PS086ME2012	390PS086MT2012	390PS086NF2012	390PS086ZR2012	390PS086Z2012
	.750	19.05	.875	22.23	390PS086ME2014	390PS086MT2014	390PS086NF2014	390PS086ZR2014	390PS086Z2014
24	.625	15.88	.750	19.05	390PS086ME2412	390PS086MT2412	390PS086NF2412	390PS086ZR2412	390PS086Z2412
	.750	19.05	.875	22.23	390PS086ME2414	390PS086MT2414	390PS086NF2414	390PS086ZR2414	390PS086Z2414
	1.000	25.40	1.250	31.75	390PS086ME2420	390PS086MT2420	390PS086NF2420	390PS086ZR2420	390PS086Z2420
28	.750	19.05	.875	22.23	390PS086ME2814	390PS086MT2814	390PS086NF2814	390PS086ZR2814	390PS086Z2814
	1.000	25.40	1.250	31.75	390PS086ME2820	390PS086MT2820	390PS086NF2820	390PS086ZR2820	390PS086Z2820
	1.125	28.58	1.375	34.93	390PS086ME2824	390PS086MT2824	390PS086NF2824	390PS086ZR2824	390PS086Z2824
32	1.125	28.58	1.375	34.93	390PS086ME3224	390PS086MT3224	390PS086NF3224	390PS086ZR3224	390PS086Z3224
	1.375	34.93	1.625	41.28	390PS086ME3228	390PS086MT3228	390PS086NF3228	390PS086ZR3228	390PS086Z3228
	1.625	41.28	1.875	47.63	390PS086ME3232	390PS086MT3232	390PS086NF3232	390PS086ZR3232	390PS086Z3232
36	1.125	28.58	1.375	34.93	390PS086ME3624	390PS086MT3624	390PS086NF3624	390PS086ZR3624	390PS086Z3624
	1.375	34.93	1.625	41.28	390PS086ME3628	390PS086MT3628	390PS086NF3628	390PS086ZR3628	390PS086Z3628
	1.625	41.28	1.875	47.63	390PS086ME3632	390PS086MT3632	390PS086NF3632	390PS086ZR3632	390PS086Z3632
	2.125	53.98	2.375	60.33	390PS086ME3640	390PS086MT3640	390PS086NF3640	390PS086ZR3640	390PS086Z3640
40	1.125	28.58	1.375	34.93	390PS086ME4024	390PS086MT4024	390PS086NF4024	390PS086ZR4024	390PS086Z4024
	1.375	34.93	1.625	41.28	390PS086ME4028	390PS086MT4028	390PS086NF4028	390PS086ZR4028	390PS086Z4028
	1.625	41.28	1.875	47.63	390PS086ME4032	390PS086MT4032	390PS086NF4032	390PS086ZR4032	390PS086Z4032
	2.125	53.98	2.375	60.33	390PS086ME4040	390PS086MT4040	390PS086NF4040	390PS086ZR4040	390PS086Z4040

Series 970 PowerTrip™ Connectors and Accessories
 Accessories
 390PS086 EMI/RFI Submersible Backshell



Accessories

390PS086 BACKSHELL WITH WIRE MESH CORD GRIP



Shell Size	Cable Range				L Length ±.12 (3.0)		Working Room		A Thread Class 2B	ØB Max.		ØC Max.		ØD Min.		X Ref.		Y Max.	
	Min.		Max.		In.	mm.	In.	mm.		In.	mm.	In.	mm.	In.	mm.	In.	mm.	In.	mm.
	In.	mm.	In.	mm.	In.	mm.	In.	mm.		In.	mm.	In.	mm.	In.	mm.	In.	mm.	In.	mm.
18	.500	12.70	.625	15.88	4.62	117.4	3.00	76.2	1.125-18 UNEF	1.44	36.6	1.406	35.71	1.000	25.40	4.37	111.0	1.16	29.5
	.625	15.88	.750	19.05	4.62	117.4	3.00	76.2	1.125-18 UNEF	1.44	36.6	1.406	35.71	1.000	25.40	5.00	127.0	1.34	34.0
	.750	19.05	.875	22.23	4.62	117.4	3.00	76.2	1.125-18 UNEF	1.44	36.6	1.531	38.89	1.125	28.58	5.00	127.0	1.59	40.4
20	.500	12.70	.625	15.88	4.62	117.4	3.00	76.2	1.250-18 UNEF	1.54	39.1	1.531	38.89	1.125	28.58	4.37	111.0	1.16	29.5
	.625	15.88	.750	19.05	4.62	117.4	3.00	76.2	1.250-18 UNEF	1.54	39.1	1.531	38.89	1.125	28.58	6.00	152.4	1.34	34.0
	.750	19.05	.875	22.23	4.62	117.4	3.00	76.2	1.250-18 UNEF	1.54	39.1	1.656	42.06	1.250	31.75	5.00	127.0	1.59	40.4
24	.625	15.88	.750	19.05	5.12	130.1	3.50	88.9	1.438-18 UNEF	1.73	43.9	1.656	42.06	1.250	31.75	6.00	152.4	1.34	34.0
	.750	19.05	.875	22.23	5.12	130.1	3.50	88.9	1.438-18 UNEF	1.73	43.9	1.781	45.24	1.375	34.93	5.00	127.0	1.59	40.4
	1.000	25.40	1.250	31.75	5.12	130.1	3.50	88.9	1.438-18 UNEF	1.73	43.9	1.781	45.24	1.375	34.93	6.25	158.8	1.94	49.3
28	.750	19.05	.875	22.23	5.12	130.1	3.50	88.9	1.812-16 UN	2.14	54.4	2.156	54.76	1.750	44.45	5.00	127.0	1.59	40.4
	1.000	25.40	1.250	31.75	5.12	130.1	3.50	88.9	1.812-16 UN	2.14	54.4	2.156	54.76	1.750	44.45	6.25	158.8	1.94	49.3
	1.125	28.58	1.375	34.93	5.12	130.1	3.50	88.9	1.812-16 UN	2.14	54.4	2.156	54.76	1.750	44.45	7.25	184.2	2.19	55.6
32	1.125	28.58	1.375	34.93	5.12	130.1	3.50	88.9	2.062-16 UNS	2.37	60.2	2.281	57.94	1.875	47.63	7.25	184.2	2.19	55.6
	1.375	34.93	1.625	41.28	6.12	155.5	4.50	114.3	2.062-16 UNS	2.37	60.2	2.281	57.94	1.875	47.63	8.00	203.2	2.43	61.7
	1.625	41.28	1.875	47.63	6.12	155.5	4.50	114.3	2.062-16 UNS	2.37	60.2	2.281	57.94	1.875	47.63	10.00	254.0	2.69	68.3
36	1.125	28.58	1.375	34.93	6.12	155.5	4.50	114.3	2.250-16 UN	2.63	66.8	2.531	64.29	2.125	53.98	7.25	184.2	2.19	55.6
	1.375	34.93	1.625	41.28	6.12	155.5	4.50	114.3	2.250-16 UN	2.63	66.8	2.531	64.29	2.125	53.98	8.00	203.2	2.43	61.7
	1.625	41.28	1.875	47.63	6.12	155.5	4.50	114.3	2.250-16 UN	2.63	66.8	2.531	64.29	2.125	53.98	10.00	254.0	2.69	68.3
	2.125	53.98	2.375	60.33	6.62	168.2	5.00	127.0	2.250-16 UN	2.63	66.8	3.031	76.99	2.625	66.68	12.60	320.0	3.19	81.0
40	1.125	28.58	1.375	34.93	6.12	155.5	4.50	114.3	2.500-16 UN	2.93	74.4	2.781	70.64	2.375	60.33	7.25	184.2	2.19	55.6
	1.375	34.93	1.625	41.28	6.12	155.5	4.50	114.3	2.500-16 UN	2.93	74.4	2.781	70.64	2.375	60.33	8.00	203.2	2.43	61.7
	1.625	41.28	1.875	47.63	6.12	155.5	4.50	114.3	2.500-16 UN	2.93	74.4	2.781	70.64	2.375	60.33	10.00	254.0	2.69	68.3
	2.125	53.98	2.375	60.33	6.62	168.2	5.00	127.0	2.500-16 UN	2.93	74.4	3.031	76.99	2.625	66.68	12.60	320.0	3.19	81.0

H



Series 970 PowerTrip™ Connectors and Accessories Accessories

390PS036 EMI/RFI Submersible Backshell

390PS036 SUBMERSIBLE EMI/RFI BACKSHELL WITH SADDLE BAR CABLE CLAMP

Heavy duty backshell fits Series 970 connectors and withstands MIL-S-901 grade A high impact shock. Splined connector interface. Terminate cable shield to inner and outer ground rings. Heavy duty saddle bar cable clamp with telescoping stainless steel screws, lockwashers and lockwire holes. Meets AS85049/42 Class 1A requirements. Withstands six feet water immersion for 48 hours. Aluminum or stainless steel with silicone O-rings and cable gland. Meets environmental, electrical and mechanical requirements of MIL-DTL-28840.



MATERIALS AND FINISHES

Adapters, crimp rings, follower, coupling nut, cable clamp: aluminum or stainless steel. See Ordering Information for finish options.

Hardware: stainless steel

Cable sealing gland, O-rings: silicone

Wire mesh cordgrip: stainless steel

INSTALLATION TORQUE

Shell Size	Recommended Installation Torque Inch-Pounds ± 5
18	116
20, 24	136
28, 32, 36	148
40	164

HOW TO ORDER


SHELL SIZE	CABLE RANGE				ALUMINUM/ NICKEL	ALUMINUM/ NICKEL-PTFE	ALUMINUM/ OD CADMIUM	ALUMINUM/ BLACK ZINC- NICKEL	STAINLESS STEEL/ PASSIVATED
	Min.		Max.						
	In.	mm.	In.	mm.					
18	.375	9.53	.625	15.88	390PS036ME1810	390PS036MT1810	390PS036NF1810	390PS036ZR1810	390PS036Z11810
	.438	11.13	.750	19.05	390PS036ME1812	390PS036MT1812	390PS036NF1812	390PS036ZR1812	390PS036Z11812
	.625	15.88	.938	23.83	390PS036ME1816	390PS036MT1816	390PS036NF1816	390PS036ZR1816	390PS036Z11816
20	.375	9.53	.625	15.88	390PS036ME2010	390PS036MT2010	390PS036NF2010	390PS036ZR2010	390PS036Z12010
	.438	11.13	.750	19.05	390PS036ME2012	390PS036MT2012	390PS036NF2012	390PS036ZR2012	390PS036Z12012
	.625	15.88	.938	23.83	390PS036ME2016	390PS036MT2016	390PS036NF2016	390PS036ZR2016	390PS036Z12016
24	.438	11.13	.750	19.05	390PS036ME2412	390PS036MT2412	390PS036NF2412	390PS036ZR2412	390PS036Z12412
	.625	15.88	.938	23.83	390PS036ME2416	390PS036MT2416	390PS036NF2416	390PS036ZR2416	390PS036Z12416
	.875	22.23	1.250	31.75	390PS036ME2420	390PS036MT2420	390PS036NF2420	390PS036ZR2420	390PS036Z12420
28	.625	15.88	.938	23.83	390PS036ME2816	390PS036MT2816	390PS036NF2816	390PS036ZR2816	390PS036Z12816
	.875	22.23	1.250	31.75	390PS036ME2820	390PS036MT2820	390PS036NF2820	390PS036ZR2820	390PS036Z12820
	1.000	25.40	1.380	35.05	390PS036ME2824	390PS036MT2824	390PS036NF2824	390PS036ZR2824	390PS036Z12824
32	1.000	25.40	1.380	35.05	390PS036ME3224	390PS036MT3224	390PS036NF3224	390PS036ZR3224	390PS036Z13224
	1.250	31.75	1.625	41.28	390PS036ME3228	390PS036MT3228	390PS036NF3228	390PS036ZR3228	390PS036Z13228
	1.437	36.50	1.875	47.63	390PS036ME3232	390PS036MT3232	390PS036NF3232	390PS036ZR3232	390PS036Z13232
36	1.000	25.40	1.375	34.93	390PS036ME3624	390PS036MT3624	390PS036NF3624	390PS036ZR3624	390PS036Z13624
	1.250	31.75	1.625	41.28	390PS036ME3628	390PS036MT3628	390PS036NF3628	390PS036ZR3628	390PS036Z13628
	1.437	36.50	1.875	47.63	390PS036ME3632	390PS036MT3632	390PS036NF3632	390PS036ZR3632	390PS036Z13632
	1.875	25.40	2.375	60.33	390PS036ME3640	390PS036MT3640	390PS036NF3640	390PS036ZR3640	390PS036Z13640
40	1.000	47.63	1.375	34.93	390PS036ME4024	390PS036MT4024	390PS036NF4024	390PS036ZR4024	390PS036Z14024
	1.250	31.75	1.625	41.28	390PS036ME4028	390PS036MT4028	390PS036NF4028	390PS036ZR4028	390PS036Z14028
	1.437	36.50	1.875	47.63	390PS036ME4032	390PS036MT4032	390PS036NF4032	390PS036ZR4032	390PS036Z14032
	2.125	47.63	2.375	60.33	390PS036ME4040	390PS036MT4040	390PS036NF4040	390PS036ZR4040	390PS036Z14040

Series 970 PowerTrip™ Connectors and Accessories Accessories

390PS036 EMI/RFI Submersible Backshell



390PS036 BACKSHELL WITH SADDLE BAR CLAMP



Shell Size	Cable Range				L Length ±.12 (3.0)		Working Room		A Thread Class 2B	ØB Max.		ØC Max.		ØD Min.		ØX Max.		Y Ref.	
	Min.		Max.		In.	mm.	In.	mm.		In.	mm.	In.	mm.	In.	mm.	In.	mm.	In.	mm.
	In.	mm.	In.	mm.															
18	.375	9.53	.625	15.88	4.62	117.4	3.00	76.2	1.125-18 UNEF	1.44	36.6	1.406	35.71	1.000	25.40	1.281	32.54	1.312	33.32
	.438	11.13	.750	19.05	4.62	117.4	3.00	76.2	1.125-18 UNEF	1.44	36.6	1.406	35.71	1.000	25.40	1.312	33.32	1.593	40.46
	.625	15.88	.938	23.83	4.62	117.4	3.00	76.2	1.125-18 UNEF	1.44	36.6	1.531	38.89	1.125	28.58	1.406	35.71	1.750	44.45
20	.375	9.53	.625	15.88	4.62	117.4	3.00	76.2	1.250-18 UNEF	1.54	39.1	1.531	38.89	1.125	28.58	1.281	32.54	1.312	33.32
	.438	11.13	.750	19.05	4.62	117.4	3.00	76.2	1.250-18 UNEF	1.54	39.1	1.531	38.89	1.125	28.58	1.312	33.32	1.593	40.46
	.625	15.88	.938	23.83	4.62	117.4	3.00	76.2	1.250-18 UNEF	1.54	39.1	1.656	42.06	1.250	31.75	1.406	35.71	1.750	44.45
24	.438	11.13	.750	19.05	5.12	130.1	3.50	88.9	1.438-18 UNEF	1.73	43.9	1.656	42.06	1.250	31.75	1.312	33.32	1.593	40.46
	.625	15.88	.938	23.83	5.12	130.1	3.50	88.9	1.438-18 UNEF	1.73	43.9	1.781	45.24	1.375	34.93	1.593	40.46	1.750	44.45
	.875	22.23	1.250	31.75	5.12	130.1	3.50	88.9	1.438-18 UNEF	1.73	43.9	1.781	45.24	1.375	34.93	1.625	41.28	2.093	53.16
28	.625	15.88	.938	23.83	5.12	130.1	3.50	88.9	1.812-16 UN	2.14	54.4	2.156	54.76	1.750	44.45	1.406	35.71	1.750	44.45
	.875	22.23	1.250	31.75	5.12	130.1	3.50	88.9	1.812-16 UN	2.14	54.4	2.156	54.76	1.750	44.45	1.593	40.46	2.093	53.16
	1.000	25.40	1.380	35.05	5.12	130.1	3.50	88.9	1.812-16 UN	2.14	54.4	2.156	54.76	1.750	44.45	1.625	41.28	2.343	59.51
32	1.000	25.40	1.380	35.05	5.12	130.1	3.50	88.9	2.062-16 UNS	2.37	60.2	2.281	57.94	1.875	47.63	1.625	41.28	2.343	59.51
	1.250	31.75	1.625	41.28	6.12	155.5	4.50	114.3	2.062-16 UNS	2.37	60.2	2.281	57.94	1.875	47.63	1.900	48.26	2.750	69.85
	1.437	36.50	1.875	47.63	6.12	155.5	4.50	114.3	2.062-16 UNS	2.37	60.2	2.281	57.94	1.875	47.63	1.900	48.26	3.000	76.20
36	1.000	25.40	1.375	34.93	6.12	155.5	4.50	114.3	2.250-16 UN	2.63	66.8	2.531	64.29	2.125	53.98	1.625	41.28	2.343	59.51
	1.250	31.75	1.625	41.28	6.12	155.5	4.50	114.3	2.250-16 UN	2.63	66.8	2.531	64.29	2.125	53.98	1.900	48.26	2.750	69.85
	1.437	36.50	1.875	47.63	6.12	155.5	4.50	114.3	2.250-16 UN	2.63	66.8	2.531	64.29	2.125	53.98	1.900	48.26	3.000	76.20
40	1.875	47.63	2.375	60.33	6.62	168.2	5.00	127.0	2.250-16 UN	2.63	66.8	3.031	76.99	2.625	66.68	2.060	52.32	3.500	88.90
	1.000	25.40	1.375	34.93	6.12	155.5	4.50	114.3	2.500-16 UN	2.93	74.4	2.781	70.64	2.375	60.33	1.625	41.28	2.343	59.51
	1.250	31.75	1.625	41.28	6.12	155.5	4.50	114.3	2.500-16 UN	2.93	74.4	2.781	70.64	2.375	60.33	1.900	48.26	2.750	69.85
	1.437	36.50	1.875	47.63	6.12	155.5	4.50	114.3	2.500-16 UN	2.93	74.4	2.781	70.64	2.375	60.33	1.900	48.26	3.000	76.20
	1.875	47.63	2.375	60.33	6.62	168.2	5.00	127.0	2.500-16 UN	2.93	74.4	3.031	76.99	2.625	66.68	2.060	52.32	3.500	88.90





Series 970 PowerTrip™ Connectors and Accessories Accessories

930-014 Flange Mount Gaskets

930-014 FLANGE MOUNT GASKETS

Flange mount gaskets protect equipment from moisture ingress and contamination. Conductive gaskets reduce EMI problems. These die-cut elastomeric gaskets fit Series 970 square flange connectors.



About Fluorosilicone

Fluorosilicone (FVMQ) offers excellent resistance to hydrocarbons, oils, petroleum fuels and greases. Suitable for use with mineral-based hydraulic fluids. Continuous operating temperature -60°C to +175°C, +200°C intermittent. Meets MIL-DTL-25988.

FLUOROSILICONE GASKETS

Shell Size	Part Number	A Bsc.		B Dia.		C Typ.		D Dia.	
		In.	mm.	In.	mm.	In.	mm.	In.	mm.
18	930-014F18	1.015	25.78	1.187	30.15	1.383	35.13	.146	3.71
20	930-014F20	1.140	28.96	1.374	34.90	1.508	38.30	.146	3.71
24	930-014F24	1.281	32.54	1.562	39.67	1.718	43.64	.146	3.71
28	930-014F28	1.568	39.83	1.874	47.60	2.138	54.31	.170	4.32
32	930-014F32	1.734	44.04	2.062	52.37	2.328	59.13	.170	4.32
36	930-014F36	1.984	50.39	2.302	58.47	2.578	65.48	.170	4.32
40	930-014F40	2.234	56.74	2.562	65.07	2.828	71.83	.170	4.32

About Viton®

Viton® fluoroelastomer (FKM) offers excellent resistance to high temperatures, ozone and solvents. Continuous operating temperature -20°C to +200°C.

VITON® GASKETS

Shell Size	Part Number	A Bsc.		B Dia.		C Typ.		D Dia.	
		In.	mm.	In.	mm.	In.	mm.	In.	mm.
18	930-014V18	1.015	25.78	1.187	30.15	1.383	35.13	.146	3.71
20	930-014V20	1.140	28.96	1.374	34.90	1.508	38.30	.146	3.71
24	930-014V24	1.281	32.54	1.562	39.67	1.718	43.64	.146	3.71
28	930-014V28	1.568	39.83	1.874	47.60	2.138	54.31	.170	4.32
32	930-014V32	1.734	44.04	2.062	52.37	2.328	59.13	.170	4.32
36	930-014V36	1.984	50.39	2.302	58.47	2.578	65.48	.170	4.32
40	930-014V40	2.234	56.74	2.562	65.07	2.828	71.83	.170	4.32

About Conductive Fluorosilicone

High performance silver-filled fluorosilicone has excellent corrosion resistance in harsh environments. 90 dB plane wave shielding effectiveness at 10GHz, continuous operating temperature -55°C to +160°C, resistant to solvents and fuels. Material meets MIL-DTL-83528 Type D.

CONDUCTIVE FLUOROSILICONE GASKETS

Shell Size	Part Number	A Bsc.		B Dia.		C Typ.		D Dia.	
		In.	mm.	In.	mm.	In.	mm.	In.	mm.
18	930-014X18	1.015	25.78	1.187	30.15	1.383	35.13	.146	3.71
20	930-014X20	1.140	28.96	1.374	34.90	1.508	38.30	.146	3.71
24	930-014X24	1.281	32.54	1.562	39.67	1.718	43.64	.146	3.71
28	930-014X28	1.568	39.83	1.874	47.60	2.138	54.31	.170	4.32
32	930-014X32	1.734	44.04	2.062	52.37	2.328	59.13	.170	4.32
36	930-014X36	1.984	50.39	2.302	58.47	2.578	65.48	.170	4.32
40	930-014X40	2.234	56.74	2.562	65.07	2.828	71.83	.170	4.32

Series 970 PowerTrip™ Connectors and Accessories
Accessories
660PS097 & 098 Protective Covers



METAL PROTECTIVE COVERS




Metal covers protect unmated Series 970 connectors. Available with no attachment (see table below for part numbers), or choose sash chain, wire rope or nylon cord attachments from the ordering table on the following page.



Plug Cover



Receptacle Cover

ATTACHMENT OPTIONS	
 Sash Chain	#8 sash chain, 300 series stainless steel, passivated. Glenair's most popular attachment option for circular connector covers.
 Fluoropolymer Coated SST Wire Rope	Tough, flexible translucent FEP fluoropolymer® jacket over stainless steel, +200°C., resists weather, chemicals and abrasion. Glenair's best selling wire rope. 1/16 inch diameter uncoated, .09 inch (2.3 mm) finished diameter.
 Black Nylon Cord	Black braided nylon cord. Very flexible, very good abrasion resistance, good chemical resistance. .120" (3mm) diameter. +125°C.

MATERIALS AND FINISHES	
Cover	Aluminum or Stainless Steel. See ordering information for finish options.
Gasket (Receptacle Cover)	Silicone
Rivet, Ring, Clevis	Stainless Steel

PROTECTIVE COVERS WITH NO ATTACHMENT (SEE NEXT PAGE FOR ATTACHMENT OPTIONS)

SHELL SIZE	THREAD SIZE	TYPE	ALUMINUM/ NICKEL	ALUMINUM/ NICKEL- PTFE	ALUMINUM/ OD CADMIUM	ALUMINUM/ BLACK ZINC-NICKEL	STAINLESS STEEL/ PASSIVATED
18	1.125-.1P-.3L-TS	Plug Cover	660PS097ME18N	660PS097MT18N	660PS097NF18N	660PS097ZR18N	660PS097Z118N
		Receptacle Cover	660PS098ME18N	660PS098MT18N	660PS098NF18N	660PS098ZR18N	660PS098Z118N
20	1.250-.1P-.3L-TS	Plug Cover	660PS097ME20N	660PS097MT20N	660PS097NF20N	660PS097ZR20N	660PS097Z120N
		Receptacle Cover	660PS098ME20N	660PS098MT20N	660PS098NF20N	660PS098ZR20N	660PS098Z120N
24	1.500-.1P-.3L-TS	Plug Cover	660PS097ME24N	660PS097MT24N	660PS097NF24N	660PS097ZR24N	660PS097Z124N
		Receptacle Cover	660PS098ME24N	660PS098MT24N	660PS098NF24N	660PS098ZR24N	660PS098Z124N
28	1.750-.1P-.3L-TS	Plug Cover	660PS097ME28N	660PS097MT28N	660PS097NF28N	660PS097ZR28N	660PS097Z128N
		Receptacle Cover	660PS098ME28N	660PS098MT28N	660PS098NF28N	660PS098ZR28N	660PS098Z128N
32	2.000-.1P-.3L-TS	Plug Cover	660PS097ME32N	660PS097MT32N	660PS097NF32N	660PS097ZR32N	660PS097Z132N
		Receptacle Cover	660PS098ME32N	660PS098MT32N	660PS098NF32N	660PS098ZR32N	660PS098Z132N
36	2.250-.1P-.3L-TS	Plug Cover	660PS097ME36N	660PS097MT36N	660PS097NF36N	660PS097ZR36N	660PS097Z136N
		Receptacle Cover	660PS098ME36N	660PS098MT36N	660PS098NF36N	660PS098ZR36N	660PS098Z136N
40	2.500-.1P-.3L-TS	Plug Cover	660PS097ME40N	660PS097MT40N	660PS097NF40N	660PS097ZR40N	660PS097Z140N
		Receptacle Cover	660PS098ME40N	660PS098MT40N	660PS098NF40N	660PS098ZR40N	660PS098Z140N










Series 970 PowerTrip™ Connectors and Accessories

660PS097 & 098 Protective Covers

PROTECTIVE COVERS

Attach covers to panel or cable connector with sash chain or rope. Large ring fits under jam nut of panel mount receptacle or over accessory thread of cable connector (captivate with backshell or adapter). Ring terminal fits #4, #6 or #8 screws on backshell or square flange panel receptacle mounting screws. Split rings also available-see next page.

HOW TO ORDER

SERIES	SHELL MATERIAL / FINISH	SHELL SIZE	ATTACHMENT TYPE	ATTACHMENT LENGTH	FITTING TYPE AND DIAMETER (SEE NEXT PAGE FOR ADDITIONAL SIZES)					
660PS097 Plug Cover 	ME Aluminum / Electroless Nickel RoHS Compliant	18 20 24 28 32 36 40	N No attachment	Length in Inches	Ring Terminal or Clevis for Attaching With #4, #6 or #8 Screw					
				3	 Clevis Fitting Type S Chain	 Ring Terminal Type H and G Rope				
			3 inches	S Sash Chain			4	Code Screw Size Ring I.D.		
			4 inches		-06 #4 .125					
			5 inches		-09 #6 .156					
	660PS098 Receptacle Cover 	ZR Aluminum / Zinc-Nickel with Non-Reflective Black Chromate RoHS Compliant	18 20 24 28 32 36 40	H Fluoro-polymer Coated SST Wire Rope	6	-03 #8 .191				
					6 inches	G Black Nylon Rope	Ring for Attaching Under Jam Nut Receptacle or Over Accessory Thread			
					Other lengths are available, including fractional sizes. EXAMPLE: for a 7 1/2 inch length, use 7.5					
					Code Shell Size Jam Nut Thd. Ring I.D.					
					-21 18 1.250 1.265					
-23 20 1.4375 1.453										
	MT Aluminum / Nickel-PTFE RoHS Compliant Z1 Stainless Steel / Passivated RoHS Compliant	18 20 24 28 32 36 40	G Black Nylon Rope		-31 28 1.9375 1.953					
					-35 32 2.125 2.140					
					-40 36 2.375 2.406					
					-44 40 2.625 2.656					
				Code Shell Size Access. Thd. Ring I.D.						
				-19 18 1.125 1.140						
				-21 20 1.250 1.265						
				-23 24 1.4375 1.453						
				-30 28 1.8125 1.890						
				-33 32 2.0625 2.077						
-40 36 2.250 2.406										
-44 40 2.500 2.656										
Sample Part Number										
660PS097	MT	24	S	4	-06					

Series 970 PowerTrip™ Connectors and Accessories


Accessories

660PS097 & 098 Protective Covers




660PS097 AND -098 PROTECTIVE COVERS

Shell Size	A Max.		B Thread
	In.	mm.	
18	1.417	36.0	1.125-.1P-.3L-TS
20	1.535	39.0	1.250-.1P-.3L-TS
24	1.772	45.0	1.500-.1P-.3L-TS
28	2.007	51.0	1.750-.1P-.3L-TS
32	2.244	57.0	2.000-.1P-.3L-TS
36	2.480	63.0	2.250-.1P-.3L-TS
40	2.716	69.0	2.500-.1P-.3L-TS



660PS097 Plug Cover



660PS098 Receptacle Cover

RING STYLES



Style A Solid Ring



Style B Solid Ring



Ring Terminal



Clevis (Sash Chain)



Split Ring

RING REFERENCE TABLE (IN ASCENDING DIAMETER ORDER)

Code	Ring Type	I.D.	Code	Ring Type	I.D.	Code	Ring Type	I.D.	Code	Ring Type	I.D.
		In. mm.			In. mm.			In. mm.			In. mm.
00	No Fitting	- -	13	Solid Ring Style B	.765 19.43	21	Solid Ring Style B	1.265 32.13	78	Split Ring	1.875 47.63
06	Ring terminal/Clevis	.125 3.18	105	Solid Ring Style A	.766 19.46	109	Solid Ring Style A	1.266 32.16	30	Solid Ring Style B	1.890 48.01
01	Ring terminal/Clevis	.145 3.68	205	Solid Ring Style A	.788 20.02	209	Solid Ring Style A	1.312 33.32	114	Solid Ring Style A	1.891 48.03
09	Ring terminal/Clevis	.156 3.96	14	Solid Ring Style B	.844 21.44	22	Solid Ring Style B	1.343 34.11	214	Solid Ring Style A	1.938 49.23
05	Ring terminal/Clevis	.167 4.24	15	Solid Ring Style B	.890 22.61	68	Split Ring	1.350 34.29	31	Solid Ring Style B	1.953 49.61
02	Ring terminal/Clevis	.182 4.62	58	Split Ring	.890 22.61	70	Split Ring	1.375 34.93	32	Solid Ring Style B	1.968 49.99
03	Ring terminal/Clevis	.191 4.85	106	Solid Ring Style A	.896 22.76	110	Solid Ring Style A	1.391 35.33	80	Split Ring	1.980 50.29
04	Ring terminal/Clevis	.197 5.00	206	Solid Ring Style A	.907 23.04	210	Solid Ring Style A	1.438 36.53	82	Split Ring	2.060 52.32
07	Ring terminal/Clevis	.218 5.54	16	Solid Ring Style B	.968 24.59	23	Solid Ring Style B	1.453 36.91	33	Solid Ring Style B	2.077 52.76
095	Solid Ring Style A	.312 7.92	17	Solid Ring Style B	1.015 25.78	24	Solid Ring Style B	1.484 37.69	115	Solid Ring Style A	2.078 52.78
100	Solid Ring Style A	.391 9.93	60	Split Ring	1.015 25.78	72	SPLIT RING	1.485 37.72	35	Solid Ring Style B	2.140 54.36
50	Split Ring	.425 10.80	107	Solid Ring Style A	1.016 25.81	111	Solid Ring Style A	1.521 38.63	36	Solid Ring Style B	2.187 55.55
08	Solid Ring Style B	.468 11.89	207	Solid Ring Style A	1.025 26.04	211	Solid Ring Style A	1.536 39.01	84	Split Ring	2.235 56.77
52	Split Ring	.485 12.32	18	Solid Ring Style B	1.093 27.76	25	Solid Ring Style B	1.577 40.06	86	Split Ring	2.310 58.67
101	Solid Ring Style A	.516 13.11	62	Split Ring	1.095 27.81	74	Split Ring	1.625 41.28	116	Solid Ring Style A	2.406 61.11
102	Solid Ring Style A	.583 14.81	64	Split Ring	1.130 28.70	27	Solid Ring Style B	1.640 41.66	40	Solid Ring Style B	2.406 61.11
10	Solid Ring Style B	.593 15.06	19	Solid Ring Style B	1.140 28.96	112	Solid Ring Style A	1.641 41.68	88	Split Ring	2.475 62.87
54	Split Ring	.640 16.26	108	Solid Ring Style A	1.141 28.98	28	Solid Ring Style B	1.687 42.85	117	Solid Ring Style A	2.510 63.75
103	Solid Ring Style A	.641 16.28	308	Solid Ring Style A	1.188 30.18	76	Split Ring	1.750 44.45	90	Split Ring	2.655 67.44
104	Solid Ring Style A	.708 17.98	208	Solid Ring Style A	1.203 30.56	29	Solid Ring Style B	1.765 44.83	44	Solid Ring Style B	2.656 67.46
12	Solid Ring Style B	.718 18.24	20	Solid Ring Style B	1.203 30.56	113	Solid Ring Style A	1.766 44.86	92	Split Ring	2.810 71.37
56	Split Ring	.750 19.05	66	Split Ring	1.250 31.75	213	Solid Ring Style A	1.812 46.02	48	Solid Ring Style B	3.031 76.99
									94	Split Ring	3.045 77.34



Series 970 PowerTrip™ Connectors and Accessories

780-001 Bean Rubber Covers






RUBBER COVERS FOR SERIES 970 CONNECTORS



These *splashproof molded rubber covers* fit Series 970 plugs and receptacles. Braided black nylon lanyard is available with metal rings, cable tie or slipknot for attachment to panel or to cable. -40° to +120° C operating temperature.

MATERIALS	
Cover	SBR rubber blend, black
Lanyard	.094 (2.4) nylon cord, black
Cable Tie	Nylon, black, SST locking tab
Attachment Ring	Stainless steel
Friction Sleeve	Kynar
Crimp Ring	Copper alloy, tin plated


HOW TO ORDER

SERIES	SIZE	LANYARD TYPE	LANYARD LENGTH	ATTACHMENT CODE	MATERIAL				
780-001 Plug Cover	780-001 Plug Covers		Length in Inches ± 1 (25.4) Inch	 -WS Nylon Cable Tie, 1.77 Inch (45mm) Maximum Wire Bundle Diameter	Omit for Standard SBR Rubber C Optional Conductive Rubber				
	Size Code	Shell Size							
	-19	18							
	-22	20							
	-25	24							
	-32	28							
	-36	32							
	-38	36							
780-002 Receptacle Cover	780-002 Receptacle Covers			 -SK Adjustable Slip Knot with Friction Sleeve. The sleeve can be crimped with pliers for a permanent attachment.					
	-14	18							
	-16	20							
	-22	24							
	-24	28							
	-27	32							
	-32	36							
	-36	40							
						 -00 Lanyard With No Attachment (Fused End)			
						Ring Terminals and Solid Rings			
				 Ring Terminal	-06 – .125 (3.2) I.D. -09 – .156 (3.9) I.D. -03 – .191 (4.9) I.D.				
				 Solid Ring	-19 – 1.140 (29.0) I.D. -21 – 1.265 (32.1) I.D. -23 – 1.453 (36.9) I.D. -27 – 1.640 (41.7) I.D. -30 – 1.875 (47.6) I.D. -31 – 1.953 (49.6) I.D. -33 – 2.077 (52.8) I.D. -35 – 2.140 (54.4) I.D. -40 – 2.406 (61.1) I.D. -44 – 2.656 (67.5) I.D.				
Sample Part Number									
780-001	-19	G	5	-SK					

Series 970 PowerTrip™ Connectors and Accessories
Accessories
 780-001 Bean Rubber Covers



RUBBER COVERS



780-001 AND 780-002 DIMENSIONS										
Shell Size	Type	Part Number	A Dia.		B Dia.		C Typ.		D Dia.	
			In.	mm.	In.	mm.	In.	mm.	In.	mm.
18	Plug	780-001-19	1.58	40.13	1.36	34.54	1.25	31.75	2.18	55.37
	Receptacle	780-002-13	1.22	30.99	1.00	25.40	.63	16.00	1.68	42.67
20	Plug	780-001-22	1.68	42.67	1.44	36.58	1.25	31.75	2.31	58.67
	Receptacle	780-002-16	1.31	33.27	1.09	27.69	.63	16.00	1.81	45.97
24	Plug	780-001-25	1.96	49.78	1.74	44.20	1.25	31.75	2.68	68.07
	Receptacle	780-002-22	1.68	42.67	1.46	37.08	.63	16.00	2.31	58.67
28	Plug	780-001-32	2.31	58.67	2.13	54.10	1.25	31.75	2.98	75.69
	Receptacle	780-002-24	1.80	45.72	1.59	40.39	.69	17.53	2.43	61.72
32	Plug	780-001-36	2.56	65.02	2.32	58.93	1.25	31.75	3.21	81.53
	Receptacle	780-002-27	2.16	54.86	1.75	44.45	.69	17.53	2.58	65.53
36	Plug	780-001-38	2.76	70.10	2.50	63.50	1.25	31.75	3.21	81.53
	Receptacle	780-002-32	2.31	58.67	2.13	54.10	.69	17.53	2.98	75.69
40	Plug	780-001-44	3.06	77.72	2.84	72.14	1.56	39.62	3.58	90.93
	Receptacle	780-002-36	2.56	65.02	2.32	58.93	.69	17.53	3.21	81.53




Series 970 PowerTrip™ Connectors and Accessories

Accessories

780-001 Bean Rubber Covers


RUBBER COVERS FOR SERIES 970 CONNECTORS

RING FOR ATTACHING UNDER JAM NUT RECEPTACLE



Ring Code	Shell Size	Jam Nut Thd.	Ring I.D.
-21	18	1.250	1.265
-23	20	1.4375	1.453
-27	24	1.625	1.640
-31	28	1.9375	1.953
-35	32	2.125	2.140
-40	36	2.375	2.406
-44	40	2.625	2.656

RING FOR ATTACHING OVER ACCESSORY THREAD



Ring Code	Shell Size	Access. Thd.	Ring I.D.
-19	18	1.125	1.140
-21	20	1.250	1.265
-23	24	1.500	1.453
-30	28	1.750	1.875
-33	32	2.000	2.077
-40	36	2.250	2.406
-44	40	2.500	2.656

RING STYLES



Style A Solid Ring



Style B Solid Ring



Ring Terminal



Split Ring

RING REFERENCE TABLE (IN ASCENDING DIAMETER ORDER)

Code	Ring Type	I.D.	Code	Ring Type	I.D.	Code	Ring Type	I.D.	Code	Ring Type	I.D.
		In. mm.			In. mm.			In. mm.			In. mm.
00	No Fitting	- -	13	Solid Ring Style B	.765 19.43	21	Solid Ring Style B	1.265 32.13	78	Split Ring	1.875 47.63
06	Ring terminal	.125 3.18	105	Solid Ring Style A	.766 19.46	109	Solid Ring Style A	1.266 32.16	30	Solid Ring Style B	1.890 48.01
01	Ring terminal	.145 3.68	205	Solid Ring Style A	.788 20.02	209	Solid Ring Style A	1.312 33.32	114	Solid Ring Style A	1.891 48.03
09	Ring terminal	.156 3.96	14	Solid Ring Style B	.844 21.44	22	Solid Ring Style B	1.343 34.11	214	Solid Ring Style A	1.938 49.23
05	Ring terminal	.167 4.24	15	Solid Ring Style B	.890 22.61	68	Split Ring	1.350 34.29	31	Solid Ring Style B	1.953 49.61
02	Ring terminal	.182 4.62	58	Split Ring	.890 22.61	70	Split Ring	1.375 34.93	32	Solid Ring Style B	1.968 49.99
03	Ring terminal	.191 4.85	106	Solid Ring Style A	.896 22.76	110	Solid Ring Style A	1.391 35.33	80	Split Ring	1.980 50.29
04	Ring terminal	.197 5.00	206	Solid Ring Style A	.907 23.04	210	Solid Ring Style A	1.438 36.53	82	Split Ring	2.060 52.32
07	Ring terminal	.218 5.54	16	Solid Ring Style B	.968 24.59	23	Solid Ring Style B	1.453 36.91	33	Solid Ring Style B	2.077 52.76
095	Solid Ring Style A	.312 7.92	17	Solid Ring Style B	1.015 25.78	24	Solid Ring Style B	1.484 37.69	115	Solid Ring Style A	2.078 52.78
100	Solid Ring Style A	.391 9.93	60	Split Ring	1.015 25.78	72	Split Ring	1.485 37.72	35	Solid Ring Style B	2.140 54.36
50	Split Ring	.425 10.80	107	Solid Ring Style A	1.016 25.81	111	Solid Ring Style A	1.521 38.63	36	Solid Ring Style B	2.187 55.55
08	Solid Ring Style B	.468 11.89	207	Solid Ring Style A	1.025 26.04	211	Solid Ring Style A	1.536 39.01	84	Split Ring	2.235 56.77
52	Split Ring	.485 12.32	18	Solid Ring Style B	1.093 27.76	25	Solid Ring Style B	1.577 40.06	86	Split Ring	2.310 58.67
101	Solid Ring Style A	.516 13.11	62	Split Ring	1.095 27.81	74	Split Ring	1.625 41.28	116	Solid Ring Style A	2.406 61.11
102	Solid Ring Style A	.583 14.81	64	Split Ring	1.130 28.70	27	Solid Ring Style B	1.640 41.66	40	Solid Ring Style B	2.406 61.11
10	Solid Ring Style B	.593 15.06	19	Solid Ring Style B	1.140 28.96	112	Solid Ring Style A	1.641 41.68	88	Split Ring	2.475 62.87
54	Split Ring	.640 16.26	108	Solid Ring Style A	1.141 28.98	28	Solid Ring Style B	1.687 42.85	117	Solid Ring Style A	2.510 63.75
103	Solid Ring Style A	.641 16.28	308	Solid Ring Style A	1.188 30.18	76	Split Ring	1.750 44.45	90	Split Ring	2.655 67.44
104	Solid Ring Style A	.708 17.98	208	Solid Ring Style A	1.203 30.56	29	Solid Ring Style B	1.765 44.83	44	Solid Ring Style B	2.656 67.46
12	Solid Ring Style B	.718 18.24	20	Solid Ring Style B	1.203 30.56	113	Solid Ring Style A	1.766 44.86	92	Split Ring	2.810 71.37
56	Split Ring	.750 19.05	66	Split Ring	1.250 31.75	213	Solid Ring Style A	1.812 46.02	48	Solid Ring Style B	3.031 76.99
									94	Split Ring	3.045 77.34

Connectors and Accessories
870P001 PowerTrip Swing-Arm, Non-EMI




HOW TO ORDER				
Sample Part Number	870P 001	MT	20	-4
Product Series	870P001 PowerTrip Swing-Arm, Non-EMI			
Finish Symbols	See Material/Finish Table			
Order Number	See Dimensions Table			
Bushing Option	See Bushing Options Table (Omit for None)			

MATERIAL AND FINISH

- Coupling nut, clamp, saddle bars: See Material/Finish Table
- Hardware: cres/passivate
- Bushing and anti-decoupling device: high temperature thermoplastic / NA

MATERIAL/FINISH			
Symbol	Finish Description	Component	Material
ME	Electroless Nickel	Coupling, Clamp, Saddle Bars	Aluminum Alloy
MT	Nickel - PTFE	Coupling, Clamp, Saddle Bars	
NF	Cad O.D. Over E.N.	Coupling, Clamp, Saddle Bars	
ZR	Zinc - Nickel, Black Over E.N.	Coupling, Clamp, Saddle Bars	300 Series Stainless Steel
ZM	Electroless Nickel	Clamp, Saddle Bars	
	Passivate	Coupling	
ZMT	Nickel - PTFE	Clamp, Saddle Bars	
	Passivate	Coupling	
ZW	Cad O.D. Over E.N.	Clamp, Saddle Bars	
	Passivate	Coupling	
Z1	Passivate	Coupling, Clamp, Saddle Bars	




DIMENSIONS												
Order No.	A Thread Class 2B	B MAX	C ±.031	D MAX	E MAX	F MAX	G MAX	H REF	J MAX	K MAX	L REF	M REF
18	1 1/8-18 UNEF	1.39 (35.31)	0.518 (13.16)	1.795 (45.59)	2.379 (60.43)	2.280 (57.91)	1.211 (30.76)	1.52 (38.61)	1.513 (38.43)	1.310 (33.27)	0.63 (16.00)	0.63 (16.00)
20	1 1/4-18 UNEF	1.53 (38.86)	0.665 (16.89)	1.929 (49.00)	2.504 (63.60)	2.456 (62.38)	1.263 (32.08)	1.81 (45.97)	1.711 (43.46)	1.310 (33.27)	0.75 (19.05)	0.63 (16.00)
24	1 7/16-18 UNEF	1.72 (43.69)	0.795 (20.19)	2.114 (53.70)	2.879 (73.13)	2.805 (71.25)	1.486 (37.74)	2.12 (53.85)	1.901 (48.29)	1.560 (39.62)	0.88 (22.35)	0.75 (19.05)
28	1 13/16-16 UN	2.13 (54.10)	1.080 (27.43)	2.424 (61.57)	3.004 (76.30)	3.031 (76.99)	1.587 (40.31)	2.41 (61.21)	2.169 (55.09)	1.560 (39.62)	1.00 (25.40)	0.75 (19.05)
32	2 1/16-16 UNS	2.35 (59.69)	1.200 (30.48)	2.816 (71.53)	3.629 (92.18)	3.596 (91.34)	2.027 (51.49)	2.75 (69.85)	2.417 (61.39)	2.060 (52.32)	1.13 (28.70)	0.88 (22.35)
36	2 1/4-16 UN	2.59 (65.79)	1.400 (35.56)	3.019 (76.68)	3.754 (95.35)	3.792 (96.32)	2.098 (53.29)	3.03 (76.96)	2.642 (67.11)	2.060 (52.32)	1.25 (31.75)	0.88 (22.35)
40	2 1/2-16 UN	2.87 (72.90)	1.700 (43.18)	3.246 (82.45)	3.879 (98.53)	4.023 (102.18)	2.204 (55.98)	3.32 (84.33)	2.917 (74.09)	2.060 (52.32)	1.38 (35.05)	0.88 (22.35)

Series 970 PowerTrip™


Connectors and Accessories

870P001 PowerTrip Swing-Arm, Non-EMI



BUSHING OPTIONS			
Order Number	Bushing Option	øP	R
18	-2	0.518 (13.2)	0.225 (5.7)
20	-3	0.665 (16.9)	0.215 (5.5)
20	-4	0.665 (16.9)	0.225 (5.7)
24	-2	0.795 (20.2)	0.342 (8.7)
24	-3	0.795 (20.2)	0.341 (8.7)
24	-5	0.795 (20.2)	0.225 (5.7)
28	-4	1.080 (27.4)	0.341 (8.7)
32	-2	1.200 (30.5)	0.508 (12.9)
32	-3	1.200 (30.5)	0.508 (12.9)
32	-5	1.200 (30.5)	0.341 (8.7)
36	-4	1.400 (35.6)	0.508 (12.9)
40	-5	1.700 (43.2)	0.508 (12.9)
40	-5 -2	1.688 (42.9)	0.398 (10.11)

Quick Picks: A Guide to Glenair's Most Popular Materials and Finishes



Electroless Nickel

Cost	\$	\$	\$	\$	\$
Conductivity	+	+	+	+	+
Corrosion Resistance	⌚	⌚	⌚	⌚	⌚

-65 to +200°C

Glenair Code **M, ME**



Aluminum plated with electroless nickel offers excellent conductivity, wear resistance, and adequate corrosion resistance. Typically specified on electrical connectors and accessories used in avionics boxes, exoatmospheric equipment, and missiles, electroless nickel is a good choice when exposure to marine or corrosive atmospheres is not a primary concern. The plating process is purely chemical, and once started, is autocatalytic (it runs by itself).



Marine Bronze

Cost	\$	\$	\$	\$	\$
Conductivity	+	+	+	+	+
Corrosion Resistance	⌚	⌚	⌚	⌚	⌚

-65 to +200°C

Glenair Code **AB**



Marine bronze, an alloy of bronze, aluminum and nickel, is more resistant to the corrosive effects of seawater than ferrous alloys. Used on Glenair's GeoMarine connector coupling nuts, marine bronze is unplated and develops an aluminum oxide protective layer when exposed to air. Marine bronze connectors and accessories are found in shipboard and offshore drilling applications.



Black Zinc Nickel

Cost	\$	\$	\$	\$	\$
Conductivity	+	+	+	+	+
Corrosion Resistance	⌚	⌚	⌚	⌚	⌚

-65 to +175°C

Glenair Code **ZR**



RoHS-compliant black zinc-nickel is approved for MIL-DTL-38999, AS85049 and other major military specifications as a replacement for cadmium and hexavalent chromium platings. The non-reflective finish and good conductivity make the Glenair ZR finish a leading choice for cadmium-free tactical systems. Corrosion resistance is comparable to cadmium, and the ZR finish is backward-compatible with Cd-plated connectors and accessories.



Zinc-Nickel

Cost	\$	\$	\$	\$	\$
Conductivity	+	+	+	+	+
Corrosion Resistance	⌚	⌚	⌚	⌚	⌚

-65 to +175°C

Glenair Code **ZN, ZNU**



Recently added to MIL-DTL-38999 and MIL-DTL-83513, zinc-nickel plated aluminum has become a cost-effective alternative to cadmium. Available with olive drab or black chromate conversion coatings, zinc-nickel plated aluminum is commonly found on soldier systems and military airframe applications.



Cadmium

Cost	\$	\$	\$	\$	\$
Conductivity	+	+	+	+	+
Corrosion Resistance	⌚	⌚	⌚	⌚	⌚

-65 to +175°C

Glenair Code **NE, JF**



Cadmium plated aluminum has been the unchallenged workhorse of the defense/aerospace industry. Offering up to 1000 hours of salt spray protection when deposited over electroless nickel, cadmium is highly conductive, and provides good lubricity and resistance to galling. As plated, cadmium has a silvery appearance. A subsequent chromic acid passivation bath creates a chromate topcoat over the cadmium, enhancing corrosion protection. Olive drab chromate is widely used, followed by gold chromate and clear chromate.



Stainless Steel

Cost	\$	\$	\$	\$	\$
Conductivity	+	+	+	+	+
Corrosion Resistance	⌚	⌚	⌚	⌚	⌚

-65 to +200°C

Glenair Code **Z1, ZL, ZW**



Stainless steel offers unbeatable strength and protection from environmental stress if durability and corrosion resistance are more important than cost and weight. Typically found on aircraft engines, landing gear, geophysical equipment, armored vehicles and marine applications, passivated stainless steel is widely specified in throughout the interconnect industry. Also offered with nickel and cadmium plating for improved conductivity, stainless steel is an obvious alternative to cadmium if cost and weight are not an issue.



Quick Picks: A Guide to Glenair's Most Popular Materials and Finishes




Black Anodize

Cost	\$	\$	\$	\$	\$
Conductivity	+	+	+	+	+
Corrosion Resistance	⌚	⌚	⌚	⌚	⌚

-65 to +175°C
Glenair Code **C**

RoHS COMPLIANT Black anodized aluminum is a popular finish for electrical connectors and accessories. Typically employed when conductivity is not required, black anodized aluminum offers a modicum of corrosion protection and is relatively inexpensive. Anodizing is an electrolytic process that creates aluminum oxide films by oxidizing the base metal. The resulting coating is much harder and denser than natural oxidation. The parts are immersed in a sulfuric acid solution at room temperature. After anodizing, the parts are dyed black.




Chem Film

Cost	\$	\$	\$	\$	\$
Conductivity	+	+	+	+	+
Corrosion Resistance	⌚	⌚	⌚	⌚	⌚

-65 to +175°C
Glenair Code **E**

RoHS Not Compliant Chem Film is Glenair's standard chem film finish. Plated IAW MIL-DTL-5541, Class 3, Chem Film is a relatively inexpensive, moderately durable barrier plating. This chemical conversion coating is intended for use as a corrosion preventative film for electrical and electronic applications where lower resistant contacts, relative to Class 1A coatings, and anodic coatings in accordance with Mil-A-8625, are required.



Zinc-Cobalt

Cost	\$	\$	\$	\$	\$
Conductivity	+	+	+	+	+
Corrosion Resistance	⌚	⌚	⌚	⌚	⌚

-65 to +175°C
Glenair Code **UC, UCR, ZC, ZCR**

RoHS COMPLIANT Zinc-cobalt with olive drab chromate topcoat fills the need for a RoHS compliant conductive NF olive drab finish for military vehicles, robots and other land system equipment.



AlumiPlateSM

Cost	\$	\$	\$	\$	\$
Conductivity	+	+	+	+	+
Corrosion Resistance	⌚	⌚	⌚	⌚	⌚

-65 to +175°C
Glenair Code **AL, XAL**

RoHS COMPLIANT AlumiPlate provides excellent conductivity and corrosion resistance. 99.99% pure aluminum is electrolytically deposited onto aluminum or composite in a specialized water-free process, followed by a trivalent chromate conversion coating. AlumiPlate has been approved by Boeing and Lockheed as a replacement for cadmium. AlumiPlate has been added to MIL-DTL-38999 and MIL-DTL-83513. Threaded parts require dry lube to prevent galling. AlumiPlate is a service mark of AlumiPlate Incorporated, Minneapolis, Minnesota.



Nickel-PTFE

Cost	\$	\$	\$	\$	\$
Conductivity	+	+	+	+	+
Corrosion Resistance	⌚	⌚	⌚	⌚	⌚

-65 to +175°C
Glenair Code **MT, ZMT**

RoHS COMPLIANT Now approved for MIL-DTL-38999 and MIL-DTL-83513, Glenair's 1000 Hour Grey™ meets the need for a cadmium replacement with excellent conductivity, wear resistance and corrosion protection. This extremely durable finish is gun-metal gray. A proprietary preliminary undercoat is followed with a composite coating of electroless nickel phosphorus and polytetra-fluoroethylene (PTFE). An organic topcoat provides sealing and added resistance to SO2 salt fog. Ni-PTFE is approved for the Joint Strike Fighter and offers extremely good lubricity.



Hardcoat Anodize

Cost	\$	\$	\$	\$	\$
Conductivity	+	+	+	+	+
Corrosion Resistance	⌚	⌚	⌚	⌚	⌚

-65 to +200°C
Glenair Code **G2**

RoHS COMPLIANT Hardcoat anodized aluminum offers greater wear resistance and better corrosion resistance compared to conventional anodizing. Typically employed when conductivity is not required, hardcoat aluminum offers good corrosion protection for marine and tactical applications. The resulting finish is a matte greenish-gray color. Hardcoat anodizing is an electrolytic process that creates aluminum oxide films by oxidizing the base metal in a sulfuric acid solution. The parts are immersed in a sulfuric acid solution at cold temperature. After anodizing, the parts can be dyed black (code GB).

M

Why Choose **GLENAIR?**



Plenty of Raw Materials!



Outstanding
Customer Service!



In-House Assembly!



Abundant Machining Capacity!




Huge "Same-Day" Inventory!



One of North America's
and Machining



High-Production Injection Molding Equipment



State-of-the-Art Plating Capabilities



The Industry's Most Experienced EMI/RFI Braided Shielding Specialists



Largest CNC Milling Installations



Clean Rooms for Filter Array and Printed Circuit Board Assembly



Out of This World
**INTERCONNECT
SOLUTIONS**

Glenair, Inc.

1211 Air Way • Glendale, California • 91201-2497
Telephone: 818-247-6000 • Fax: 818-500-9912 • sales@glenair.com
www.glenair.com

**Glenair Power
Products Group**

860 N. Main Street Extension
Wallingford, CT
06492

Telephone:
203-741-1115
Facsimile:
203-741-0053
sales@glenair.com

Glenair UK Ltd

40 Lower Oakham Way
Oakham Business Park
P.O. Box 37, Mansfield
Notts, NG18 5BY England

Telephone:
+44-1623-638100
Facsimile:
+44-1623-638111
sales@glenair.co.uk

Glenair Microway Systems

7000 North Lawndale Avenue
Lincolnwood, IL
60712

Telephone:
847-679-8833
Facsimile:
847-679-8849

Glenair Nordic AB

Gustav III : S Boulevard 46
S - 169 27 Solna
Sweden

Telephone:
+46-8-50550000
Facsimile:
+46-8-50550001
sales@glenair.se

Glenair Electric GmbH

Schaberweg 28
D. 61348 Bad Homburg
Germany

Telephone:
06172 / 68 16 0
Facsimile:
06172 / 68 16 90
germany@glenair.com

Glenair Iberica

C/ La Vega, 16
45612 Velada
Spain

Telephone:
+34-925-89-29-88
Facsimile:
+34-925-89-29-87
sales@glenair.es

Glenair Italia S.p.A.

Via Del Lavoro, 7
40057 Quarto Inferiore –
Granarolo dell'Emilia
Bologna, Italy

Telephone:
+39-051-782811
Facsimile:
+39-051-782259
info@glenair.it

Glenair France SARL

7, Avenue Parmentier
Immeuble Central Parc #2
31200 Toulouse
France

Telephone:
+33-5-34-40-97-40
Facsimile:
+33-5-61-47-86-10
sales@glenair.fr

